



# Thinsulate™ Acoustic Insulation

## TAI and SM Series (400 and 600 gram)

Technical Data Sheet

January 2012


### General Description

3M™ Thinsulate™ Acoustic Insulation is a superior sound-absorbing material specifically designed for a variety of acoustic control applications. It is recommended for acoustic control in vehicle door panels, headliners, wheel wells, pillars, and instrument panels. It is available regionally with the same performance globally.

Thinsulate Acoustic Insulation is compressible, lightweight, conformable, and can easily be die-cut, heat sealed and thermally or sonically bonded to many other substrates.

### Acoustic Properties

#### Normal Incidence ASTM E-1050



### Physical Properties<sup>A</sup>

	Weight <sup>B</sup>	Thickness <sup>C</sup>	Density	Thermal Properties		FMVSS 302
	g/m <sup>2</sup> (oz/ft <sup>2</sup> )	mm (in)	kg/m <sup>3</sup> (lb/ft <sup>3</sup> )	R-Value <sup>D</sup>	R-Value/cm	(≤101.6mm/min)
TAI4027	415 (1.36)	26 (1.02)	16.0 (1.00)	3.7	1.42	Pass
TAI4027LA	431 (1.41)	26 (1.02)	16.5 (1.03)	3.7	1.42	Pass
TAI4047	400 (1.31)	23 (0.91)	17.4 (1.08)	3.4	1.48	Pass
TAI4048	420 (1.38)	13 (0.51)	32.3 (2.02)	2.0	1.54	Pass
SM 400L	442 (1.45)	26 (1.02)	17.0 (1.06)	3.8	1.46	Pass
SM 600L	642 (2.10)	42 (1.65)	15.3 (0.95)	5.2	1.25	Pass

<sup>A</sup> Data is representative of average values of stock before converting; it includes scrims and adhesives as appropriate.

<sup>B</sup> Weight is the mass per unit area of the entire absorber composite.

<sup>C</sup> Nominal thickness is measured using a 12 in<sup>2</sup> plate with 0.002 psi applied to the sample.

<sup>D</sup> R-Value (ft<sup>2</sup>hr<sup>2</sup>F/BTU) is the thermal resistance of the insulation measured at the corresponding thickness.

Thermal conductivity, k=0.039 W/m<sup>2</sup>K

# Technical Data Sheet

3M™ Thinsulate™ Acoustic Insulation TAI and SM Series (400 and 600 gram)

Page 2

---

**Contact Information** For additional technical information, please contact your local 3M Acoustic Solutions Technical Service Representative. In the US, please contact 1-866-887-8438.

3M and Thinsulate are Trademarks of 3M Company.

**Technical Information:** The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

**Product Use:** Many factors beyond 3M's control and uniquely within the user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

**Warranty, Limited Remedy, and Disclaimer:** Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

**Limitation of Liability:** Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.



**Automotive Division**  
3M Center, Building 223-1S-02  
St. Paul, MN 55144-1000  
[WWW.3M.com/autosolutions](http://WWW.3M.com/autosolutions)  
1-866-887-8438

© 3M 2012  
70-0714-0494-4  
Printed in U.S.A.