

3M™ Pressure Sensitive
Acrylic Foam and Acrylic *Plus* Tape Sample Chart



3M™ Pressure Sensitive Acrylic Foam and Acrylic *Plus* Tape Sample Chart

	Tape	Passes OEM Specification*		Thickness	Adhesive	Liner	Core Color	Typical Application
3M™ Pressure Sensitive Acrylic Foam Tape	4257YCL	GM	GMW15201 Type XIII A	0.015 in 0.38 mm	AR5/DS6	RS-1	Gray	Windowlace
		Chrysler	MS-12194					
	5314	Ford	WSS-M11P65-A2 ⁽¹⁾	0.03 in 0.76 mm	AR7/DS4	FL-10	Gray	Narrow Body Side Moldings/Nameplates/ Sill Plates
		GM	GMW15201 Type VIA					
		Chrysler	MS-12194					
	5344	Ford	WSS-M11P65-A2 ⁽¹⁾	0.045 in 1.14 mm	AR7/DS4	FL-10	Gray	Body Side Moldings Appliques
		GM	GMW15201 Type VIB					
		Chrysler	MS-12194					
	5390	Ford	WSS-M11P65-A2 ⁽¹⁾	0.09 in 2.29 mm	AR7/AR7	FL-10	Gray	Claddings Roof Ditch Moldings
		GM	GMW15201 Type XIIIC					
		Chrysler	MS-12194					
	5567	Ford	WSS-M11P65-A2 ⁽¹⁾	0.06 in 1.52 mm	AR7/DS4	FL-10	Gray	Body Side Moldings Claddings Wheel Flares
		GM	GMW15201 Type VIC					
		Chrysler	MS-12194					
	5605	GM	GMW15201 Type VIIA	0.045 in 1.14 mm	AR7/TX1	SC2 ⁽²⁾	Gray	Primerless to TPO
		Chrysler	MS-12194					
	GT7108			0.031 in 0.80 mm	Acrylic/ Acrylic	TLR	Gray	Body Side Moldings Appliques
	RT8008	Toyota	Confidential	0.031 in 0.80 mm	Acrylic/ Acrylic	TL0	Gray	Body Side Moldings Spoilers
	RT8012	Toyota	Confidential	0.047 in 1.2 mm	Acrylic/ Acrylic	TL0	Gray	Body Side/Roof Ditch Moldings Claddings/Spoilers
3M™ Pressure Sensitive Acrylic <i>Plus</i> Tape	EX4011	Ford	WSS-M11P65-A2	0.045 in 1.14mm	JL2/VR1	KL1 ⁽³⁾ / KL2 ⁽²⁾	Black	Body Side Moldings/ Claddings/Wheel Flares
		GM	GMW15201 Type IXB					
		Chrysler	MS-12194					
	EX4015	Ford	WSS-M11P65-A2	0.06 in 1.52 mm	JL2/VR1	KL1 ⁽³⁾ / KL2 ⁽²⁾	Black	Body Side Moldings Claddings/Wheel Flares/Spoilers Roof Ditch Moldings
		GM	GMW15201 Type IXC					
		Chrysler	MS-12194					
	PT1100	Ford	WSS-M11P65-A2	0.045 in 1.14mm	VR2/VR1	GL1 ⁽²⁾ / GL3 ⁽³⁾	Black	Body Side Moldings Fender Vents
		GM	GMW15201 Type VIIIA					
		Chrysler	MS-12194 Type B					
	PT1500	Ford	WSS-M11P65-A2	0.06 in 1.52mm	VR2/VR1	GL1 ⁽²⁾ / GL3 ⁽³⁾	Black	Body Side/Roof Ditch Moldings Spoilers
		GM	GMW15201 Type VIIIB					
		Chrysler	MS-12194 Type B					
3M™ Die-Cuttable Tape	DC2008	Ford	WSS-M11P65-A	0.03 in 0.76mm	DL2/DL1	SC2 ⁽²⁾ / PET ⁽²⁾	Black	Nameplates/Badges
		GM	GMW15201 Type IB					
		Chrysler	MS-12194 Type A					
	DC2011	Ford	WSS-M11P65-A	0.045 in 1.14mm	DL2/DL1	SC2 ⁽²⁾ / PET ⁽²⁾	Black	Nameplates/Badges
		GM	GMW15201 Type IC					
		Chrysler	MS-12194 Type A					

* For products approved to OEM specifications not listed, please contact a 3M Application Engineer.

⁽¹⁾ Review with 3M Application Engineering required for use ⁽²⁾ Silicone coated – two sides ⁽³⁾ Silicone coated – one side

3M™ Adhesion Promoter Selection Guide

This selection chart is intended as an initial guide for obtaining the appropriate 3M™ Adhesion Promoter. Since applications vary with materials, stress, procedures, environmental exposures, etc., it is important to determine through testing the most suitable 3M promoter to meet your specific application need. This chart cannot take into account every variable for each application. 3M has an extensive product offering. If the below selection does not meet your needs or you need further help and information, please contact your 3M Automotive Division representative.

- Primary Choice
- Other Possible Options

Substrate	4298UV ⁽²⁾	4296T	2262AT	C100J	K500	K500NT ⁽¹⁾	K520UV ⁽²⁾	K540UVNT ⁽¹⁾⁽²⁾	N200J	N200NT ⁽¹⁾
PVC			•	•					•	•
TPO	•				•	•	•	•		
TPU	•	•		•					•	•
Fascia Paint		•		•					•	•
EPDM	•				•	•	•	•		
Santoprene®	•				•					
ABS	•		•	•					•	•
PP	•				•	•	•	•	•	•
TPV/TPE	•				•	•				
PC	•								•	•
Glass Visible Bond	•									
Glass Hidden Bond	•									
Acrylic	•									
Nylon	•		•						•	•

⁽¹⁾ NT products (K500NT, K540UVNT and N200NT) are a HAPS reduction. Solvent-based adhesion promoter use is limited in California as required by Air Quality Management Directive.

⁽²⁾ 3M™ Adhesion Promoters 4298UV, K520UV and K540UVNT contain a UV-visible dye. Primer on parts will glow under black light, to allow visual verification of primer coverage. This dye is available for customer addition to 3M™ Adhesion Promoter 4296T. Use of this dye with other adhesion promoters is not recommended without prior consultation with 3M technical service personnel.

These adhesion promoters are not interchangeable. Mixing or substituting adhesion promoters without consultation with 3M technical service personnel can lead to adhesion failures. Care must be taken to ensure that adhesion promoters are not inadvertently mixed or substituted when poured into bottles or other containers to facilitate application to parts.

Contact 3M at 1-800-328-3081 for ordering or questions.

3M is a registered trademark of 3M Company.

Warranty, Limited Remedy, and Disclaimer: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. User is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application. Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.



Automotive Division

3M Center, Building 223-1S-02
St. Paul, MN 55144-1000
www.3M.com/autosolutions
1-800-328-1684

Please recycle. Printed in U.S.A.
© 3M 2012. All rights reserved.
75-3470-8770-4