3M<sup>™</sup> Heat-Activated Acrylic Foam and Acrylic *Plus* Tape Sample Chart

## Provenue of the second second



## 3M<sup>™</sup> Heat-Activated Acrylic Foam and Acrylic Plus Tape Sample Chart

Таре	OEM Specified*		Thickness		Oana Oalar	Adhesive		Heat-Activated Adhesive Bonds to						
			in	mm	Core Color	HAA/PSA <sup>(1)</sup>	Liner	Neoprene	PVC	Alcryn®	EPDM	Santoprene®	<b>Kraton</b> ®	TPV/TPE
3412	2		0.047	1.2	Gray	E2/DS6	Red Printed PE				•	•	•	•
4981			0.008	0.2	Clear	E2/A10	PE				•	•	•	•
5935	Chrysler Ford GM	MS-CC260 WSS-M3G168B GMW15201 Type XA	0.016	0.4	Gray	E2/AR7	Orange PE				٠	•	•	•
5403	Chrysler Ford GM	MS-CC260 WSS-M3G168B GMW15201 Type XB	0.032	0.8	Gray	E2/AR7	Orange PE				•	•	•	•
5404	Chrysler Ford GM	MS-CC260 WSS-M3G168B GMW15201 Type XC	0.047	1.2	Gray	E2/AR7	Orange PE				•	•	•	•
5933	Ford	WSS-M3G168B GMW15201 Type XC	0.045	1.1	Gray	N1/AR7	Red PE	•	•	•				
ST1200	Chrysler Ford GM	MS-CC260 WSS-M3G168B GMW15201 Type XI	0.047	1.2	Black	E2/VR2	Red PE				٠	•	•	
WT4112	Ford	WSS-M3G168B GMW15201 Type XII	0.047	1.2	Black	E2/JL2	Red PE				٠	•	٠	•

 $^{*}$  For products approved to OEM specifications not listed, please contact a 3M Application Engineer.

This selection chart is intended as an initial guide for selecting the appropriate 3M<sup>™</sup> Heat-Activated Acrylic Foam and Acrylic Plus Tapes. Since applications vary with materials, stress, procedures, environmental exposures, etc., it is important to determine through testing the most suitable 3M tape to meet your specific application. This chart cannot take into account every variable for each application. 3M has an extensive product offering. If the above selection does not meet your needs or if you need further help and information, please contact your 3M Automotive Division representative.

## Benefits of 3M<sup>™</sup> Heat-Activated Tapes vs. Alternative Attachment Methods

Attachment Method	Diagram	Benefits of using 3M Heat-Activated Tapes				
<b>3M Heat-Activated Tape</b> Can be applied to most surfaces with manual or automatic installation		<ul> <li>3M Heat-Activated Tape</li> <li>Provides a continuous seal against moisture</li> <li>Reduces noise levels inside vehicles</li> <li>Offers design flexibility with lower overall system cost</li> </ul>				
<b>Pins</b> Require holes for application and manual installation		<ul> <li>3M Heat-Activated Tape</li> <li>Does not require holes</li> <li>Eliminates potential corrosion sites and possible seal gaps between pins</li> <li>Eliminates potential noise path</li> <li>Improves application ergonomics</li> </ul>				
<b>Channel</b> Requires channel for application and manual installation		<ul> <li>3M Heat-Activated Tape</li> <li>Reduces weight by elimination of wire carrier</li> <li>Reduces cost by eliminating channel welding and sealant process steps</li> <li>Eliminates potential leak path under channel</li> </ul>				
<b>Wire Carrier</b> Requires flange for application and manual installation		<ul> <li>3M Heat-Activated Tape</li> <li>Reduces weight by elimination of channel</li> <li>Offers simpler extrusion profile for tier suppliers</li> <li>Eliminates corrosion concerns associated with the wire</li> <li>Accomodates multiple sheet metal thicknesses</li> </ul>				
<b>Liquid</b> Can be applied to most horizontal surfaces		<ul> <li>3M Heat-Activated Tape</li> <li>Offers higher initial holding power and consistent seal height</li> <li>Enables cleaner installation</li> <li>Eliminates sliding and oozing</li> </ul>				

3M is a trademark of 3M Company. Alcryn® is a registered trademark of Advanced Polymer Alloys. Kraton® is a registered trademark of Kraton Polymers. Santoprene® is a registered trademark of AES.

Warranty, Limited Remedy, and Disclaimer: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. User is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application. Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

## **3**M

Automotive Division 3M Center, Building 223-1S-02 St. Paul, MN 55144-1000 www.3M.com/autosolutions 1-800-328-1684

Please recycle. Printed in U.S.A. © 3M 2012. All rights reserved. 75-3470-8771-2