

3M Commercial Graphics

Scotchgard™ Graphic and Surface Protection Films



Robust and Effective Against Vandalism

Product range includes: SG8991, SG8991R, SG8993, SG8995

- Gloss and matte finishing
- Polyester films for indoor and outdoor graphic and surface protection
- Solution against vandalism and graffiti to reduce maintenance costs

3M



Scotchgard™ Graphic and Surface Protection Film 8991
 Scotchgard™ Removable Graphic and Surface Protection Film 8991R
 Scotchgard™ Graphic and Surface Protection Film 8993
 Scotchgard™ Graphic and Surface Protection Film 8995-124

Effective protection against vandalism damage

Scratch marks and graffiti on exterior and interior surfaces into rolling cars or any other public transportation vehicle, public transit or other surfaces, look very much unattractive and unpleasant in the eyes of passengers and people. Occurring more and more frequently the rail industry suffers from property damage due to vandalism for millions of Euro every year.

3M Anti-Graffiti and Scratch-Resistant Films are effective aids for offering your passengers a clean environment and providing optimal protection for any surface you care and you want to keep protect.

Coloured films and printed graphics overlamine

Polyester films take care to Corporate Identity colours and images, protecting short and long term investments. Graffiti can be easily removed during cleaning process and reducing overall maintenance costs.



Product range

Scotchgard™ Graphic and Surface Protection Film range is available in the following range:

Product	Finishing	Adhesive type	Thickness
SG8991	High gloss	Permanent	100 µm (0.1 mm)
SG8991R	High gloss	Removable	100 µm (0.1 mm)
SG8993	High gloss	Permanent	25 µm (0.025 mm)
SG8995-124	Matte	Permanent	25 µm (0.025 mm)

3M™ MCS™ warranty

With 3M MCS warranty, you can be absolutely confident of the perfect appearance of your printed or unprinted film or any surface you need to protect.



Graffiti removal

3M Graffiti Remover System cleans paint smears from plastic or painted surfaces gently and effectively. Ideal in conjunction with 3M Graphic and Surface Protections Films.

3M film removal

Hot steam device is suitable for removing PVC film with overlamine within the warranty period of time, without adhesive residue.

For more details please see our product information at www.3Mgraphics.com or contact your 3M distributor.



3M Europe S.A./N.V.
Commercial Graphics
 Hermeslaan 7
 1831 Diegem, Belgium
www.3Mgraphics.com

Please recycle. Printed in Germany
 © 3M 2012. All rights reserved.