3MTM Cold Shrink QT-III Silicone Rubber Skirted Termination Kit 7673-S-8 & 7673-S-10 Series

Data Sheet January 2016

Description

3M Cold Shrink QT-III Silicone Rubber Skirted Termination Kit 7673-S-8 & 7673-S-10 Series contains one silicone rubber, non-self supporting termination qualified to IEEE 48 Class 1 for 69 kV and IEC 60840 for 72.5 kV for outdoor termination applications.

The complete termination is constructed of four sub-assemblies: 1) The Silicone Rubber Skirted Stress Control Assembly 2) The Hi-K Stress Control Adapter Assembly 3) The Silicone Rubber Lug Seal Assembly 4) The Silicone Rubber Ground Seal Assembly. The skirted assembly consists of an inner Hi-K stress control layer and 8-10 silicone rubber skirts. Each assembly is pre-stretched and loaded on a support core. Following installation, the support cores can be recycled.

The termination kit shall include a high ampacity ground strap assembly as a means for grounding the terminated cable's metallic insulation shield. The ground strap assembly consists of a three-loop pre-formed ground braid with a 2-hole copper lug crimped onto the ground braid tails. Three constant force springs are used to attach the ground strap assembly to the cable's metallic shield.

The 3M cold shrink QT-III termination kit 7673-S-8 & 7673-S-10 Series are designed to terminate 69 kV, 650 mil solid dielectric, Tape (TS), Longitudinally Corrugated (LC), Jacketed Concentric Neutral (JCN), Tape Over Wire (TOW), or Wire Over Tape (WOT) shielded power cable. Covering a conductor size range of 1/0AWG to 3000 kcmil (50 -1500 mm²). The 3M cold shrink QT-III termination kit 7673-S-10 series provide a longer creepage path for higher contamination environments. See the selection table for detailed sizing information.

Kit Contents

Each kit contains sufficient quantities of the following materials as appropriate to make one singlephase termination (lug not included unless requested in advance):

- Silicone Rubber Skirted Stress Control Assembly
- Hi-K Stress Control Adapter Assembly
- Lug Seal Tube
- Ground Seal Tube
- Ground Strap Assembly
- Constant Force Springs
- Tubes 3M Red Compound P55/R (Non-Silicone Grease)
- Scotch[®] Electrical Shielding Tape 24
- 3M Scotch-Seal[™] Mastic Tape Compound 2229
- 3M EMI Copper Foil Shielding Tape 1181
- Scotch[®] Vinyl Electrical Tape Super 88
- Scotch[®] Linerless Rubber Splicing Tape 130C (WB kits only)
- 3M Cable Cleaning Pads CC-3
- Scotch[®] Self-fusing Silicone Rubber Electrical Tape 70
- Instruction Sheets



3MTM Cold Shrink QT-III Silicone Rubber Skirted Termination Kit 7673-S-8 & 7673-S-10 Series

Features

- Conforms to IEEE 48 Class 1 requirements for 69 kV, 350 kV BIL outdoor applications and to IEC 60840 for 72.5 kV, 325 kV BIL outdoor applications.
- Can be used on cables with a maximum temperature rating of 105°C and an emergency overload rating of 140°C.
- Hi-K stress control, specifically formulated high dielectric constant material minimizes surface stress by more uniformly distributing the electrical stress over the entire surface of the insulator.
- Cold shrink delivery system for easy installation. Simply slide each termination sub-assembly over the prepared cable to its proper position and unwind the core to shrink in place.
- Installation temperature range of -4F to 122F (-20°C to +50°C)
- An improved compact design allows for easier Porcelain/Heat Shrink termination replacement and new installations in restricted spaces.
- Silicone rubber materials are compatible with all common solid dielectric cables, such as cross-linked polyethylene (XLPE), ethylene propylene rubber (EPR), or polyethylene (PE).
- Designed to accommodate all available cable lugs designs including hexagonal or deep indent crimping technologies or a variety of mechanical sheer-off connecting technologies.

Applications

The 3M Cold Shrink QT-III Silicone Rubber Skirted Termination Kit 7673-S-8 & 7673-S-10 Series are designed for :

- Outdoor installations required to meet:
- IEEE 48 Class 1 for 69 kV and/or IEC 60840 for 72.5 kV.
- Applications requiring 350 kV BIL performance levels.
- Solid dielectric insulation, such as (XLPE), (EPR), and (PE).
- Tape (TS), Longitudinally Corrugated (LC), Jacketed Concentric Neutral (JCN), Tape Over Wire (TOW), or Wire Over Tape (WOT) shield configurations.

Pollution Class Rating

Part Number	Specific Creepage Distance*	USCD Required for 72.5kV	
T dit Ndilibei	mm/kV	per IEC 60815	
7673-S-8(S)	49.7	Class (d) 43,3 mm/kV	
7673-S-8	49.7	Heavy	
7673-S-10(R)	54.0	Class (d) 53,7 mm/kV	
7673-S-INV-10(R)	54.0	Very Heavy	
7673-S-10(S)	63.5	Class (e) 53,7 mm/kV	
7673-S-10	03.5	Very Heavy	

^{*}Calculation based on U₀ (phase to ground) voltage for 72.5kV system, for 69kV systems mm/kV will be higher.


3MTM Cold Shrink QT-III Silicone Rubber Skirted Termination Kit 7673-S-8 & 7673-S-10 Series

Selection Table	Kit Number	Primary Insulation OD Range Inches (mm)	Jacket OD Range Inches (mm)	Typical Conductor* Size Range AWG/Kcmil (mm²)	Maximum Lug Width Inches (mm)
	7673-S-8(S)	2.01-2.87 (51,1-72,9)	2.25-3.45 (57,2-87,6)	350-1500 (175-725)	3 (76)
	7673-S-8	2.79-3.45 (70,9-87,6)	3.00-4.25 (76,2-108,0)	1500-3000 (800-1500)	4 (102)
	7673-S-10(R) 7673-S-INV- 10(R)	1.30-2.36 (33,0-60,0)	1.60-2.85 (40,6-72,4)	1/0-350 (50-175)	2 (51)
	7673-S-10(S) 7673-S- INV- 10(S)	2.01-2.87 (51,1-72,9)	2.25-3.45 (57,2-87,6)	350-1500 (175-725)	3 (76)
	7673-S-10 7673-S- INV-10	2.79-3.45 (70,9-87,6)	3.00-4.25 (76,2-108,0)	1500-3000 (800-1500)	4 (102)

^{*}Sizing based on 650 mil insulation thickness. For reduced wall cables, use the cables Primary Insulation OD and the ranges shown above to determine the correct kit for the application. Kits with an added suffix may contain materials such as: a lug, mounting bracket, cable clamps, special instructions, "WB" for additional water blocking of 10 skirt kits or other application specific.

Typical Dimensions


Kit Number	Dimension A Typical	Creepage Distance Typical
7673-S-8(S) 7673-S-8	46" (117 cm)	82" (208 cm)
7673-S-10(R) 7673-S-INV-10(R)	49" (124 cm)	89" (226 cm)
7673-S-10(S) 7673-S-10	52" (132 cm)	105" (266 cm)



Typical Physical and Electrical Properties

Typical Materials Data for Silicone Rubber

Property	Units	Numerical Value		
		Insulation	Semi- Conductive	High- Permittivity
Hardness	Shore A	30	40	40
Tensile Strength	Мра	7.5	6.0	5.5
Ultimate Elongation	%	750	600	400
Tear Resistance	N/mm	25	20	15
Compression Set	%	20	20	15
Volume Resistivity	Wcm	10 ¹⁵	<100	10 ¹¹
Dielectric Strength	kV/mm	25	-	-
Relative Permittivity		2.8	-	20
Dielectric Loss Factor Tan ō		0.003	-	0.1
Service Temperature Range	°C	-20 to +50	-20 to +50	-20 to +50



Product Specification

The non-self supporting cable termination must have a voltage rating equal to or greater than the cable being terminated. The termination shall be rated for 69 kV, 350 kV BIL and meet the requirements of IEEE 48 for Class 1 outdoor termination. The termination shall meet the requirements of IEC 60840 for 72.5 kV outdoor terminations. It must have a maximum operating temperature of 105°C, with an emergency overload temperature of 130°C. The termination kit shall consist of four cold shrink subassemblies, 1) Silicone Rubber Lug Seal Assembly. 2) Stress Control Assembly. 3) Silicone Rubber Ground Seal Assembly. 4) Silicone Rubber 8 Skirt Insulator Assembly. All exposed insulating materials shall be manufactured of track-resistant silicone rubber. The termination kit shall include a ground strap assembly as the means of grounding the terminated cable. The ground strap assembly shall consist of a three loop pre-formed ground braid with a copper lug crimped onto the ground braid tails. Three constant force springs shall be used to attach the ground strap assembly to the cable's metallic shield. The termination stress control shall be capacitive and constructed of a Hi-K stress control assembly and a Hi-K/Skirted insulator assembly. The termination subassemblies shall be prestretched cold shrink design, and installed by removing the support core. The termination kit shall include all materials necessary for installation on a single-conductor shielded power cable except for the lug, unless specified in advance.

Engineering/ Architectural Specification

Terminate shielded power cable rated for 69 kV, 350 kV BIL per IEEE 48 - Class 1 for outdoor non-self supporting terminations using a 3M Cold Shrink QT-III Silicone Rubber Skirted Termination Kit 7673-S-8 & 7673-S-10 Series.

Terminate shielded power cable rated for 72.5 kV, 325 kV BIL per IEC 60840 for outdoor termination with 3M Cold Shrink QT-III Silicone Rubber Skirted Termination Kit 7673-S-8 & 7673-S-10 Series.

Typical Performance Testing

Typical Results, IEEE Standard 48 Long-Term Test Sequence

3M [™] Cold Shrink Silicone QT-III Rubber Skirted Termination Kit 7673-S-8 & 7673-S- 10 Series	69 kV		
Insulation Class Test	Requirements	Typical Value	
Partial Discharge Extinction Voltage @ 3 pC*	60 kV	80 kV	
Power Frequency Voltage 1 Min. Dry Withstand	175 kV	Pass	
Power Frequency Voltage 6 Hour Dry Withstand	120 kV	Pass	
Power Frequency Voltage 1 Min. Wet Withstand	145 kV	Pass	
Direct Voltage 15 Min. Dry Withstand	245 kV	Pass	
Lightning Impulse Voltage Withstand (BIL)	350 kV	Pass	
Partial Discharge Extinction Voltage @ 3 pC	60 kV	80 kV	
Cycling Aging (30 Days, 130°C Cond. Temp.)	80 kV	Pass	
Lightning Impulse Voltage Withstand (BIL)	350 kV	Pass	
Partial Discharge Extinction Voltage @ 3 pC	60 kV	80 kV	
Pressure Leak (See Sealing Tests Below)	7 psi for 6 hours	Pass	

^{*}IEEE 48 Requires <5 pC @ 60 kV

Typical Results, IEC 60840 Test Sequence

3M [™] Cold Shrink QT-III Silicone Rubber Skirted Termination Kit 7673-S-8 & 7673-S- 10 Series	72.5 kV		
Insulation Class Test	Requirements	Typical Value	
PD at Ambient CSV 63 kV for 10 Sec CEV 54 kV	Pass	Pass	
Load Cycle for 20 Cycles (8 Hour Loading to 95°C-100°C, at Least 2 Hours at Temperature, and 16 Hours Off-24 cycle) at 72 kV	Pass	Pass	
PD at Ambient	Pass	Pass	
PD at Elevated Temperature (95-100°C)	Pass	Pass	
Impulse (10 Impulses Each Polarity) at Elevated Temperature (95°-100°C)	Pass	Pass	
15 Min AC Withstand at 90 kV	Pass	Pass	
Cable and Accessory Examination	Pass	No Evidence of Electrical Activity	

Test Definitions

Partial Discharge (Corona) Tests

The purpose of partial discharge testing is to determine that all properly installed terminations operate corona free at a minimum of 150% of their operating voltage. For the test, the applied test voltage is gradually increased until discharges appear on the test set oscilloscope display. The voltage at which these discharges reach a magnitude greater than 3 Pico coulombs is recorded as the corona starting voltage (CSV). The applied voltage is then lowered until the discharge level drops below 3 Pico coulombs, and this is recorded as the corona extinction voltage (CEV).

Lightning Impulse Tests

The 3M Cold Shrink QT-III Silicone Rubber Skirted Termination Kit 7673-S-8 & 7673-S-10 Series was evaluated to IEEE Standard 48 Basic Impulse Levels. For this test a 1.2 X 50 microsecond voltage wave is applied to the termination lug. The test consists of both positive and negative polarity surges per the specified standard. The 3M cold shrink QT-III termination kit 7673-S-8 & 7673-S-10 Series meets or exceeds the requirements of IEEE Standard 48.

Power Frequency (AC) Withstand Tests

The AC Power Withstand test consists of a 1 minute dry withstand. 10 second wet withstand and 6 hour dry withstand per the voltages specified in Table 2 of IEEE Standard 48. The 3M cold shrink QT-III termination kit 7673-S-8 & 7673-S-10 Series meets the requirements of IEEE Standard 48 Class 1. Additional AC Withstand for 1 hr. after current cycling.

Sealing Tests

Termination top and bottom seals are tested by applying 7 psi (0.05 MPa) and a vacuum of ~13 Pisa to the cable conductor strands with the termination submerged in water. Both seals withstand this internal air pressure for 6 hours and vacuum for 30 minutes without leaking. Per IEEE 48, 8.4.3a Pressure Leak Tests.

EHS



CAUTION

Working around energized electrical systems may cause serious injury or death. Installation should be performed by personnel familiar with good safety practice in handling high-voltage electrical equipment. De-energize and ground all electrical systems before installing product.

3M Cold Shrink Removable Core is mixed polymer and recyclable with 🖄 waste.




Read all Health Hazard, Precautionary and First Aid statements found in the Material Safety Data Sheet (MSDS) and/or product label prior to handling or use.


Installation

Detailed instructions are included in each kit to provide the installer with all of the information required to properly install the 3M Cold Shrink QT-III Silicone Rubber Skirted Termination Kit 7673-S-8 & 7673-S-10 Series. A brief summary of the typical installation steps are outlined as follows:


- 1. Prepare the cable following standard procedures.
- 2. Install the Cold Shrink Hi-K Stress Control Assembly.




3. Install the Cold Shrink Silicone Rubber Skirted Assembly.



4. Shrink the Ground Seal Tube at the bottom of the termination.



5. Shrink the Lug Seal Tube covering the top of the skirted assembly and onto the lug barrel.



3MTM Cold Shrink QT-III Silicone Rubber Skirted Termination Kit 7673-S-8 & 7673-S-10 Series

Maintenance

It is good practice to incorporate a general inspection/cleaning of 3M Cold Shrink QT-III Silicone Rubber Skirted Termination Kits during normal scheduled or maintenance inspections. Once the area has been de-energized, the terminations can be inspected, and if need be, cleaned. Some recommendations for surface cleaning 3M Cold Shrink QT-III Silicone Rubber Skirted Terminations are as follows:

Use a can of compressed 'air' in order to blast off dust and miscellaneous airborne contaminants on the surface of the termination body. If needed, wipe the surface of the termination with a cable cleaning solvent, such as 3M Cable Cleaning Solvent (CC-2), and allow it to dry before reenergizing the installation.

Mix a mild soap and water solution (deionized water is recommended, if available) in a hand sprayer, or spray bottle, and spray down the surface of the termination. Wipe dry, or allow to air dry, before re-energizing.

If tan discoloration between skirts is observed on the surface of the termination, wipe with a cable cleaning solvent. The discoloration itself does not pose any detrimental effect to the installation, and may not disappear entirely, but it will lighten up to some degree. This discoloration is a typical result of the outgassing effect of EPR cable and does not interfere with the performance of the termination in any capacity.

Do not abrade the surface of the termination in any way. Do not use high pressure cleaning (this can tear, or split, the termination), high pressure water with corn cobs, sandpaper or other abrasive products. This will damage the termination surface and reduce tracking and arcing resistance provided, in the expanded state.

Shelf Life & Storage

As provided, in the expanded state, the 3M Cold Shrink QT-III Silicone Rubber Skirted Termination Kit 7673-S-8 & 7673-S-10 Series have a 3 year shelf life from date of manufacture when stored in a humidity controlled storage (50°F/10°C to 80°F/27°C and <75% relative humidity).

Availability

Pease contact your local distributor; available from 3M.com/electrical [Where to Buy] or call 1.800.245.3573.

3M, Scotch-Seal and Scotch are trademarks of 3M Company.

Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product, which are not contained in 3M's current publications, or any contrary statements contained on your purchase order, shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

Warranty; Limited Remedy; Limited Liability

This product will be free from defects in material and manufacture at the time of purchase. 3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. Except where prohibited by law, 3M will not be liable for any direct, indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.



Electrical Markets Division 6801 River Place Blvd. Austin, TX 78726-9000 800.245.3573 FAX: 800.245.0329 www.3M.com/electrical

Please recycle
© 3M 2016 All rights reserved
78-8141-4841-3 Rev D