

3M[™] High-Speed Cable Assembly Solutions

High-speed cable assemblies are essential for the efficient operation of systems that process large volumes of data. For high-performance computing, routers, storage and switches, 3M has the cabling solutions you need to connect devices with the latest industry standard physical interfaces.

- Utilizing 3M™ Twin Axial Cable technology: Highly routable, foldable, flexible
- Thin, low-profile ribbon cable allows more routing options within a case, and enables many packaging configurations
- Foldable ribbon construction allows for extremely tight bend radii with minimal performance impact

Internal Cable Assemblies

3M[™] SlimLine Twin Axial Cable Assembly (SFF-8654)

- x4 and x8 configurations
- SFF-8654 straight and right angle
- Signal wire size 30AWG and 31AWG
- Standard lengths 0.5 m, 0.75 m, and 1 m
- PCIe (85 ohm) and SAS (100 ohm) applications
- Custom folded assemblies available

Internal miniSAS Cable Assembly, Series 8F36 / 8F68 / 8S36

- x4 (36-position) and x8 (68-position) configurations
- SFF-8087 straight (contact 3M regarding right angle and side exit)
- SFF-8087 to 7-position SATA fan-out assemblies
- Signal wire size 30AWG, available in either silver or tin
- Available with and without sidebands
- SAS (100 ohm) applications
- SFF-8087 hybrid to SATA
- Standard lengths available up to 1 m
- Custom folded assemblies available





Internal miniSAS HD Cable Assembly, Series 8US4 / 8UH4

- x4 configuration
- SFF-8643 straight short body,
- straight, and right angle • SFF-8643 hybrid to SFF-8087
- Signal wire size 30AWG
- Signal wire size SOAWG
- Available with or without sidebands
 Available with mesh sleeve
- SAS (100 ohm) applications (contact 3M regarding
- PCIe 85 ohm applications) • Standard lengths available up to 1 m
- Custom lengths available

Internal SATA Cable Assembly, Series 5602

- 7-position configuration
- Straight and right angle with either passive or active latch
- Signal wire size 30AWG
- SATA (100 ohm) applications
- Standard lengths available up to 1 m

Internal PCI Express Extender and Jumper Cable Assemblies, Series 8K

- x4, x8 and x16 configurations
- Signal wire size 30AWG
- Includes aux signals
- PCIe (85 ohm) applications
- Standard lengths 0.25 m and 0.5 m





Product specifications:

PD-0352 / 78-5102-0352-9

• Data sheet / Customer drawing:

External Cable Assemblies

External QSFP28 Cable

- Assembly, Series 9Q

 IEEE 802.3bj and SFF-8665,
- -8661, -8662 • Tested at Open Network Systems
- Interoperability PlugFest (UNH IOL)
 Signal wire size 30AWG and 26AWG
- Signal wire size 30AwG and 26AWG
 Standard lengths available up to 4 m
- 100G Ethernet applications
- Custom EEPROM mapping available
- QSFP28 (100G) to 4xSFP28 (25G) break out assemblies available
- QSFP28 (100G) to 2xQSFP28 (50G) Y-cable assemblies available

External QSFP+ Cable Assembly, Series 9Q

- SFF-8436
- Signal wire size 30AWG
- Standard lengths available up to 3 m
- 40G Ethernet applications
- InfiniBand DDR (4×5Gbps), QDR (4×10Gbps) and FDR (4×14Gbps) applications
- Custom EEPROM mapping available

External miniSAS Cable Assembly, Series 8G26

- x4 configuration
- SFF-8088
- Signal wire size 30AWG and 28AWG
- SAS (100 ohm) applications
- Various keying options and custom cable lengths available
- Standard lengths available up to 6 m

3M[™] 400G QSFP-DD Direct Attach Copper Cable Assemblies, 9V Series

- Delivers aggregate data bandwidth up to 400 Gbps (8x 50Gbps) with passive copper assemblies:
- Up to 2 m with 30 AWG
 2 to 3.25 m, 3.5* meter
- with 26 AWG
- Designed to meet the following industry-standard protocols:
- QSFP-DD MSA; IEEE 802.3cd
 400G Ethernet applications
- Custom EEPROM mapping available
- Custom EEPROM mapping available
 RoHS 2011/65/EU compliant**

External SFP28 Cable Assembly, Series: 1422

- IEEE 802.3by and SFF-8431
- Tested at Open Network Systems Interoperability PlugFest (UNH IOL)
- Signal wire size 30AWG and 26AWG
- Standard lengths available up to 4 m
- 25G Ethernet applications
- Available in black (red or blue PVC jacket options available)
- Custom EEPROM mapping available

External SFP+ Cable Assembly, Series: 1410 / 1412

- SFF-8431 and SFF-8432
- Signal wire size 30AWG and 26AWG
- Standard lengths available up to 7 m
- 10G Ethernet applications
- Available in black, red or blue PVC jacket options
- Custom EEPROM mapping available
- $^{*\,3.25\,meter\,cable\,assembly\,meets\,IEEE802.3cd\,and\,3.5\,meter\,assembly\,meets\,IEEE802.3cd\,Channel\,Operating\,Margin\,(COM).$
- **RoHS 2011/65/EU Compliant: the product or part ("Product") does not contain any of the substances in excess of the maximum concentration values ("MCVs") in EU Directive 2002/95/EC, as amended by Commission Decision 2005/618/EC, and/or in the recast RoHS Directive 2011/65/EU, Annex II, unless the substance is in an application that is exempt under the RoHS Directive 2002/95/EC, as amended, and/or under Annex III or Annex IV to the recast RoHS Directive 2011/65/EU. The MCVs are by weight in homogeneous materials.

Regulatory: For regulatory information about this product, contact your 3M representative.

Technical Information: The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

Product Use: Many factors beyond 3M's control and uniquely within user's control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty, Limited Remedy, and Disclaimer: Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OR TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.



Electronics Materials Solutions Division 3M Center, Building 224-3N-11 St. Paul, MN 55144-1000 USA

Web www.3Mhighspeed.com Phone 1-800-810-8513 Please recycle. Printed in USA. ©3M 2020. All rights reserved. Issued: 9/20 16435HB 80-4000-7021-7 Rev. A

3M is a trademark of 3M.

Used under license by 3M subsidiaries and affiliates.







