

Product Description

3M™ FASARA™ Glass Finishes (the “Products”) are decorative glass and window films available in over 100 designs. These decorative Products can be used in vertical applications in commercial buildings to control both light and privacy through a building’s interior glass, including the interior of an outside glass wall (the “Interior Applications”). The current Product line can be found in the *3M™ FASARA™ Glass Finishes Product Catalog* (the “Catalog”).

Featured Benefits

Expected Performance Life is 5 to 20 years for indoor, vertical applications on non-perimeter glass, depending on the design.

Product Characteristics

The values in this table are typical, and are based on test data deemed reliable but are not warranted.

| Characteristic | | Value |
|--------------------|---|--|
| Material | Film | Polyester* |
| | Adhesive | Pressure-sensitive acrylic, permanent |
| | Release Liner | Silicone-coated polyester. |
| Thickness | Film + Adhesive | 3.3 mils (85 microns) (approx.) See Table A. |
| | Release Liner | 1 mil (25 microns) |
| Maximum Roll Size | Standard | 50 in. x 98.4 ft. (1270mm x 30m) |
| | Cloud, Mat Crystal-i, Milky Milky, Oslo, Fine Crystal, Frost Walnut, Frost Walnut Smoke, Pyrgos | 60 in. x 98.4 ft. (1524mm x 30m) |
| | Milky White | 60 in. x 196.8 ft. (1524mm x 60m) |
| Maximum Sheet Size | Illumina Silky-W | 50 in. x 116 in. (1270mm x 2950mm) 60 in. x 116 in. (1524mm x 2950mm) |
| | Illumina Silky-S | 50 in. x 78 in. (1270mm x 1980mm) 60 in. x 78 in. (1524mm x 1980mm) |
| Maximum Weight | | 35 lb. (16 kg) (approx.) for a 50 in. x 98.4 ft. roll |

* Exterior Mat Crystal 2 and Milky Crystal contain Polyester and Polyvinyl Chloride.

Product Performance

The values in this table are typical, and are based on test data deemed reliable but are not warranted.

| Characteristics | Value |
|--------------------------------------|---|
| Adhesion 24 hours after application* | Glass: 1.6 lb/in. (7.0 N/25 mm) |
| Tensile Strength | 45 - 90 lb/in. (200 - 400 N/25 mm) |
| Fire Resistance | When used in Interior Applications on glass, all patterns have the National Fire Protection Association Class A (as defined in NFPA 101 “Life Safety Code” Test Method ASTM E84). |
| Heat Transmission Coefficient | 6 W/m ² K, all products |
| UV Blocking | Blocks at least 99% of UV light to reduce the discoloring (fading caused by sunlight) of furniture and other items. |

* Test specimens were applied to the substrate and conditioned at 68 F (20 C), then peel tested at 180 degree at a tensile speed of 12 inches (300 mm) per minute.

Optical Performance Characteristics Definitions

Shading coefficient: Measurement of sun-blocking effect, based on the percentage of sunlight passing through the Product applied to transparent glass, where the value “1” represents the amount of sunlight passing through 0.12 inch (3mm) thick transparent glass with no film applied. Lower shading coefficient numbers represent greater shading effect.

Transmittance, reflectance and absorbance: Measurement of the respective rates at which UV (ultraviolet), brightness (visible light), and heat (sunlight) are transmitted, reflected, or absorbed.



Heat transmittance: Measurement of the ease of heat escape caused by a temperature difference between interior and exterior, based on the amount of heat that would escape in 1 hour from a surface area of 10.8 square feet (1m²) when there is a temperature difference of 34°F (1°C).

Table A. Optical Performance Characteristics for All Product Designs

The optical values are calculated as theoretical values and compiled with existing data. In patterned Product designs, the value is an average across the pattern. The values in this table are typical, and are based on test data deemed reliable but are not warranted.

| | Product Design | Thickness Film + adhesive (microns) | Shading Coefficient | Solar Heat (%) | | | Visible Light (%) | | UV (%) |
|------------------|--|-------------------------------------|---------------------|----------------|---------------|------------|-------------------|---------------|---------------|
| | | | | Reflectance | Transmittance | Absorbance | Reflectance | Transmittance | Transmittance |
| 2017 New Designs | Frost Walnut (SH2PTFW) | 84 | 0.96 | 8 | 80 | 12 | 9 | 87 | 0.1 |
| | String (SH2PTST) | 77 | 0.88 | 17 | 74 | 9 | 22 | 74 | 0 |
| | Buckram (SH2FGBU) | 79 | 0.86 | 12 | 69 | 19 | 14 | 69 | 0 |
| | Fine String (SH2PTFS) | 76 | 0.86 | 13 | 69 | 18 | 16 | 69 | 0 |
| | Weave pearl (SH2EMWP) | 90 | 0.84 | 12 | 66 | 22 | 15 | 66 | 0 |
| | Grain champagne gold (SH2CSGC) | 78 | 0.78 | 22 | 64 | 14 | 24 | 64 | 0 |
| | Grain silver (SH2CSGS) | 76 | 0.76 | 29 | 64 | 7 | 33 | 64 | 0 |
| | Sensai Linen champagne gold (SH2CSSEC) | 79 | 0.77 | 22 | 63 | 15 | 25 | 63 | 0 |
| | Safari (SH2PTSR) | 85 | 0.81 | 13 | 63 | 24 | 16 | 63 | 0 |
| | Canvas champagne gold (SH2CSCVC) | 78 | 0.74 | 25 | 61 | 14 | 29 | 61 | 0 |
| | Wind (SH2PTWD) | 88 | 0.81 | 11 | 61 | 28 | 13 | 61 | 0 |
| | Fusion pearl (SH2CSFP) | 78 | 0.78 | 16 | 60 | 24 | 21 | 60 | 0.1 |
| | Diamond (SH2FGDM) | 80 | 0.76 | 16 | 58 | 26 | 20 | 58 | 0 |
| | Cut Glass pearl (SH2CSCP) | 78 | 0.76 | 16 | 58 | 26 | 18 | 58 | 0.1 |
| | Straight Washi (SH2FGSW) | 90 | 0.77 | 14 | 57 | 29 | 18 | 57 | 0 |
| | Burlap (SH2FGBL) | 75 | 0.75 | 15 | 57 | 28 | 20 | 57 | 0 |
| | Sensai Linen (SH2FGSE) | 74 | 0.75 | 16 | 56 | 28 | 21 | 56 | 0 |
| | Burlap champagne gold (SH2CSBLC) | 79 | 0.71 | 23 | 56 | 21 | 26 | 56 | 0 |
| | Cut Glass (SH2CSC) | 76 | 0.75 | 15 | 55 | 30 | 20 | 55 | 0.1 |
| | Grid reflect (SH2SIGDR) | 76 | 0.7 | 25 | 55 | 20 | 30 | 55 | 0 |
| | Buckram pearl + gray (SH2FGBUG) | 77 | 0.76 | 11 | 55 | 34 | 12 | 55 | 0 |
| | String Reverse (SH2PTSTR) | 78 | 0.74 | 16 | 54 | 30 | 21 | 54 | 0 |
| | Illumina Silky W (SH2SSIM-W) | 78 | 0.7 | 29 | 57 | 14 | 36 | 54 | 0.1 |
| | Grid (SH2FGGD) | 79 | 0.72 | 18 | 53 | 29 | 23 | 53 | 0 |

3M™ FASARA™ Glass Finishes

| | Product Design | Thickness Film + adhesive (microns) | Shading Coefficient | Solar Heat (%) | | | Visible Light (%) | | UV (%) |
|---------------------|-----------------------------------|-------------------------------------|---------------------|----------------|---------------|------------|-------------------|---------------|---------------|
| | | | | Reflectance | Transmittance | Absorbance | Reflectance | Transmittance | Transmittance |
| 2017 New Designs | Weave pearl + dark gray (SH2EMWG) | 94 | 0.73 | 10 | 50 | 40 | 10 | 50 | 0 |
| | Frost Walnut smoke (SH2PTFWS) | 87 | 0.75 | 7 | 50 | 43 | 7 | 49 | 0 |
| | Illumina Silky S (SH2SSIM-S) | 78 | 0.66 | 32 | 53 | 16 | 40 | 48 | 0.1 |
| | Canvas (SH2FGCV) | 77 | 0.66 | 21 | 47 | 33 | 28 | 47 | 0 |
| | Cut Glass silver (SH2CSCS) | 77 | 0.63 | 26 | 46 | 27 | 30 | 46 | 0 |
| | Pyrgos (SH2PTPG) | 88 | 0.66 | 19 | 45 | 36 | 25 | 43 | 0 |
| | Diamond reflect (SH2SIDR) | 77 | 0.56 | 37 | 43 | 20 | 43 | 43 | 0 |
| | Chain Mesh reflect (SH2SICMR) | 76 | 0.46 | 51 | 36 | 14 | 59 | 36 | 0 |
| | Diamond Ghost reflect (SH2SIDGR) | 77 | 0.36 | 60 | 27 | 14 | 69 | 27 | 0 |
| Gradation | Sabrina (SH2FGSB) | 90 | 0.93 | 9 | 77 | 14 | 10 | 83 | 0 |
| | Aerina (SH2FGAR) | 81 | 0.91 | 12 | 76 | 13 | 13 | 79 | 0 |
| | Cloud (SH2FGCL) | 90 | 0.87 | 11 | 70 | 19 | 13 | 73 | 0.1 |
| | Illumina Alpha (SH4FGMIX) | 153 | 0.8 | 16 | 63 | 21 | 22 | 65 | 0.4 |
| | Lontano (SH2FGLO) | 81 | 0.74 | 20 | 57 | 23 | 22 | 61 | 0 |
| | Tsurugi (SH2FGTG) | 81 | 0.75 | 19 | 58 | 23 | 21 | 61 | 0 |
| | Venetian (SH2FGVN) | 85 | 0.73 | 18 | 55 | 27 | 23 | 54 | 0 |
| | Illumina Silver (SH2SIIM) | 77 | 0.44 | 50 | 33 | 17 | 59 | 36 | 0 |
| | Robe (SH2FGRB) | 85 | 0.59 | 23 | 39 | 38 | 31 | 35 | 0 |
| | Illumina Black (SH2BKIM) | 79 | 0.52 | 6 | 19 | 75 | 6 | 20 | 0 |
| Stripe | Seattle (SH2DGST) | 81 | 0.85 | 16 | 70 | 14 | 22 | 74 | 0 |
| | Seattle Fine (SH2DGST-F) | 80 | 0.85 | 16 | 71 | 13 | 25 | 68 | 0 |
| | Arpa (SH2FGAP) | 79 | 0.78 | 17 | 61 | 22 | 22 | 67 | 0.1 |
| | Shutie (SH2FGST) | 81 | 0.77 | 17 | 60 | 24 | 22 | 59 | 0 |
| | Arpa Crystal (SH2APCR) | 81 | 0.78 | 13 | 59 | 28 | 17 | 58 | 0 |
| | Shutie Black (SH2BKST) | 81 | 0.7 | 21 | 53 | 26 | 29 | 51 | 0 |
| | Fine (SH2FGFN) | 81 | 0.65 | 22 | 46 | 32 | 27 | 48 | 0 |
| | Arpa Black (SH2BKAP) | 81 | 0.54 | 8 | 25 | 67 | 8 | 22 | 0 |
| | Nokto (SH2SCSNK) | 81 | 0.44 | 7 | 12 | 81 | 7 | 13 | 0 |
| | Radius (SH2CSRDR) | 81 | 0.4 | 7 | 7 | 86 | 7 | 6 | 0 |
| Border / Horizontal | Leise (SH2FGLS) | 81 | 0.96 | 9 | 81 | 11 | 9 | 88 | 0 |
| | Lattice g (SH2FGLT) | 79 | 0.8 | 13 | 62 | 26 | 14 | 60 | 0 |
| | Pixela (SH2FGPX) | 81 | 0.78 | 16 | 62 | 22 | 18 | 60 | 0 |
| | Slat g (SH2FGSL-G) | 83 | 0.77 | 14 | 58 | 28 | 16 | 56 | 0 |
| | Paracell (SH2FGPR) | 80 | 0.71 | 17 | 53 | 30 | 20 | 50 | 0 |
| | Lattice (SH2FGLT-G) | 84 | 0.6 | 22 | 41 | 37 | 28 | 36 | 0 |
| | Slat (SH2FGSL) | 88 | 0.6 | 22 | 41 | 37 | 28 | 36 | 0 |

3M™ FASARA™ Glass Finishes

| | Product Design | Thickness Film + adhesive (microns) | Shading Coefficient | Solar Heat (%) | | | Visible Light (%) | | UV (%) |
|------------------------------------|-------------------------|-------------------------------------|---------------------|----------------|---------------|------------|-------------------|---------------|---------------|
| | | | | Reflectance | Transmittance | Absorbance | Reflectance | Transmittance | Transmittance |
| Prism / Dot | Aura 9 (SH2PCA9) | 81 | 0.96 | 8 | 89 | 3 | 8 | 87 | 0 |
| | KANON (SH2FGKN) | 79 | 0.88 | 13 | 73 | 14 | 14 | 78 | 0 |
| | Vista (SH2FGVI) | 81 | 0.83 | 15 | 67 | 18 | 17 | 72 | 0 |
| | SHIZUKU (SH2FGSK) | 81 | 0.84 | 13 | 68 | 19 | 16 | 71 | 0 |
| | Cielo (SH2FGCE) | 81 | 0.74 | 19 | 58 | 23 | 26 | 56 | 0 |
| | Prism Silver (SH2CSPS) | 78 | 0.64 | 28 | 49 | 24 | 31 | 53 | 0 |
| | Luna 6 (SH2PCL6) | 76 | 0.68 | 17 | 48 | 34 | 22 | 46 | 0 |
| | Prism Noir (SH2CSPN) | 78 | 0.67 | 7 | 42 | 51 | 7 | 42 | 0 |
| | Luna 9 (SH2PCL9) | 83 | 0.63 | 19 | 43 | 39 | 24 | 39 | 0 |
| | Astral Silver (SH2CSAS) | 82 | 0.42 | 44 | 28 | 28 | 51 | 30 | 0 |
| Fabric/Japan Paper | YAMATO (SH2PTYA) | 89 | 0.89 | 12 | 74 | 14 | 15 | 79 | 0 |
| | RIKYU (SH2PTRK) | 103 | 0.86 | 7 | 67 | 26 | 8 | 72 | 0 |
| | SAGANO (SH2PTSA2) | 89 | 0.83 | 14 | 66 | 20 | 18 | 68 | 0 |
| | Linen (SH2FGLN) | 78 | 0.79 | 17 | 64 | 19 | 23 | 65 | 0 |
| | Linen Crystal (SH2LNCR) | 81 | 0.81 | 13 | 62 | 25 | 17 | 63 | 0 |
| | Altair (SH2FGAT) | 86 | 0.77 | 17 | 60 | 22 | 23 | 60 | 0 |
| | Vega (SH2FGVG) | 86 | 0.77 | 16 | 60 | 24 | 21 | 60 | 0 |
| | SAFU (SH2PTSF) | 95 | 0.72 | 20 | 54 | 26 | 27 | 54 | 0 |
| | KEN-UN (SH2PTKU) | 97 | 0.7 | 21 | 53 | 26 | 28 | 51 | 0 |
| | Frost / Matte | Mat Crystal 2 (SH2MACRX2) | 126 | 0.95 | 7 | 79 | 14 | 8 | 86 |
| Mat Crystal-i (SH2MACR-I) | | 95 | 0.94 | 8 | 78 | 14 | 9 | 85 | 0.1 |
| LAUSANNE (SH2EMLA) | | 113 | 0.94 | 8 | 78 | 14 | 9 | 84 | 0.1 |
| Fine Crystal (SH2FNCR) | | 113 | 0.94 | 8 | 78 | 14 | 9 | 84 | 0.1 |
| OSLO (SH2EMOS) | | 119 | 0.92 | 8 | 76 | 16 | 9 | 83 | 0.1 |
| OSLO-P (SH2EMOS-P) | | 119 | 0.92 | 8 | 76 | 16 | 9 | 83 | 0.1 |
| Mare (SH2FGMR) | | 90 | 0.91 | 9 | 74 | 18 | 10 | 78 | 0 |
| Milky White (Milano) (SH2MAML) | | 77 | 0.75 | 17 | 57 | 26 | 21 | 59 | 0 |
| Glace (SH2MAGL) | | 85 | 0.77 | 14 | 58 | 28 | 18 | 56 | 0 |
| ESSEN (SH2EMES) | | 120 | 0.67 | 23 | 50 | 27 | 26 | 55 | 0.1 |
| CHAMONIX (SH2EMCH) | | 120 | 0.67 | 26 | 51 | 23 | 35 | 47 | 0 |
| Luce (SH2FGLU) | | 85 | 0.59 | 23 | 39 | 38 | 31 | 34 | 0 |
| Milky Milky (San Marino) (SH2MAMM) | | 105 | 0.44 | 34 | 25 | 41 | 43 | 21 | 0 |
| Milky Crystal (SH2MLCRX) | | 126 | 0.4 | 31 | 18 | 51 | 42 | 19 | 0 |
| Opaque White (SH2MAOW) | | 142 | 0.3 | 46 | 13 | 41 | 57 | 10 | 0 |
| Opaque Black (SH2BKOP) | | 79 | 0.39 | 5 | 1 | 94 | 5 | 0 | 0 |
| Silver 1 (RE1SAIR) | | 74 | 0.08 | 78 | 0 | 21 | 91 | 0 | 0 |
| Transparent Glass Substrate * | - | 1.00 | 8 | 86 | 6 | 8 | 90 | 71 | |

* All product designs were applied to a 3 mm transparent glass substrate to calculate the values in this table.

Product Use

Interior Use: Most Products are designed for application to building interior glass and building interior perimeter glass, meaning the interior of an outside glass wall.

Exterior Use: Illumina Alpha, Mat Crystal 2, and Milky Crystal are the only Products designed for use on exterior glass.

Anti-reflection effect: When used in Exterior Applications, the Mat Crystal 2 and Milky Crystal Product designs scatter sunlight to reduce reflected light.

Application and Removal Guidelines

Avoid scratching, denting, or stretching the Product during installation. The values in these tables are typical, and are based on test data deemed reliable but are not warranted. See the 3M FASARA Glass Finishes Installation Guide for additional information.

| Characteristic | Value |
|---|---|
| Application Surface Type | Flat |
| Application Surface Material | Use only glass substrates. Illumina-P (SH2FGIM-P) and OSLO-P (SH2EMOS-P) product designs are for use on plastic substrates on a user test and approve basis. |
| Application Location | Mat Crystal 2, Milky Crystal, and Illumina Alpha Product designs can be applied to Exterior Applications. All other Product designs are only for Interior Applications. |
| Application Temperature | 54°F - 100°F (12°C - 38°C) air and application surface |
| Application Method | Wet application |
| Applied Product Shrinkage | Nominal |
| Applied Product Exposure Temperature | Exterior Applications: -40°F - +149°F (-40°C - +65°C) Interior Applications: maximum 176°F (+80°C) |
| High Humidity Environments | Products are not recommended for Interior Applications where condensation consistently occurs. |
| Product Removal | Low heat or 3M Adhesive Remover Citrus Base and scraper |

NOTE: Removing the Product too quickly can result in excessive adhesive left on the substrate. If necessary, heat a small section of the film with a heat gun to soften the adhesive, peel back slowly, then heat and remove the next section.

Processing Options

Processing of the Product is on a user test and approve basis only. The user is responsible for results in all processing applications.

Printing

The Products are not designed for surface printing and have various surface textures. Printing is on a user test and approve basis only. No warranty is made for the quality or durability of printed Product.

Cutting

Electronic cutting, weeding and application tape with the Product is on a user test and approve basis. The user should consider the following: (1) the type of liner used for the Product is not intended for electronic cutting; (2) there is currently no recommended application tape that adheres properly to the face of the Product to hold cut shapes in place.

Shelf Life and Storage

Shelf Life

Apply the Product within 1 year of the date of purchase. The storage conditions specified in this document must be maintained for full shelf life.

Storage Conditions

- 40°F - 90°F (4°C - 32°C)
- Away from direct sunlight and high humidity
- Clean, dry area
- Original container with end caps, in the plastic sleeve, stored horizontally, a maximum of 6 cartons high

Cleaning and Maintenance

NOTE: The Product may be cleaned beginning 30 days after installation.

Regular cleaning will help maintain the Product's appearance. Use only clean, nick-free tools and wipe gently only in one direction. Do not use ammonia, chlorine, or organic-based cleaning products, polishing or cleaning compound, sponges, brushes or electric polishing equipment.

- If there is dust and grit, wipe it off with a soft, damp cloth.
- If it is soiled, but not gritty, use water and squeegee.
- If there is heavier soil, use a mild liquid detergent and water solution, then clear water, and wipe gently with a cloth wipe.

Health and Safety

CAUTION

When handling any chemical products, read the manufacturers' container labels and the Safety Data Sheets (SDS) for important health, safety and environmental information. To obtain SDS sheets for 3M products go to 3M.com/SDS, or by mail or in case of an emergency, call 1-800-364-3577 or 1-651-737-6501.

When using any equipment, always follow the manufacturers' instructions for safe operation.

WARNING

To reduce the risks of personal injury and/or property damage associated with glass breakage:

A glass surface covered by a film with areas of high opacity or dark-colored ink will absorb more heat than other glass surfaces when exposed to sunlight. Heat absorption can create thermal expansion that could result in glass breakage or cracking. Do not use a film with areas of high opacity or dark-colored ink on glass surfaces with significant exposure to sunlight.

Technical Information

Technical information and data, recommendations, and other statements provided by 3M are based on information, tests, or experience which 3M believes to be reliable, but the accuracy or completeness of such information is not guaranteed. Such technical information and data are intended for persons with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. The typical values shown should not be used for the purpose of specification limits. If you have questions about this Product, contact the Technical Service helpline at 1-888-650-3497.

LEEDv4 Credits

This section describes some of the options for acquiring LEED credits using 3M™ Glass Finishes.

NOTE: Each application is different. It is the sole responsibility of the end user to evaluate and determine whether LEED credits can be acquired.

ID+C MR Credit, Interiors Life-Cycle Impact Reduction

- Option 1: Interior Reuse - Product can be used to refinish salvaged, refurbished, or reused building materials

ID+C, BD+C EQ Credit, Low-Emitting Materials

- Product has been tested to and is in compliance with the General Emissions Evaluation (California Department of Public Health (CDPH) Standard Method V1.1-2010)

ID+C, BD+C EQ Credit, Daylight

- Product can be used to enable daylight in enclosed spaces

BD+C MR Credit, Building Life-Cycle Impact Reduction

- Option 3: Building and Material Reuse - Product can be used to refinish salvaged, refurbished, or reused building materials

O+M MR Credit, Purchasing - Facility Maintenance and Renovation

- Product can be used to refinish salvaged, refurbished, or reused building materials
- Product has been tested to and is in compliance with the General Emissions Evaluation (California Department of Public Health (CDPH) Standard Method V1.1-2010)

BUILDING PRODUCT DISCLOSURE AND OPTIMIZATION INFORMATION

Environmental Product Declaration (EPD) or Life Cycle Analysis (LCA)

EPD and/or LCA information not available.

Raw Material Source and Extraction Reporting

Raw Material source and extraction information for this product is considered to be 3M confidential and is therefore not available.

Extended Producer Responsibility

Take-back or recycling program for this product is not available.

Bio-based Materials

Product have not been tested to ASTM D6866.

Wood Products

Product does not contain wood-based materials.

Materials Reuse

Product can be used to refinish salvaged, refurbished, or reused building materials.

Recycled Content

Product does not contain pre- or post-consumer recycled content.

WARRANTY

Products

3M FASARA Glass Finishes (the “Product(s)”) are decorative films for use in vertical interior glass applications in commercial buildings (“Interior Applications”). Three of the Product designs can be used in vertical applications on the exterior of an outside glass wall (the “Exterior Applications”).

3M Basic Product Warranty

The Product(s) specified in this document are warranted to be free of defects in materials and manufacture (“3M Basic Product Warranty”) on the date of shipment (“Warranty Period”) by 3M or its authorized distributor.

Limited Warranty

- For Products used in the United States, 3M makes the following warranty (the “3M Limited Warranty”) for the applicable time period stated below (“Warranty Period”), which will begin on the earlier of: (a) Product installation date; or (b) six months after 3M’s Product shipment date.

The Product will have no significant discoloration, cracking or other similar visual defects for the applicable time period below:

| Application | | Warranty Period - Vertical Applications ¹ |
|--|---|--|
| Interior Applications - 2017 New Designs | Excluding building perimeter glass | 3 years |
| | Building perimeter glass | 1 year |
| Interior Applications (including Illumina Silky-W & -S) | Excluding building perimeter glass | 5 years |
| | Building perimeter glass (except Illumina Black (SH2BKIM) and Opaque Black (SH2BKOP)) | 3 years |
| Interior Applications (not recommended for building perimeter glass) | Illumina Black (SH2BKIM) | 2 years |
| | Opaque Black (SH2BKOP) | |
| Exterior Applications | Mat Crystal 2 (SH2MACRX2) Milky Crystal (SH2MLCRX) Illumina Alpha (SH4FGMIX) | 3 years |
| Plastic application surfaces | | 3M Basic Product Warranty only (see above) |

Non-vertical applications are not warranted.

- For a buyer’s convenience, 3M may provide engineering or technical information, recommendations, installation instructions, and other information or materials relating to Product (“Other Product Information”), but 3M makes only the 3M Basic Product Warranty and the 3M Limited Warranty and does not warrant any Other Product Information.
- 3M has no obligation under the 3M Basic Product Warranty or the 3M Limited Warranty as to Product that has been: (a) modified, altered or processed in any manner; (b) stored, applied, installed, or used in a manner other than that 3M recommends in this document and in all Other Product Information; (c) damaged through contact with a person or thing, misuse, accident, neglect, or other action by anyone other than 3M; (d) improperly installed, including, without limitation, installation after the expiration the Product’s shelf life or installation without proper surface preparation, (e) exposed to excessive heat, humidity, dirt or UV light, or (f) installed in a non-vertical application.
- EXCEPT TO THE EXTENT PROHIBITED BY APPLICABLE LAW, THE 3M BASIC PRODUCT WARRANTY AND 3M LIMITED WARRANTY ARE MADE IN LIEU OF ALL OTHER WARRANTIES, RIGHTS OR CONDITIONS, EXPRESS OR IMPLIED, STATUTORY OR OTHERWISE, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY, SATISFACTORY QUALITY, FITNESS FOR A PARTICULAR PURPOSE AND THOSE ARISING FROM A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. THE BUYER IS RESPONSIBLE FOR DETERMINING IF A PRODUCT IS SUITABLE FOR ITS PARTICULAR PURPOSE AND ITS APPLICATION METHODS.
- 3M must receive any 3M Basic Product Warranty or 3M Limited Warranty claim in writing no later than 10 business days after (a) the end of the Warranty Period or (b) the discovery of the 3M Warranty claim, whichever is earlier.

Limited Remedy

IF ANY PRODUCT IS PROVEN NOT TO HAVE MET THE 3M BASIC PRODUCT WARRANTY OR THE 3M LIMITED WARRANTY DURING THE WARRANTY PERIOD, THEN THE BUYER'S EXCLUSIVE REMEDY, AND 3M'S SOLE OBLIGATION, WILL BE, AT 3M'S OPTION, TO REPLACE THE NONCONFORMING PRODUCT OR TO REFUND THE NONCONFORMING PRODUCT'S PURCHASE PRICE.

No Extension of Warranty

In the case of an approved warranty claim, the replacement Product will carry only the remaining term of the original warranty period.

Limitation of Liability

3M WILL NOT UNDER ANY CIRCUMSTANCES BE LIABLE TO A BUYER FOR DIRECT (other than the Limited Remedy stated above), SPECIAL, INCIDENTAL, INDIRECT OR CONSEQUENTIAL DAMAGES (INCLUDING, WITHOUT LIMITATION, LOSS OF PROFITS) IN ANY WAY RELATED TO THE PRODUCT, THE TECH DATA SHEET OR OTHER PRODUCT INFORMATION, REGARDLESS OF THE LEGAL OR EQUITABLE THEORY ON WHICH SUCH DAMAGES ARE SOUGHT.

Commercial Solutions

3M Center, Building 220-12E-04
St. Paul, MN 55144

1-800-650-3497
3M.com/AMD

© 3M 2017. All rights reserved.

3M is a trademark of 3M. Used under license in Canada.
All other trademarks are property of their respective owners.
Please recycle. Revision K, August 2017

