



# Blocks Flame, Builds Confidence

## 3M™ Flame Barrier FRB Series

The 3M™ Flame Barrier FRB Series is flexible insulation for OEM electrical flame barrier applications. The FRB Series products are made primarily of inorganic materials that are intrinsically flame retardant with good dielectric strength.

### The FRB Series has six product families:

- FRB-NT Series (natural-color, densified barrier)
- FRB-NC Series (natural-color, undensified barrier)
- FRB-WT Series (white-coated, densified barrier)
- FRB-BK Series (black-coated, densified barrier)
- FRB-NT Laminate Series (FRB-NT/Polyester/FRB-NT laminate barrier)
- FRB-NC Laminate Series (FRB-NC/Polyester/FRB-NC laminate barrier)

### The key features of these products are:

- An inorganic-based, halogen-free\* material (per IEC 61249-2-21 standard)
- Base material with UL 94 5VA flame rating (five times more severe flame than V-0 test method)
- Excellent ignitability resistance
- Excellent arc and track resistance
- Good dielectric strength, made even better when densified or laminated to polyester
- Good rated thermal index of 130°C for base material (tested only for FRB-NT Series)
- Low outgassing for base material (tested only for FRB-NT Series)
- Dimensionally stable (very low moisture absorption and very low shrinkage at high temperature)

- Thin calipers with 5VA flame ratings - saves cost and weight in end-use applications
- Optional increased density for higher dielectric strength, a smoother surface and a more closed cell structure
- Optional white and black flame-retardant coatings for excellent optical and aesthetic results
- Optional laminated product is manufactured with UL Recognized UL 94 VTM-2 PET film
- Good convertibility - material is easily slit, cut, formed and die cut

### How the Flame Barrier FRB Series is different:

- 5VA flame rating is better than aramid, polypropylene & polycarbonate
- 130°C rated thermal index (RTI) rating is better than polypropylene & polycarbonate

### Target flame barrier applications:

- General purpose lighting luminaires (including LED type)
- Electric and hybrid electric vehicles (between batteries, power converters, etc.)
- Appliances (vacuum cleaners, slow cookers, rice cookers, etc.)
- Electrical devices (timers, actuators, switches, etc.)

\*Halogen-free is defined as having less than 900 ppm bromine, less than 900 ppm chlorine, and less than 1500 ppm total bromine and chlorine; other halogens are excluded from this definition. These are levels set forth in certain industry standards, such as International Electrotechnical Commission (IEC) 61249-2-21 standard. This information is 3M's current knowledge and belief, which may be based in whole or in part on information provided by its suppliers.

## 3M™ Flame Barrier FRB-NT Series (natural-color, densified barrier)

Product #	Thickness*		Roll Width (inches)	Roll Length* (yds)	Roll O.D. (inches)	Weight* (Lbs/SqYd)
	(mils)	(mm)				
FRB-NT076	3	0.076	36	265	7.00	0.19
FRB-NT076	3	0.076	36	1090	12.75	0.19
FRB-NT102	4	0.102	36	200	7.00	0.29
FRB-NT102	4	0.102	36	815	12.75	0.29
FRB-NT127	5	0.127	36	155	7.00	0.36
FRB-NT127	5	0.127	36	650	12.75	0.36
FRB-NT178	7	0.178	36	110	7.00	0.49
FRB-NT178	7	0.178	36	465	12.75	0.49
FRB-NT254	10	0.254	36	75	7.00	0.70
FRB-NT254	10	0.254	36	325	12.75	0.70
FRB-NT381	15	0.381	36	50	7.00	1.04
FRB-NT381	15	0.381	36	215	12.75	1.04

The FRB-NT series products are standard flame barriers for general purpose applications. The densified material provides higher dielectric strength, a smoother surface for improved tape adhesion and a closed cell structure.

\*Roll thickness, length and weight are for guideline purposes only, as they can vary by +/- 15%. Product is also available in 8.5"x11", 36"x24" or 36"x36" sheets.

## 3M™ Flame Barrier FRB-NC Series (natural-color, undensified barrier)

Product #	Thickness*		Roll Width (inches)	Roll Length* (yds)	Roll O.D. (inches)	Weight* (Lbs/SqYd)
	(mils)	(mm)				
FRB-NC127	5	0.127	36	160	7.00	0.19
FRB-NC127	5	0.127	36	650	12.75	0.19
FRB-NC178	7	0.178	36	115	7.00	0.29
FRB-NC178	7	0.178	36	465	12.75	0.29
FRB-NC229	9	0.229	36	90	7.00	0.37
FRB-NC229	9	0.229	36	360	12.75	0.37

The 3M™ Flame Barrier FRB-NC series products are lower-cost flame barriers for general purpose applications. The undensified material does not have the improved characteristics of a densified material (see the FRB-NT short description).

## 3M™ Flame Barrier FRB-WT Series (white-coated, densified barrier)

Product #	Thickness*		Roll Width (inches)	Roll Length* (yds)	Roll O.D. (inches)	Weight* (Lbs/SqYd)
	(mils)	(mm)				
FRB-WT145	5.8	0.145	36	135	7.00	0.43
FRB-WT145	5.8	0.145	36	565	12.75	0.43
FRB-WT225	8.8	0.225	36	90	7.00	0.63
FRB-WT225	8.8	0.225	36	370	12.75	0.63

The FRB-WT series products are white-coated flame barriers for lighting and label applications. White coating has 90% reflectivity to maximize the light output of a luminaire. FRB-WT series can also be used as a high-temperature label.

### 3M™ Flame Barrier FRB-BK Series (black-coated, densified barrier)

Product #	Thickness*		Roll Width (inches)	Roll Length* (yds)	Roll O.D. (inches)	Weight* (Lbs/SqYd)
	(mils)	(mm)				
FRB-BK145	5.8	0.145	36	135	7.00	0.38
FRB-BK145	5.8	0.145	36	565	12.75	0.38
FRB-BK225	8.8	0.225	36	90	7.00	0.58
FRB-BK225	8.8	0.225	36	370	12.75	0.58

The FRB-BK series products are black-coated flame barriers for lighting and label applications. Black coating has only 6% reflectivity to minimize light pollution of a luminaire. FRB-BK series can also be used as a high-temperature label.

### 3M™ Flame Barrier FRB-NT Laminate Series (FRB-NT/Polyester/FRB-NT laminate barrier)

Product #	Thickness*		Roll Width (inches)	Roll Length* (yds)	Roll O.D. (inches)	Weight* (Lbs/SqYd)
	(mils)	(mm)				
FRB-NT 3/5/3	11.0	0.279	36	72	7.00	0.72
FRB-NT 3/5/3	11.0	0.279	36	300	12.75	0.72
FRB-NT 5/5/5	15.0	0.381	36	53	7.00	1.05
FRB-NT 5/5/5	15.0	0.381	36	220	12.75	1.05
FRB-NT 5/7.5/5	17.5	0.445	36	45	7.00	1.22
FRB-NT 5/7.5/5	17.5	0.445	36	185	12.75	1.22

The FRB-NT Laminate series products are polyester-reinforced flame barriers for appliance and lighting applications, particularly for formed shapes. The densified laminate provides smoother surface for improved tape adhesion and a closed cell structure.

### 3M™ Flame Barrier FRB-NC Laminate Series (FRB-NC/Polyester/FRB-NC laminate barrier)

Product #	Thickness*		Roll Width (inches)	Roll Length* (yds)	Roll O.D. (inches)	Weight* (Lbs/SqYd)
	(mils)	(mm)				
FRB-NC 5/5/5	15.0	0.381	36	53	7.00	0.72
FRB-NC 5/5/5	15.0	0.381	36	220	12.75	0.72
FRB-NC 5/7.5/5	17.5	0.445	36	45	7.00	0.91
FRB-NC 5/7.5/5	17.5	0.445	36	185	12.75	0.91

The FRB-NC Laminate series products are lower-cost polyester-reinforced flame barriers for appliance and lighting applications, particularly for formed shapes. The undensified material does not have the improved characteristics of a densified material (see the FRN-NT Laminate short description).

\*Roll thickness, length and weight are for guideline purposes only, as they can vary by +/- 15%. Product is also available in 8.5"x11", 36"x24" or 36"x36" sheets.

3M is a trademark of 3M Company.

## Availability

For availability, please contact your 3M sales representative. Contact details are available at [3M.com/electrical](http://3M.com/electrical) [Where to Buy] or call 855 293 6018.

## Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

### **Warranty; Limited Remedy; Limited Liability.**

This product will be free from defects in material and manufacture at the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**



### **Electrical Markets Division**

6801 River Place Blvd.

Austin, TX 78726-9000

855 293 6018

Fax 800 828 9329

[www.3M.com/flexibleinsulation](http://www.3M.com/flexibleinsulation)

Please recycle. Printed in USA.

© 3M 2016. All rights reserved.

80-6016-0658-7B