

3M Commercial Graphics

3M™ Envision™ Translucent Film Series 3730

3M™ Envision™ Translucent Films IJ3730-50, IJ3730-60

3M™ Envision™ Diffuser Films 3735-50, 3735-60



Switch On

Introducing the first graphic films that optimize LED light

3M™ Envision™ Translucent and Diffuser Films

You no longer need to add more LEDs to get the level of brilliance you want. Now you can deliver rich, vibrant signs without hot spots when you use the NEW 3M™ Envision™ Translucent Films and 3M™ Envision™ Diffuser Films. Get great graphics requiring fewer LEDs, using less energy*. The switch to LEDs is on, so lead the way and offer your customers a brilliant solution.

Stay bright

3M technology makes it easy and practical to use LEDs. Get the same level of brightness using fewer light sources, reducing material and maintenance costs. Get more light transmission for vibrant, rich color.

Go greener

3M™ Envision™ Translucent and Diffuser Films give your customers the opportunity to be more sustainable without sacrificing performance. They'll get an energy-saving, premium product backed by an industry-leading warranty. So they won't just look good — they'll feel good, too. You win. They win. The environment wins.




Make the **switch.**



3M™ Envision™ Translucent Film Series 3730

3M™ Envision™ Translucent Films IJ3730-50, IJ3730-60

3M™ Envision™ Diffuser Films 3735-50, 3735-60



FEATURES

More light transmission

Hiding of light source

Warranted performance

Custom color, standard color and inkjet printable translucents

ADVANTAGES

Efficient use of light sources and energy

Elimination of hot spots

Assurance of finished graphic performance

Increased number of construction options

BENEFITS

Brighter sign faces at lower costs

Uniform illuminance at minimal thickness

Peace of mind

Design and manufacturing flexibility

* Most graphics using film series 3730 on diffuser film 3735-50 provide more light transmission than other graphics using 3M™ Scotchcal™ Translucent Film Series 3630 on 3M™ Diffuser Film 3635-30. See the Product Bulletin 3630/3730 for details.

Request 3M™ Envision™ Translucent and Diffuser Films, visit 3Mgraphics.com/switchon or call 1-800-328-3908.

Let our sales representative show you how much energy you can save!

Warranty and Limitations. The following is made in lieu of all other express or implied warranties, including any implied warranty of merchantability or fitness for a particular purpose. All 3M products are warranted to be free of defects in materials and manufacture at the

time of shipment and to meet the specifications stated in the film or media's Product Bulletin. Also see the Commercial Graphics Warranty Brochure, which gives the terms, additional limitations of the warranty, if any, and limitations of liability.

Stay Informed:



3M

Commercial Graphics
3M Center, Building 220-12E-04
St. Paul, MN 55144 USA
General & Technical Information:
1-800-328-3908

3M Canada
PO Box 5757
London, Ontario
Canada N64 4T1
1-800-265-1840
Fax 519-452-6245

3M México S.A. de C.V.
Av. Santa Fe No. 55
Col. Santa Fe, Del. Alvaro
Obregón
México D.F. 01210
5255-5270-0400
Fax 5255-5270-2277

3M Puerto Rico, Inc.
350 Chardon Ave.
Suite 1100
San Juan, PR 00918
787-620-3000
Fax 787-620-3018

Release A. October 2012.
3M, Scotchcal and Envision are trademarks of 3M.
Please recycle. Printed in USA.
© 3M 2012. All rights reserved.
75-5100-3965-6