

3M™ Reusable Respirator Starter Kits



Comfort
Versatility
Convenience



Respirator Starter Kits

These kits have been designed to provide respiratory protection in a convenient and easy way – an ideal solution to get you started. The kits provide protection for a range of applications, from paint spraying to sanding or welding.

All kits include a pair of 3M™ Earplugs, 3M™ Respirator Cleaning Wipes and a 3M Respiratory Protection Guide. To avoid moisture and contaminant exposure, store the respirator in the handy, sealable storage container.





3M™ Welding Respirator Kit 7528, GP2

Includes a 3M™ Half Face 7500 Series Respirator with special Cool Flow™ valve and soft silicone material. Ideal for working in hot and humid conditions or during prolonged use.

Applications/Hazards:

- + Welding - Fume/ozone
- + Soldering/Brazing - Fume
- + Grinding/Polishing - Metal dust and particles
- + Drilling - Metal particles
- + Metal Pouring - Fume
- + Machining - Oil mist

Kit Includes:

- + 1 x 3M™ Half Face Respirator 7500 Series - Medium
- + 1 x pair of 3M™ Particle & Metal Fume Filters 2128, GP2
- + 4 x 3M™ Respirator Cleaning Wipes 504
- + 1 x 3M™ Skull Screws™ Earplugs P1300, Class 5
- + 1 x 3M™ Respiratory Protection Guide
- + 1 x Handy Storage Container



3M™ Welding Respirator Kit 6228, GP2

Includes a 3M™ Half Face 6000 Series Respirator that is simple and lightweight.

Applications/Hazards:

- + Welding - Fume/ozone
- + Soldering/Brazing - Fume
- + Grinding/Polishing - Metal dust and particles
- + Drilling - Metal particles
- + Metal Pouring - Fume
- + Machining - Oil mist

Kit Includes:

- + 1 x 3M™ Half Face Respirator 6000 Series - Medium
- + 1 x pair of 3M™ Particle & Metal Fume Filters 2128, GP2
- + 4 x 3M™ Respirator Cleaning Wipes 504
- + 1 x 3M™ Skull Screws™ Earplugs P1300, Class 5
- + 1 x 3M™ Respiratory Protection Guide
- + 1 x Handy Storage Container



3M™ Spraying Respirator Kit 7551, A1P2

Includes a 3M™ Half Face 7500 Series Respirator with special Cool Flow™ valve and soft silicone material. Ideal for working in hot and humid conditions or during prolonged use.

Applications/Hazards:

- + Paint Spray - Solvent vapours/mist
- + Pesticide Spray - Organic vapours/mist
- + Chemical Handling - Organic vapours from thinners, adhesives
- + Fibreglassing - Solvent vapours
- + Printing - Solvent vapours
- + Degreasing - Solvent vapours

Kit Includes:

- + 1 x 3M™ Half Face Respirator 7500 Series – Medium
- + 1 x pair of 3M™ Organic Vapour Cartridges 6051, A1
- + 1 x box (5 pairs) of 3M™ Particulate Filters 5925, P2
- + 1 x pair of 3M™ Filter Retainers 501
- + 4 x 3M™ Respirator Cleaning Wipes 504
- + 1 x 3M™ No-Touch™ Foam Earplugs P2000, Class 4
- + 1 x 3M™ Respiratory Protection Guide
- + 1 x Handy Storage Container

3M™ Spraying Respirator Kit 6251, A1P2



Includes a 3M™ Half Face 6000 Series Respirator that is simple and lightweight.

Applications/Hazards:

- + Paint Spray - Solvent vapours/mist
- + Pesticide Spray - Organic vapours/mist
- + Chemical Handling - Organic vapours from thinners, adhesives
- + Fibreglassing - Solvent vapours
- + Printing - Solvent vapours
- + Degreasing - Solvent vapours

Kit Includes:

- + 1 x 3M™ Half Face Respirator 6000 Series – Medium
- + 1 x pair of 3M™ Organic Vapour Cartridges 6051, A1
- + 1 x pair of 3M™ Particulate Filters 5925, P2
- + 1 x pair of 3M™ Filter Retainers 501
- + 4 x 3M™ Respirator Cleaning Wipes 504
- + 1 x 3M™ No-Touch™ Foam Earplugs P2000, Class 4
- + 1 x 3M™ Respiratory Protection Guide
- + 1 x Handy Storage Container

3M™ Multi-Gas Respirator Kit 6259, A1B1E1K1P2



Includes a 3M™ Half Face 6000 Series Respirator that is simple and lightweight.

Applications/Hazards:

Range of vapours and gases including (but not limited to):

- + Chlorine
- + Sulphur Dioxide
- + Solvents (boiling points >65°C)
- + Hydrogen Sulphide
- + Ammonia
- + Hydrogen Chloride

Kit Includes:

- + 1 x 3M™ Half Face Respirator 6000 Series – Medium
- + 1 x pair of 3M™ Multi-Gas Cartridges 6059, A1B1E1K1
- + 1 x pair of 3M™ Particulate Filters 5925, P2
- + 1 x pair of 3M™ Filter Retainers 501
- + 4 x 3M™ Respirator Cleaning Wipes 504
- + 1 x 3M™ No-Touch™ Foam Earplugs P2000, Class 4
- + 1 x 3M™ Respiratory Protection Guide
- + 1 x Handy Storage Container

3M™ Dust/Particle Respirator Kit 6225, P2



Includes a 3M™ Half Face 6000 Series Respirator that is simple and lightweight.

Applications/Hazards:

- + Sanding/Sawing - Wood/plaster dust
- + Lead Paint Removal - Metal fume and/or particles
- + Food Manufacturing - Fine food powders
- + Insulation - Fibreglass particles
- + Drilling/Cutting - Metal/wood/plastic particles
- + Masonry - Stone particles
- + Grinding - Metal dust and particles
- + Powder Coating - Dust

Kit Includes:

- + 1 x 3M™ Half Face Respirator 6000 Series - Medium
- + 1 x pair of 3M™ Particulate Filters 2125, P2
- + 4 x 3M™ Respirator Cleaning Wipes 504
- + 1 x 3M™ No-Touch™ Foam Earplugs P2000, Class 4
- + 1 x 3M™ Respiratory Protection Guide
- + 1 x Handy storage container

For more information about 3M Safety products or solutions please contact us:

AUSTRALIA

TechAssist Helpline 1800 024 464
TechAssist Email techassist@mmm.com
Customer Service 1300 363 565
Website www.3m.com/au/PPESafety

NEW ZEALAND

TechAssist Helpline 0800 364 357
Email anz3msafety@mmm.com
Customer Service 0800 252 627
Website www.3m.com/nz/PPESafety



**Occupational Health
and Environmental
Safety Division**

3M Australia Pty Limited
ABN 90 000 100 096
Building A, 1 Rivett Road
North Ryde NSW 2113

3M New Zealand Limited
94 Apollo Drive
Rosedale
Auckland 0632

© 3M 2012. All rights reserved.
Please recycle.

PSSSP0HE0001215