

3M™ H-700 Series Hard Hats



Lightweight Comfort, Tough Performance

3M™ H-700 Series Hard Hat with Uvicator™ Sensor is the newest addition to the H-700 series hard hat family. This award-winning, lightweight hard hat offers extended comfort and protection, and also features a sensor that changes color as the hard hat is exposed to UV light.

The sun's UV rays can cause a hard hat shell to become brittle and compromise its ability to help protect the wearer. With the Uvicator sensor, wearers know it's time for a replacement when the sensor changes from red to white. The H-700 hard hat with Uvicator sensor is available with a 4-point ratchet suspension.

3M™ H-700 Series Hard Hat with Uvicator™ Sensor

UPC: 10078371655515

Product #: H-702R-UV

With the Uvicator™ Sensor, you'll know when your hard hat has been in the sun too long.

Features and Benefits

All H-700 series hard hats include:


- Low-profile design for stability and balance
- Replaceable brow pad
- Short brim for better upward visibility
- Slots to accommodate 3M's accessories, such as earmuffs, headgear, faceshields and welding helmets
- Compliant when worn in forward and reverse donning positions
- 4-point Ratchet or Pinlock suspension system with height adjustment
- Vented and non-vented models

Typical Applications

- Mining
- Construction Work
- Road Construction
- Forestry
- Oil & Gas
- Heavy and Light Industrial

Made in U.S.A. with
Globally Sourced Materials

NEW



WORN



REPLACE



Colors Available:

Yellow



Green



Blue



Bright Yellow



White



See 3M.com/PPESafety for more product selection.



Experience Full-Shift Comfort with the 3M™ H-700 Series Hard Hat

3M™ H-700 Series Hard Hat is comfortable, tough and lightweight. Designed with a low profile for improved stability and balance, the H-700 series provide comfort and protection from small falling objects striking the top of the hard hat. These hard hats feature accessory slots to accommodate 3M's cap-mounted ear muffs, headgear, faceshields and welding helmets. The non-vented 3M H-700 series hard hat meets the requirements of ANSI/ISEA Z89.1-2009 Type I, Class C, G and E. The vented 3M H-700 series hard hat meets the requirements of ANSI/ISEA Z89.1 Type I, Class C.

3M™ H-700 Series Hard Hat

UPC: 10078371641990

Product #: H-703R




Colors Available:

Red		Orange	
Yellow		Gray	
Blue		Bright Yellow	
Green		Navy Blue	
White		Bright Orange	

Features and Benefits

- Comfortable when worn for extended periods of time
- The 3M™ H-700 Series Hard Hat is available with a 4-point ratchet or pinlock suspension or an optional 6-point strap



Optional 6-point Strap

UPC: 10078371654921

Product #: H-700-S6

Typical Applications

- Heavy and Light Industrial
- Construction Work
- Oil & Gas
- Road Construction
- Forestry
- Mining



Custom Logo Program

The Custom Logo Program for 3M™ H-700 Series Hard Hats makes it easy to imprint a logo on your next hard hat. Visit 3M.com/customlogo to learn more.



Additional Head & Face Products

3M also offers a range of faceshields and headgear. Visit 3M.com/PPESafety to view products.

