



# X-Series Hi-Performance Adhesive Transfer Tape

## XG2105

Technical Data

February, 2013

### X-Series Description

3M™ X-Series Industrial Attachment Tapes offer a variety of performance characteristics and product constructions to support demanding application requirements. This product line provides a range of adhesive transfer and double-coated tapes designed for attachment of paper, corrugated, films, foils, fabric, plastics and metal. Double Coated (DC) tapes provide a backing for improved handling. Adhesive Transfer Tapes (ATT) provide the thinnest bond lines. The 3M™ X-Series Tape System is manufactured in the United States by 3M.

# XG

The X-Series Tape System offers four performance categories enabling quick identification and selection of the appropriate product for the intended application.

- XP - High Performance Acrylic – superior holding power over a range of temperatures.
- XT - High Tack Acrylic Adhesive – excellent initial adhesion for hard-to-stick surfaces.
- XG - General Purpose Acrylic – a clean acrylic adhesive for paper bonding and sensitive applications.**
- XR - Rubber Adhesive – good initial grab and clean removal on many surfaces.

Construction	Products	X-Series Adhesive Transfer Tape XG2105
Adhesive Type:		General Purpose Acrylic
Release Liner:		White Densified Kraft Liner with Red Print
Approximate Thickness:		
Release Liner:		0.003 inches (0.08 mm)
Tape Only:		0.002 inches (0.05 mm)
Tape Color:		Translucent

# 3M™ X-Series General Purpose Transfer Tape

## XG2105

### Typical Physical Properties and Performance Characteristics

**Note:** The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Products	X-Series Adhesive Transfer Tape XG2105	
	Faceside <sup>(1)</sup>	Backside <sup>(2)</sup>
Adhesion to Stainless Steel: 180 Degree Peel (ASTM Test Method – 2 mil Al)	50 oz/in (55 N/100mm)	47 oz/in (51 N/100mm)
Relative High Temperature Operating Ranges:		
Long Term (days / weeks)	150°F (65°C)	
Short Term (minutes / hours)	180°F (82°C)	
Relative Solvent Resistance:	Medium	
U.V. Resistance:	Good	
Shelf Life of Tape in Roll Form:	18 Months from date of manufacture when stored in original cartons at 70°F and 50% relative humidity.	

**Note 1:** Faceside adhesive is on the interior of the roll, exposed when unwound.

**Note 2:** Backside adhesive is on the exterior of the roll, exposed when the liner is removed.

### Available Sizes - Minimum Order Quantity Requirements

Please contact your 3M Customer Service Representative for available sizes and minimum order quantity requirements.

### Features and Benefits

- Balance of initial adhesion and holding power.
- Excellent adhesion to most grades of paper, newsprint, clay coated and corrugated.
- Stable adhesive – good U.V. resistance.

### Application Techniques

- Bond Strength is dependent upon the amount of adhesive to surface contact developed. Firm application pressure helps develop better adhesive contact and improve bond strength.
  - To obtain optimum adhesion, the bonding surfaces must be clean, dry and well unified. Some typical surface cleaning solvents are isopropyl alcohol or heptane.\*
- \*Note:** Be sure to follow solvent manufacturer's precautions and directions for use when using solvents.
- Ideal tape application temperature range is 70°F to 100°F (21°C to 38°C). Initial tape application to surfaces at temperatures below 50°F (10°C) is not recommended because the adhesive becomes too firm to adhere readily. However, once properly applied, low temperature holding is satisfactory.

# 3M™ X-Series General Purpose Transfer Tape

## XG2105

---

### Technical Information

The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

---

### Product Use

Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

---

### Warranty, Limited Remedy, and Disclaimer

Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

---

### Limitation of Liability

Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

**ISO 9001**

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001 standards.



### Industrial Adhesives and Tapes Division

3M Center, Building 225-3S-06  
St. Paul, MN 55144-1000  
800-362-3550 • 877-369-2923 (Fax)  
www.3M.com/xseries



*Recycled Paper*  
40% pre-consumer  
10% post-consumer

3M is a trademark of 3M Company.  
Printed in U.S.A.  
©3M 2013 (2/13)