

# **Product Description**

- Non-PVC adhesive backed film for Solvent, UV, Latex Inkjet printing and UV Screen Printing
- This film utilizes 3M<sup>™</sup> Controltac<sup>™</sup> and 3M<sup>™</sup> Comply<sup>™</sup> technology Controltac<sup>™</sup> minimizes the initial contact area of the adhesive for easy sliding, tacking, snap-up and repositioning

Comply<sup>™</sup> technology allows air to exit through air release channels to the edge of the graphic

- Use LX480mC with Latex Inkjet Inks or UV Inkjet Inks
- Use SV480mC with Solvent, Eco-solvent and UV Inkjet Inks
- Expected Performance Life (unwarranted period for unprinted film with no graphic protection, applied to a flat, vertical, outdoor surface under Northern European climate conditions):

- White:

11 years • Expected Performance Life (unwarranted period for unprinted film with no graphic protection, applied to a vertical textured surface, indoor application):

- White:

12 years

## **Recommended types of graphic and use**

- Indoor and outdoor graphics and signs
- Wraps for vehicles, straight trucks, semi-trucks and semi-trailers
- Bus graphics
- Watercraft graphics (above the static water line only)
- Point-of-purchase graphics and displays, emblems or striping
- Small format original equipment manufacturer's (OEM) decorative and identification graphics, cautionary and safety labeling
- Smooth and textured walls graphics

#### Surface types



# **Product line**

Product name	Description	Features
3M™ Envision™ Print Wrap Film LX480mC	white, opaque film with a glossy finish	Controltac™ and Comply™
3M™ Envision™ Print Wrap Film SV480mC	white, opaque film with a glossy finish	Controltac™ and Comply™



## **Recommended Compatible Products**

See instruction bulletin 'AT-1' for information about selection and use of suitable application tapes for this product, please.

Follow the link for further information about selection and use of compatible protective overlaminates and printable clears.

Follow the link for a complete list of compatible products that are approved by 3M for use with the base film covered in this Bulletin and used for the creation of a graphic that may be eligible for the 3M<sup>™</sup> MCS<sup>™</sup> Warranty or 3M Performance Guarantee.

### **Physical Properties**

The values displayed are the results of illustrative lab test measures made according to the indicated external norm and shall not be considered as a commitment from 3M.

Characteristic		
Non-Vinyl Composite		
Film without adhesive:	0,05 ± 0,005 mm	
Film with adhesive:	0,08 - 0,10 ± 0,01 mm	
Acrylic pressure-sensitive, repositionable		
Grey		
ABS	20 ± 2 N/25 mm	
Aluminum etched	20 ± 2 N/25 mm	
Paint	20 ± 2 N/25 mm	
0,4 mm		
Polyethylene-coated paper		
Dry only		
Aluminum, glass, PMMA, PC*, ABS, paint**		
The application of film onto glass can cause glass break by uneven heat absorption through sun exposure. 3M does not accept liability for glass breakage. * Might require drying with heat before application of film.		
** Check adhesion to powder-coated or water-based paints.		
4 – 38 °C	Flat	
10 – 38 °C	Simple curves, corrugations and rivets	
16 – 32 °C	Compound curves, recesses and watercrafts	
SV version 10 - 38 °C		
-53 to +107 °C		
(not for extended periods of time at the extremes)		
• Resists mild alkalis, mild acids, and salt		
<ul> <li>Excellent resistance to water (does not include immersion)</li> </ul>		
<ul> <li>Resists occasional fuel spills</li> </ul>		
Flammability standards are different from country to country. Ask your local 3M contact for details, please.		
Follow the link to check for available fire certificates.		
	Non-Vinyl Composite Film without adhesive: Film with adhesive: Acrylic pressure-sensitiv Grey ABS Aluminum etched Paint Polyethylene-coated par Dry only Aluminum, glass, PMMA The application of film onto gli through sun exposure. 3M doe * Might require drying with he ** Check adhesion to powder- 4 – 38 °C 10 – 38 °C 10 – 38 °C 16 – 32 °C SV version 10 - 38 °C -53 to +107 °C (not for extended periods of ti excellent resistance to Resists mild alkalis, mil Excellent resistance to Resists occasional fuel Flammability standards a local 3M contact for det	



# Warranty Information

3M Basic Product Warranty

3M Graphics Products are warranted to be free of defects in materials and manufacture at the time of shipment and to meet the specifications stated in its applicable 3M Graphics Product Bulletin and as further set forth in the 3M Graphics Warranties Bulletin.

3M<sup>™</sup> Performance Guarantee and MCS<sup>™</sup> Warranty

3M provides a guarantee/warranty on a finished applied graphic within the framework of 3M<sup>™</sup> Performance Guarantee and/or 3M<sup>™</sup> MCS<sup>™</sup> warranty programs.

Follow the link for a complete list of compatible products that are approved by 3M for use with the base film covered in this Bulletin and used for the creation of a graphic that may be eligible for the 3M<sup>™</sup> MCS<sup>™</sup> Warranty or 3M<sup>™</sup> Performance Guarantee.

# Limited Remedy

#### Unsuitable End Uses

3M recommended product end uses are listed in each 3M graphics product bulletin. End uses not listed in the applicable 3M Graphics Product Bulletins are typically not eligible for 3M Graphics Warranties. For non-recommended and/or non-warranted end uses or applications, users must test and approve the end uses or applications, assume any associated risks, and acknowledge that 3M has no liability for such end uses or applications. Please contact your 3M representative with any questions about graphic applications, end uses, and warranties.

#### Limitations of liability

All questions of warranty and liability relating to this product are governed by the terms and conditions of the sale, subject, where applicable, to the prevailing law. 3M Commercial Solutions products are not tested against automotive manufacturer specifications!

## **Graphic Manufacturing**

#### Ink jet printing

A too high total physical ink amount on the film results in media characteristic changes, inadequate drying, overlaminate lifting, and/or poor graphic performance. The maximum recommended total ink coverage for this film is 270%.

See the individual ink bulletins for details, please.

IMPORTANT NOTE: Incomplete drying or curing can result in graphic failure including curling, increased shrinkage and adhesion failure, which are not covered under any 3M Graphic Warranty.

Special Instructions for HP Latex 831/891

See 3M Customer Information on credits under LEED®v4

#### Sheeting, Scoring and Film Cutting

See 3M Instruction Bulletin 4.1 for Sheeting, Scoring and Film Cutting details



### **Application and Installation**

In addition to other 3M Bulletins specified in this document, the following Bulletins provide details that you may need to successfully apply a graphic.

See 3M Instruction Bulletin 5.42 for application and special considerations for watercrafts.

#### See 3M Instruction Bulletin 5.46 for application on substrates with recesses.

See 3M Instruction Bulletin 5.5 for general procedures for interior and exterior dry application.

<u>See 3M Instruction Bulletin 6.5 for information about storage, handling, maintenance</u> and removal of films and sheetings.

#### Maintenance, Cleaning and Removal

Use a cleaner designed for high-quality painted surfaces. The cleaner must be wet, non-abrasive, without solvents, and have a pH value between 3 and 11 (neither strongly acidic nor strongly alkaline).

These films can be removed with the aid of heat and/or chemicals.

<u>See 3M Instruction Bulletin 6.5 for information about storage, handling, maintenance</u> and removal of films and sheetings.

### Shelf Life, Storage and Shipping

The shelf life as defined below remains an indicative and maximum data, subject to many external and non-controllable factors. It may never be interpreted as warranty.

The shelf life is never more than 3 years from the date of manufacture on the original box. If you process the film, the shelf life is changed to 1 year from the processing date, but not later than the 3-year maximum from the manufacturing date.

Storage conditions: +4°C to +40°C, out of sunlight, original container in clean and dry area.

Shipping finished graphics: Flat, or rolled printed side out on 6 inch (15 cm) or larger core.

## **Health and Safety**

When handling any chemical products, read the manufacturer's container labels and the Safety Data Sheets (SDS) for important health, safety and environmental information.

Follow the link to obtain SDS sheets for 3M products on 3M.com/SDS.

Follow the link to obtain information about substances of very high concern (SVHC).

IMPORTANT! When using any equipment, always follow the manufacturer's instructions for safe operation.

3M, Controltac, Comply, Envision, MCS, Scotchgard and Scotchcal are trademarks of 3M. All other trademarks are the property of their respective owners.

3M United Kingdom PLC Commercial Solutions Division Cain Road Bracknell, RG12 8HT UK www.3m.co.uk/graphics-and-signage-uk/

© 3M 2020. All rights reserved.

3M Ireland (Dublin) The Iveagh Building The Park, Carrickmines Dublin 18 Ireland www.3m.co.uk/graphics-and-signage-uk/