

3M™ Elite Random Orbital Sanders

Now available with 3M™ Hookit™ Clean Sanding Backup Pad



Greater Conformability and Finer Finish

We took our best line of air-powered Random Orbital Sanders and made it better

Built to Last

- Sturdy, lightweight aluminum body
- All 3M™ Elite Series Tools feature internally located muffler
- Plenty of power for your tough sanding challenges

Designed for Maximum Operator Comfort

- Ergonomically enhanced for less vibration, quiet operation, more wrist support and overall operator comfort
- Lever is recessed, so no pinch points
- Durable cover for improved tactile feel and reduced vibration




Four Tools
Now with
Recommended
3M™ Hookit™
Backup Pad



3M

Recommended 3M™ Hookit™ Clean Sanding Backup Pads for Automotive Finishing Applications



Purple — For greater conformability and finer finish
3M™ Hookit™ Clean Sanding Painter's Backup Pad for primer, color and clear coat sanding applications



Yellow — Use with 3M interface pad for damp sanding applications
Designed for 6 inch 3M™ Clean Sanding Dust Free Disc Pad with Hook-it™ or with 6-hole, 7-hole, or other hole configuration dust free discs



Model 28701
with Hookit™ 05865



Model 28703
with Hookit™ 05551



Model 28702
with Hookit™ 05865



Model 28704
with Hookit™ 05551

Ordering Information



Model No.	Tool Dia. Inch (mm)	Max RPM	Motor HP (W)	Airflow Rate SCFM (LPM)	Orbit Dia. Inch (mm)	Weight Pound (kg)	Length Inch (mm)	Height Inch (mm)		UPC
3M™ Elite Non-Vacuum Random Orbital Sanders										
28701	6 (152)	12,000	.28 (209)	17 (481)	5/16 (8)	1.91 (.869)	7.36 (187)	3.58 (91)	Hookit™ 05865	051141-28701-0
28703	6 (152)	12,000	.28 (209)	17 (481)	3/16 (5)	1.86 (.844)	7.36 (187)	3.58 (91)	Hookit™ 05551	051141-28703-4
3M™ Elite Self-Generated Vacuum Random Orbital Sanders*										
28702	6 (152)	12,000	.28 (209)	17 (481)	5/16 (8)	2.04 (.927)	9.64 (245)	3.64 (92.6)	Hookit™ 05865	051141-28702-7
28704	6 (152)	12,000	.28 (209)	17 (481)	3/16 (5)	1.99 (.904)	9.64 (245)	3.64 (92.6)	Hookit™ 05551	051141-28704-1

*One (1) each of the following included: 3M™ Clean Sanding Filter Bag, Filter Bag Adapter, Hose Seal

To request additional product information or to arrange for sales assistance, call 1-800-3M-HELPS or visit 3Mcollision.com

Warranty, Limited Remedy, and Disclaimer: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. User is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application. Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.



Automotive Aftermarket Division
3M Center
Building 223-6N-01
St. Paul, MN 55144-1000
3Mcollision.com

3M and Hookit are trademarks of 3M. Used under license in Canada.
Please recycle. Printed in U.S.A. © 3M 2012. All rights reserved. 61-5002-8331-4