

Choose the right floor pad for the job.

| Maintenance Operation | Equipment Speed | First Choice | Alternate Choices | |
|-------------------------------------------------------------------------------------------------------|-------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Stripping To remove finish, sealer and contaminants from the floor surface. | Rotary or Automatic |  3M™ High Productivity Pad 7300 Our most aggressive stripping pad. Unique open construction resists loading and clogging. For fast removal of finish and proven consistent stripping. |  3M™ Black Stripper Pad 7200 Standard of the industry. Consistent proven performance. Long pad life. |  3M™ Brown Stripper Pad 7100 Conformable stripping pad for uneven floors. Super heavy-duty scrubbing for 2-4 coat removal. |
| | Low Speed 175-600 RPM | | | |
| Scrubbing To provide a fresh new surface for finishing. | Rotary or Automatic |  Scotch-Brite™ Clean & Shine Pad 2-in-1 daily cleaning pad for low-speed scrubbers that gradually increases shine with repeated use. |  3M™ TopLine Autoscrubber Pad 5000 Scrubs and cleans. Open construction resists clogging. Ideal for autoscrubbers. |  3M™ Red Buffer Pad 5100 Designed for everyday cleaning and light scrubbing to remove light soil, scuff marks and black heel marks. |
| | Low Speed 175-600 RPM | | | |
| Buffing To remove scuffs and black heel marks and enhance floor appearance. | Rotary |  3M™ Eraser Burnish Pad 3600 Removes black marks and returns gloss in fewer passes than other pads while producing less dust. Ideal for harder finishes and high traffic areas. Excellent durability and minimal finish removal. |  3M™ Natural Blend Tan Pad 3500 Blend of natural and synthetic fibers. Ideal for harder finishes and high traffic conditions. Removes marks and scuffs while polishing. |  3M™ Natural Blend White Pad 3300 Blend of natural and synthetic fibers. Excellent results on a wide variety of finishes and traffic conditions. Consistent high gloss with minimal swirl marks. |
| | Low Speed 175-600 RPM | | | |
| Burnishing To remove scuffs and marks, repair finish and improve gloss and image clarity. | Electric, Battery, Propane |  3M™ Sky Blue Hi-Performance Burnish Pad 3050 Restores gloss to dull floors. Designed for frequent burnishing with less dust, point buildup and burning. |  Scotch-Brite™ Sienna Diamond Floor Pad Plus Diamond-coated floor pads clean and condition worn and dull marble, terrazzo, slate and polished concrete, bringing it to a medium gloss. |  Greener Solutions Greener Solutions is a 3M program for 3M™ Floor Pads* that are made with at least 50% post-consumer recycled materials and water-based latex resins. Plus, our packaging is 100% recyclable and made with 50-100% recycled content. <small>The polyester fiber used to make a range of floor pads* contains a minimum of 50% post-consumer recycled content. The recycled polyester fiber used is third-party certified for post-consumer recycled content. *3M™ Brand Floor Pad families include: 3200, 3300, 3400, 3500, 3600, 5000, 5100, Sienna and Purple Diamond Pad. Niagara™ Brand Floor Pad families include: 3300N, 3400N, 3500N, 3700N, 5100N, 5400N and 7200N.</small> |
| | Ultra High Speed 1500 RPM & Above | | | |
| Best Gloss | Electric, Battery, Propane |  | | |
| | Ultra High Speed 1500 RPM & Above | | | |
| Soft Finish | Electric, Battery, Propane | | | |
| | Ultra High Speed 1500 RPM & Above | | | |
| Stone Floor Conditioning To clean and condition worn and dull stone floors. | Rotary, Automatic, Electric, Battery or Propane | | | |
| | Low to Ultra High Speed 175-1500 RPM & Above | | | |
| Stone Floor Polishing To clean and polish stone floors with medium shine in good condition. | Rotary, Automatic, Electric, Battery or Propane | | | |
| | Low to Ultra High Speed 175-1500 RPM & Above | | | |