

Elavation™ 7512

Technical Data Sheet



Elavation 7512 Full Body Harness

Elavation 7512 Full Body Harnesses are designed for users with a maximum capacity up to 400 pounds (181 kg) including clothing, tools, etc.

All components of the Elavation 7512 Full Body Harness meet the ANSI Z359.1-2007 standard and OSHA 29 CFR 1910.66 and 1926.502 requirements.



Attachment Points



A The dorsal (back) D-ring affixed to all 3M Full Body Harnesses is for fall arrest or restraint systems. The dorsal D-ring may also be used for rescue applications.



L A front D-ring is used for fall arrest in vertical systems that limit the free fall distance to 18 inches. The front D-ring may be used for restraint, and ladder climbing systems.



D The seat strap D-rings are to be used for rescue, and controlled descent applications. The front D-ring may also be used for rescue, and controlled descent.



E Shoulder D-rings may be used in rescue applications. Always use both shoulder D-rings simultaneously, utilizing the 3M M30-SBA Spreader Bar Assembly. **The shoulder D-rings are not for fall arrest or climbing applications.**



P Hip D-rings are used for positioning and restraint systems. Always use both hip D-ring connections when securing work positioning devices. **Hip D-rings are not for fall arrest or climbing applications.**

⚠ WARNING

Compliant fall protection and emergency rescue systems help prevent serious injury during fall arrest. Users must read and understand the User Instructions provided with the product and be properly trained by their employer prior to use per OSHA 29 CFR 1910.66 and 1926.503 or applicable local standards. **Misuse or failure to follow warnings and instructions may result in serious personal injury or death.** For proper use, see supervisor, User Instructions, or call Technical Service at 800-243-4630.



Elevation™ 7512

Technical Data Sheet



| Model 3M ID | Webbing Material | Belt Size | D-Rings | D-Ring Material | Leg Connection | Chest Connection | Capacity | CSA Class | Weight | Compliance Standards |
|------------------------------------|---------------------|---------------|---------------------------------------|--------------------|-------------------|---------------------|---------------------|--------------|---------------------|----------------------------------|
| 7512EQ (S-M) 70071604774 | Polyester | 34 in - 47 in | Back, Side, Extended Back D | Forged Steel | Quick Connect | Quick Connect | 400 lbs (181 kg) | A, P | | ANSI Z359.1-07 CSA Z259.10-06 |
| 7512EQ (S-M)-LOGO 70071604782 | Polyester | 34 in - 47 in | Back, Side, Extended Back D | Forged Steel | Quick Connect | Quick Connect | 400 lbs (181 kg) | A, P | | ANSI Z359.1-07 CSA Z259.10-06 |
| 7512EQ (L-XL) 70071604758 | Polyester | 44 in - 57 in | Back, Side, Extended Back D | Forged Steel | Quick Connect | Quick Connect | 400 lbs (181 kg) | A, P | | ANSI Z359.1-07 CSA Z259.10-06 |
| 7512EQ (L-XL)-LOGO 70071604766 | Polyester | 44 in - 57 in | Back, Side, Extended Back D | Forged Steel | Quick Connect | Quick Connect | 400 lbs (181 kg) | A, P | | ANSI Z359.1-07 CSA Z259.10-06 |
| 7512EQ-XXL 70071604857 | Polyester | 49 in - 62 in | Back, Side, Extended Back D | Forged Steel | Quick Connect | Quick Connect | 400 lbs (181 kg) | A, P | | ANSI Z359.1-07 CSA Z259.10-06 |
| 7512EQ-XXL-LOGO 70071604865 | Polyester | 49 in - 62 in | Back, Side, Extended Back D | Forged Steel | Quick Connect | Quick Connect | 400 lbs (181 kg) | A, P | | ANSI Z359.1-07 CSA Z259.10-06 |
| 7512FB (S-M) 70071612397 | Polyester | 34 in - 47 in | Back, Side, Extended Belt D | Forged Steel | Quick Connect | Quick Connect | 400 lbs (181 kg) | A, P | | ANSI Z359.1-07 CSA Z259.10-06 |
| 7512FB (L-XL) 70071612405 | Polyester | 44 in - 57 in | Back, Side, Extended Belt D | Forged Steel | Quick Connect | Quick Connect | 400 lbs (181 kg) | A, P | | ANSI Z359.1-07 CSA Z259.10-06 |
| 7512FB-XXL 70071612413 | Polyester | 49 in - 62 in | Back, Side, Extended Belt D | Forged Steel | Quick Connect | Quick Connect | 400 lbs (181 kg) | A, P | | ANSI Z359.1-07 CSA Z259.10-06 |
| 7512FEQ (S-M) 70071604816 | Polyester | 34 in - 47 in | Back, Front, Side, Extended Back D | Forged Steel | Quick Connect | Quick Connect | 400 lbs (181 kg) | A, P, L | | ANSI Z359.1-07 CSA Z259.10-06 |
| 7512FEQ (S-M)-LOGO 70071604824 | Polyester | 34 in - 47 in | Back, Front, Side, Extended Back D | Forged Steel | Quick Connect | Quick Connect | 400 lbs (181 kg) | A, P, L | | ANSI Z359.1-07 CSA Z259.10-06 |
| 7512FEQ (L-XL) 70071604790 | Polyester | 44 in - 57 in | Back, Front, Side, Extended Back D | Forged Steel | Quick Connect | Quick Connect | 400 lbs (181 kg) | A, P, L | | ANSI Z359.1-07 CSA Z259.10-06 |
| 7512FEQ (L-XL)-LOGO 70071604808 | Polyester | 44 in - 57 in | Back, Front, Side, Extended Back D | Forged Steel | Quick Connect | Quick Connect | 400 lbs (181 kg) | A, P, L | | ANSI Z359.1-07 CSA Z259.10-06 |
| 7512FEQ-XXL 70071604832 | Polyester | 49 in - 62 in | Back, Front, Side, Extended Back D | Forged Steel | Quick Connect | Quick Connect | 400 lbs (181 kg) | A, P, L | | ANSI Z359.1-07 CSA Z259.10-06 |
| 7512FEQ-XXL-LOGO 70071604840 | Polyester | 49 in - 62 in | Back, Front, Side, Extended Back D | Forged Steel | Quick Connect | Quick Connect | 400 lbs (181 kg) | A, P, L | | ANSI Z359.1-07 CSA Z259.10-06 |
| 7512FQ (S-M) 70071603768 | Polyester | 34 in - 47 in | Back, Front, Side | Forged Steel | Quick Connect | Quick Connect | 400 lbs (181 kg) | A, P, L | | ANSI Z359.1-07 CSA Z259.10-06 |
| 7512FQ (S-M)-LOGO 70071603776 | Polyester | 34 in - 47 in | Back, Front, Side | Forged Steel | Quick Connect | Quick Connect | 400 lbs (181 kg) | A, P, L | | ANSI Z359.1-07 CSA Z259.10-06 |
| 7512FQ (L-XL) 70071603743 | Polyester | 44 in - 57 in | Back, Front, Side | Forged Steel | Quick Connect | Quick Connect | 400 lbs (181 kg) | A, P, L | | ANSI Z359.1-07 CSA Z259.10-06 |
| 7512FQ (L-XL)-LOGO 70071603750 | Polyester | 44 in - 57 in | Back, Front, Side | Forged Steel | Quick Connect | Quick Connect | 400 lbs (181 kg) | A, P, L | | ANSI Z359.1-07 CSA Z259.10-06 |
| 7512FQ-XXL 70071603784 | Polyester | 49 in - 62 in | Back, Front, Side | Forged Steel | Quick Connect | Quick Connect | 400 lbs (181 kg) | A, P, L | | ANSI Z359.1-07 CSA Z259.10-06 |
| 7512FQ-XXL-LOGO 70071603792 | Polyester | 49 in - 62 in | Back, Front, Side | Forged Steel | Quick Connect | Quick Connect | 400 lbs (181 kg) | A, P, L | | ANSI Z359.1-07 CSA Z259.10-06 |
| 7512Q (S-M) 70071603727 | Polyester | 34 in - 47 in | Back, Side | Forged Steel | Quick Connect | Quick Connect | 400 lbs (181 kg) | A, P | 6.9 lbs (3.1 kg) | ANSI Z359.1-07 CSA Z259.10-06 |
| 7512Q (S-M)-LOGO 70071603735 | Polyester | 34 in - 47 in | Back, Side | Forged Steel | Quick Connect | Quick Connect | 400 lbs (181 kg) | A, P | 6.9 lbs (3.1 kg) | ANSI Z359.1-07 CSA Z259.10-06 |
| 7512Q (L-XL) 70071603701 | Polyester | 44 in - 57 in | Back, Side | Forged Steel | Quick Connect | Quick Connect | 400 lbs (181 kg) | A, P | 7.4 lbs (3.3 kg) | ANSI Z359.1-07 CSA Z259.10-06 |

F = Front D-Ring; E = Back D-Ring Extender; Q = Quick Connect; LOGO = Option to add custom logo; Weights and measurements are approximate.


Elavation™ 7512

Technical Data Sheet



| | | | | | | | | | | |
|----------------------------------|-----------|---------------|------------|--------------|---------------|---------------|---------------------|------|---------------------|----------------------------------|
| 7512Q (L-XL)-LOGO 70071603719 | Polyester | 44 in - 57 in | Back, Side | Forged Steel | Quick Connect | Quick Connect | 400 lbs (181 kg) | A, P | 7.4 lbs (3.3 kg) | ANSI Z359.1-07 CSA Z259.10-06 |
| 7512Q-XXL 70071603800 | Polyester | 49 in - 62 in | Back, Side | Forged Steel | Quick Connect | Quick Connect | 400 lbs (181 kg) | A, P | 8.0 lbs (3.6 kg) | ANSI Z359.1-07 CSA Z259.10-06 |
| 7512Q-XXL-LOGO 70071603818 | Polyester | 49 in - 62 in | Back, Side | Forged Steel | Quick Connect | Quick Connect | 400 lbs (181 kg) | A, P | 8.0 lbs (3.6 kg) | ANSI Z359.1-07 CSA Z259.10-06 |

F = Front D-Ring; E = Back D-Ring Extender; Q = Quick Connect; LOGO = Option to add custom logo; Weights and measurements are approximate.



Product Warranty, Limited Remedy, and Limitation of Liability

WARRANTY: THE FOLLOWING IS MADE IN LIEU OF ALL WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OR CONDITIONS OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Equipment offered by 3M is warranted against factory defects in workmanship and materials for a period of one year from date of installation or first use by the original owner.

LIMITED REMEDY: Upon notice in writing, 3M will repair or replace all defective items at 3M's sole discretion. 3M reserves the right to require that the defective item be returned to its plant for inspection before determining the appropriate course of action. Warranty does not cover equipment damage resulting from wear, abuse, damage in transit, failure to maintain the product or other damage beyond the control of 3M. 3M shall be the sole judge of product condition and warranty options. This warranty applies only to original purchaser and is the only warranty applicable to this product. Please contact 3M technical service department at 800-243-4630 for assistance.

LIMITATION OF LIABILITY: IN NO EVENT WILL 3M BE LIABLE FOR ANY INDIRECT, INCIDENTAL, SPECIAL OR CONSEQUENTIAL DAMAGES INCLUDING, BUT NOT LIMITED TO LOSS OF PROFITS, IN ANY WAY RELATED TO THE PRODUCTS REGARDLESS OF THE LEGAL THEORY ASSERTED.

3M Occupational Health & Environmental Safety Division

3M Center Building 235-2W-70
Saint Paul, MN 55144-1000
USA

Technical Assistance: 1-800-243-4630 in U.S.
and 1-800-267-4414 in Canada
www.3M.com/FallProtection
www.3M.com/PPESafety



Please recycle.
© 3M 2012
3M and Elavation are trademarks of 3M Company, used under license in Canada.
All rights reserved.
TS-00040 Rev A (06-2012)

