

## E-A-R™ Ultrafit™ 27 Earplugs

### Product Description

The 3M™ E-A-R™ UltraFit™ earplugs features a proprietary, premolded, triple-flange design that fits comfortably in most earcanals. Ergonomic pistol grip for an easier fit.

### Key Features

- Ergonomic pistol grip for an easier fit
- Triple-flange provides proven protection without rolling or touching plug during insertion.
- Washable and reusable.
- SLC80 22dB (Class 4).

### Applications

The E-A-R™ Ultrafit™ 27 earplugs are ideal for high noise exposure levels, and are ideally suited to provide protection against all noise frequencies in a wide range of industrial workplace and leisure environment. Examples of typical applications include:

- Automotive
- Chemical & pharmaceutical manufacture
- Construction
- Heavy engineering
- Metal processing
- Textile manufacture
- Woodworking

### Standard & Approval

These hearing protectors have been produced to comply with the requirements of the Australian /New Zealand Standard AS/NZS 1270:2002 under an agreed production certification scheme operated during manufacture in accordance with the SAI Global Standards Mark programme.

### Materials

The following materials are used in the manufacture of this product.

Component	Material
Earplugs	Polyurethane Foam
Cord	PVC



### Attenuation values

Frequency	125	250	500	1000	2000	4000	8000
Mean (dB)	23.3	22.6	24.2	28.0	33.6	35.0	41.5
SD (dB)	7.4	7.5	8.0	8.3	8.2	10.4	9.4

**SLC(80) = 22dB Class 4**

### Key

Mean = Mean attenuation value derived from testing in accordance with AS/NZS 1270:2002 SD = Standard Deviation derived from testing in accordance with AS/NZS 1270:2002 Mean - SD = Mean attenuation value minus Standard Deviation SLC(80) = Single number rating commonly used in Australia and New Zealand to compare acoustic performance of hearing protectors. The subscript '80' indicates that in well managed hearing protector programs, the protection provided is expected to equal or exceed the SLC(80) in 80% of protector-wearer noise spectrum combinations. Class = A simplified process for selecting hearing protectors based on the wearers 8-hour equivalent continuous A-weighted sound pressure level.

### Important Notice

3M does not accept liability of any kind, be it direct or consequential (including, but not limited to, loss of profits, business and/or goodwill) arising from reliance upon any information herein provided by 3M. The user is responsible for determining the suitability of the products for their intended use. Nothing in this statement will be deemed to exclude or restrict 3M's liability for death or personal injury arising from its negligence. Please recycle. © 3M 2010. All rights reserved.



Occupational Health and Environmental Safety Division  
 3M Australia Pty Limited  
 Building A, 1 Rivett Road  
 North Ryde NSW 2133  
 P: 1300 363 565 W:www.3m.com/au/ppesafety

3M New Zealand Pty Limited  
 94 Apollo Drive  
 Rosedale, Auckland 0632  
 P: 0800 252 627 W:www.3m.co.nz/ppesafety

© 3M 2012. All rights reserved.  
 Please recycle. Printed in Australia.