

3M[™] Abrasives and Power Tools for Stainless Steel Finishing

Systems for stainless steel finishing — the way to exceptional finishes.

3M[™] Stainless Steel Finishing System

Discover how fast and effective 3M abrasives can be for the often difficult task of stainless steel weld removal and finishing. This 3-step system features our Scotch-Brite[™], Cubitron[™] II and Trizact[™] abrasives.

In three easy steps, using the 3M Finishing System, you can grind and blend welds to match your finish.



Premium





The precision-shaped grain found in 3M[™] Cubitron[™] II belts continuously fractures to form sharp points and edges.



Scotch-Brite[™] non-woven synthetic fiber and abrasive mineral forms a web that is open, tough, conformable and long-lasting.



#4 Finish: Scotch-Brite[™] Surface Conditioning Belt A MED

#5-8 Finish: 3M[™] Trizact[™] Abrasive Belt 237AA / 217EA

TrizactTM

Trizact grain featuring microreplicated threedimensional abrasive structures for the finest finishes.

Your One Stop Shop

A complete system of 3M tools and accessories to make your finishing job simpler.



3M[™] Disc Sanders

- High power-to-weight ratio helps operators get more work done in less time
- ► 3M[™] Gripping Material allows easy control and user comfort
- Ergonomic 97-degree head allows for more comfortable wrist position
- Dual mount feature allows direct mount for visibility or collet mount for extended reach

UPC	Dia.	Max RPM	Motor
051141-20231-0	2"	20,000	0.5 HP
051141-28341-8	2"	20,000	0.3 HP
051141-20232-7	2–3"	15,000	1 HP
051141-28329-6	2–3"	12,000	0.5 HP
051141-28328-9	2-3"	12,000	0.3 HP

*Also supports 3" and 4" backup pads.



3M[™] Inline Sanders

- Straight shaft sander for generating or restoring straightline finishes
- Easy to control and simplifies finish matching
- ▶ 1 HP motor easily handles most finishing applications
- Fully machined steel motor housing provides strength and durability

UPC	Max RPM	Motor
051141-28339-5	3,500	1 HP

Accessories

UPC	Dimensions	Belt Size
051141-28348-7	5" x 3-1/2"	3-1/2" x 15-1/2"
051141-28349-4	3.4" x 3"	3" x 10-11/16"
051144-45038-1	#3 Wheel Adapter Kit	



3M[™] File Belt Sander

- ► Uses coated abrasive and Scotch-Brite[™] Belts (1/8"-3/4" x 18"-24") for a wide variety of metalworking applications
- Steel drive wheel attached
- Includes standard attachment arm (PN28368) and rubber drive wheel
- ► 24" belts require 3M[™] File Belt Sander Extension (PN28376)

UPC	Max RPM	Motor
051141-28366-1	22,000	0.6 HP

Accessories

UPC	Belt Size
051141-28372-2	1/8" or 1/4" x 18"
051141-28375-3	1/4" or 1/2" x 24"



3M[™] Match & Finish Sander

- Ideal for various blending and finish matching on metal parts
- Efficient way to generate or restore straight line finishes
- Easy to control and simplifies finish matching
- ► Adapters for multiple abrasive media make these versatile, utilitarian tools

UPC	Max RPM	Motor
051141-28659-4	3,500	1 HP
Accessories		
UPC	3M [™] Expander Wheel and Adapter Kit	
051141-28718-8	5" x 3-1/2" x 1 Arbor Hole	
051141-28719-5	1" x 5/8-11 INT	

Abrasives and accessories sold separately.

Leveling the Weld

Using the following products for weld leveling helps prepare stainless steel for #3 and #4 finishes.

Recommended Starting Points

Fibre Discs are engineered to cut faster, cooler and with less grinding pressure than conventional abrasives. And they are long lasting for increased productivity!

Option #1

60+

temperatures

3M[™] Cubitron[™] II Fibre Disc 987C

Powered by 3M Precision-Shaped Grain

Includes a grinding aid for cooler running

Best in class for weld prep and removal on

heat sensitive alloys such as stainless steel

for ultra-fast cut and exceptional life

3M[™] Fibre Disc 787C

Option #2

60+

- Powered by 3M Precision-Shaped Grain
- Optimized for stainless steel and non-ferrous metals like aluminum and titanium
- Cuts cooler, faster and lasts longer than conventional ceramic discs in applications like weld removal, beveling, edge chamfering and more
- Includes a grinding aid for cooler running temperatures

Tech Tip: Use the finest grade of abrasive that gets the job done; finer grind lines are easier to remove. Use a 7" dia. black ribbed faceplate to level the weld quickly and leave fine grind lines.

Alternative Selections

Flap Discs offer an unbeatable system for grinding and blending in one easy step. The construction wears away, exposing fresh mineral to extend disc life and provide consistent cut rates. 3M[™] Roloc[™] Discs provide a fast, efficient method for grinding, blending, leveling and finishing on all types of metal.

3M[™] Cubitron[™] II Flap Disc 967A 60+

- Powered by 3M Precision-Shaped Grain, this disc cuts fast and lasts long
- Exceptional for stainless steel fabrication where finish and gouge resistance are important
- Long-life and consistency at any grinding pressure
- Constructed with a poly-cotton backing that exposes fresh mineral as it wears, for a fast, forgiving cut



3M[™] Cubitron[™] II Roloc[™] Disc 987C 60+

- Powered by 3M Precision-Shaped Grain, engineered with ultra-sharp, fast cutting points that wear evenly, run cool, and optimize mineral breakdown to maximize life
- Includes grinding aid for cooler running temperatures, reducing metal discoloration/ oxidation and the chance of heat related stress cracks
- Disc life is significantly longer, completing more parts per disc and requiring fewer disc changes
- Best in class for weld prep and removal on heat sensitive alloys such as stainless steel



3M[™] Cubitron[™] II Roloc[™] Durable Edge Disc 984F 60+

- Powered by 3M Precision-Shaped Ceramic Grain for ultra-fast cut and exceptional life
- Includes a grinding aid for cooler running temperatures



Setting the Grain

Use these products to generate a directional scratch to prepare stainless steel for final finishing.

Recommended Starting Point



3M[™] Cubitron[™] Il Cloth Belt 947A

- 120+
- 3M Precision-Shaped Grain slices through metals like a knife rather than gouging or plowing
- Removes material faster, with less pressure
- Grinding aid for less grinding friction and cooler cutting
- Optimized for low-medium pressure applications on stainless, mild steel and aluminum

Tech Tip: Attempt to stay as close as possible to the weld area to minimize final blending.

Alternative Selections



3M[™] Cloth Belt 777F P120

- Powered by a durable ceramic aluminum oxide blend that surpasses aluminum oxide abrasives in cut-rate
- Grinding aid reduces heat and increases performance, when used stainless steel



3M[™] Flap Wheel 747D 80 3" x 1" x 1/4"

- Contains 3M[™] Ceramic Aluminum Oxide blend abrasive grain
- Constructed on a resin-bonded X-wt., durable cloth backing
- Provides a uniform finish
- Features a grinding aid for cooler grinding of stainless steel

Troubleshooting Guide for Stainless Steel Repair

Problem	Solution
Heat or Warpage	 Use coarser grade abrasive Reduce speed Use new abrasive Use harder disc pad
Edge Cutting	Use softer disc padReduce angle of grinder
Disc Scratches Show Through	 Use finer grade leveling disc Increase speed
Chatter	► Reduce speed and/or pressure
Flap Wheel Bounce	Reduce speed and/or pressureUse smaller wheel
Multi-finishing Wheel Bounce	Reduce speedDress wheel to round
Smearing	 Reduce speed Clean or replace contaminated product
Tool Stalling	 Check for proper air supply at tool Increase torque and/or HP of tool
Streaking on Final Finish	► Use 3M [™] Twist-Lok [™] Pad Holder 961

3

Final Finishing: Choose Your Finish

Generate a #3 through a #8 stainless steel finish with these 3M Products.

Recommended Starting Points

#3 Stainless Steel Finish



Scotch-Brite[™] SC Surface Conditioning Belt

A Coarse

- Premium Scotch-Brite surface conditioning non-woven web
- Designed for cleaning, finishing and light deburring
- Run at low speeds to generate uniform, well-blended satin finishes

Tech Tip: Finish a small area on the corner of the piece. Examine the finish from several angles. With a little practice you can "feather" in and out of the repair area. A few slow passes should restore the finish. Working with the grain, ease off pressure on both ends of the strokes.

#4 Stainless Steel Finish

Scotch-Brite[™] SC Surface Conditioning Belt

A Medium

- Constructed with a non-woven nylon material
- Designed for cleaning, finishing and light deburring
- Run at low speeds to generate uniform, well-blended satin finishes

Alternative Selection



Scotch-Brite[™] Multi-Finishing Wheel 2S Coarse 6" dia.

- Produces uniform grain finishes on stainless steel and other metals
- Highly conformable and tough enough to finish edges and welds
- Works well on large surfaces
- ► Available in 1", 2" and 3" widths



Alternative Selections

Scotch-Brite[™] Multi-Finishing Wheel 2S Medium 6" dia.

- Use on ferrous and non-ferrous metals
- Conformable to work surface
- Designed for cleaning, finishing and light deburring
- Can finish edges, welds and large surfaces
- ► Available in 1", 2", 3" widths



Final Finishing: Choose Your Finish (cont.)

Generate a #3 through a #8 stainless steel finish with these 3M Products.

Recommended Starting Points

#5-8 Stainless Steel Finishes



3M™ Trizact™ Abrasive Belts 237AA / 217EA

A 100

- 237AA is a perfect choice for dry metalworking applications, and is semi-flexible for intermediate to final finishing
- 217EA is a flexible belt for intermediate to final finishing, and is for low to medium pressure applications
- Both contain a grinding aid to assist in cutting and keeping the workpiece cool

Tech Tip: To achieve a pharmaceutical finish, choose 3M[™] Trizact[™] Belt 237AA in a series of grades A100, A45 and A16. Also to obtain a surface finish of less than 32 micro-inch for dairy applications, refine the repair area after Step 2 with a 3M[™] Trizact[™] 237AA, grade A100, followed by a fourth step of Scotch-Brite[™] Surface Conditioning Belt in grade A Very Fine.

Choose the Scotch-Brite[™] Match & Finish Flap Brush That's Right for Your Application

Scotch-Brite[™] Match & Finish Flap Brush Selection Guide



Tech Tip: Start with HS CRS or HS MED. If the finish doesn't match, then move to a more aggressive or less aggressive grade.



Match Your Finish with Scotch-Brite™ Match & Finish Flap Brushes

- Easy to control
- Conforms to most surface geometries
- Easy-thread on/off attachment

Tech Tip: With a little practice, you can "feather" in and out of the repair area. Working with the grain, ease off pressure on both ends of the strokes.

Product Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty and Limited Remedy: 3M warrants this tool against defects in workmanship and materials under normal operating conditions for one (1) year from the date of purchase. 3M MAKES NO OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. User is responsible for determining whether the 3M tool is fit for a particular purpose and suitable for user's application. User must operate the tool in accordance with all applicable operating instructions, safety precautions, and other procedures stated in the operating manual to be entitled to warranty coverage. 3M shall have no obligation to repair or replace any tool or part that fails due to normal wear, inadequate or improper maintenance, inadequate cleaning, non-lubrication, improper operating environment, improper utilities, operator error or misuse, alteration or modification, wishandling, lack of reasonable care, or due to any accidental cause. If a tool or any part thereof is defective within this warranty period, your exclusive remedy and 3M's sole obligation will be, at 3M's option, to repair or replace the tool or refund the purchase price.

Limitation of Liability: Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

3M, Cubitron, Roloc, Scotch-Brite, Trizact and Twist-Lok are trademarks of 3M. Used under license in Canada. Please recycle. Printed in U.S.A. © 3M 2019. All rights reserved. Issued: 10/19 61-5002-8191-2



3M Abrasive Systems 3M Center, Building 223-6N-02 St. Paul, MN 55144 USA

Phone 1-866-279-1235 Web 3M.com/abrasives