

DESCRIPTION	INK COLORS	SPECIAL INSTRUCTIONS
HDMI Mobile Projector MP300 Wrap Client: SD&P Job No: 70717 File Name: HDMI MP300 Wrap Printer: tbd Print Process: Offset Revision Date: 01-23-13	Number of printed colors: 6 ● Process CMYK ● Spot PMS 2593 ● Spot PMS Black	Dieline: ☐ FPO ☒ Final Photos: ☒ FPO ☐ Final ● Direct Print ☐ Litho Label Paperstock: Bindery: GO EAST 651 702 2900 goeastdesign.com



Mobile Projector MP300



Present in seconds!



Mobile Projector MP300



Every Second Counts:

Setup in seconds.
Present in seconds,
Make an impact in seconds.



Mobile Projector MP300



Transform your small screen presentation into a big screen experience in a matter of seconds. Quick, seamless visual presentations are critical in today's business world, however, projectors often act as a roadblock to accomplishing this fundamental task. Many professionals are opting for lugging around a huge projector, renting a projector at a substantial cost, or opting for no projector at all and eating the cost of printing color presentations. Say goodbye to these frustrations. Say hello to simple, plug-n-play projection.

True Mobility

- + **Ultra portable** – small enough to put into a coat pocket with up to 3.5 hour battery life
- + **Quick set up** – turn on and present in seconds
- + **Built in speaker**
- + **Bright enough for a variety of settings** – 60 lumens (not designed for brightly lit environments)

Intuitive & Simple

- + **Beautiful design** – intuitive plug-n-play interface
- + **HDMI/MHL** – mirror* your iPad®, tablet, laptop and smartphone device

Specs

Brightness: 60 lumens
Projected image size: 10" – 80" diagonal
Resolution: WVGA (854 x 480)
Audio: One 2 W speaker and audio output
Size (HxDxW): 4.3" x 4.2" X 2.0"
(109 x 106.7 x 50.8 mm)
Weight: 10.4 oz. (0.29 kg)
Light Source: LED (20,000 hours)
Warranty: 90 day
Battery: Rechargeable, up to 3.5 hours per charge (eco mode)
– runs continuous on AC power

*Apple® devices require an Apple® Digital AV Adapter (not included).



Specialty Display & Projection

3M Austin Center
6801 River Place Blvd.
Austin, TX 78726-9000
866-831-1656
3MMobileProductivity.com

Warranty and Limited Remedy: 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER EXPRESS OR IMPLIED WARRANTIES OR CONDITIONS, INCLUDING ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If the 3M product does not conform to this warranty, the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted.



Mobile Projector MP300

Contents

- Mobile Projector MP300
- Remote control
- HDMI Cable
- Power supply with US, EU, UK & AUS adapters
- Quick start guide

Features

- Up to 3.5 hour battery life
- HDMI/MHL compatible
- Portable design
- Bright, crisp image up to 80"
- Built-in speaker
- Speaker/headphone jack



4.3"



2.0"

4.2"



©3M 2013. All rights reserved. Please recycle. Printed in China. Made in China.
3M and the 3M logo are trademarks of 3M Company. Used under license in Canada. All other trade names referenced are the service marks, trademarks or registered trademarks of their respective companies.