

3M Science.
Applied to Life.™

Raise visibility, help reduce accidents.

Help improve road safety with
3M™ Raised Pavement Markers.

Throw dark and rainy roads a curve with 3M™ Raised Pavement Markers. These tough, impact-resistant lane indicators feature abrasion-resistant microprismatic lenses for high visibility that will last down the road.

Raised Pavement
Markers can help
**reduce
accidents**
by up to

24%

Safety Evaluation of Permanent Raised Pavement Markers, NCHRP Report 518, Transportation Research Board, 2004.

Road-ready reflectivity and durability.

Day or night, rain or shine, 3M™ Raised Pavement Markers can help enhance the visibility of center lines, edge lines and gore, ramp and specialty applications. These durable markers are engineered to remain highly-visible even on rain covered roadways. They also create an audible rumble when struck by tires that help alert drivers when they veer out of their lane.

Up to **9.6X brighter** than initial R_L minimums and up to **6.3X brighter** than minimum post-abrasion R_L minimums as outlined in ASTM D4280

Source: 3M Series 290 RPM Reflective Pavement Markers Test Report, Calcoast Industrial Testing Laboratory, Report No. 210712-01J, 2021.



3M™ Raised Pavement Marker Series 290 and Series 290PSA

These highly-reflective, durable markers feature 3M™ Diamond Grade™ microprismatic optics and a ceramic lens coating to provide extreme resistance to abrasion and cracking. Install them on concrete or asphalt with the pre-applied pressure-sensitive adhesive pad (290PSA). Finger grips make handling easy and installation simple.



Product Features

- Durable
- Wet and dry retroreflective
- Impact resistant
- Abrasion resistant
- Molded-in body colors
- Rumble effect
- Lightweight
- Application finger grips
- Compatible with standard bitumen and epoxy adhesives (Series 290 only)
- Meets the requirements of ASTM D4280

RPM Series 290		RPM Series 290PSA	
One-Way Markers		Body Color	Lens Color
RPM-290-W	PSA-290-W	White	White
RPM-290-Y	PSA-290-Y	White	Yellow
RPM-291-Y	PSA-291-Y	Yellow	Yellow
Two-Way Markers		Body Color	Lens Color
RPM-291-2Y	PSA-291-2Y	Yellow	Yellow
RPM-291-YR	PSA-291-YR	Yellow	Yellow and Red
RPM-290-2W	PSA-290-2W	White	White
RPM-290-YWR	PSA-290-YWR	White	White and Red
RPM-290-WY	PSA-290-WY	White	White and Yellow
RPM-290-2R	PSA-290-2R	White	Red
RPM-295-2B	PSA-295-2B	Blue	Blue
RPM-297-2G	PSA-297-2G	Green	Green
RPM-292-2R	PSA-292-2R	Red	Red

Product Dimensions

Dimension	Value
Height	0.625 in. ± 0.02 in. (15.88 mm ± 0.5 mm)
Width	4.00 in. ± 0.02 in. (101.6 mm ± 0.5 mm)
Length	3.50 in. ± 0.02 in. (88.9 mm ± 0.5 mm)

* Specialty Markers: Make-to-Order and Longer Lead Times

** Some combinations not available, see price book for more information.



Commercial Branding and Transportation
3M Center, Building 223-3N-30
St. Paul, MN 55144
Phone: 1-800-553-1380
3M.com/RoadSafety

Raise your visibility at
3M.com/PavementMarkings

© 3M 2026. All rights reserved.
3M and Diamond Grade are trademarks of 3M.