

Raise visibility, reduce crashes.

Help improve road safety with
3M™ Raised Pavement Markers.

Throw dark and rainy roads a curve with 3M™ Raised Pavement Markers. These tough, impact-resistant lane indicators feature abrasion-resistant microprismatic lenses for high visibility that will last down the road.

Raised Pavement
Markers can help

**reduce
crashes**

by up to

24%

Safety Evaluation of Permanent Raised Pavement Markers, NCHRP Report 518, Transportation Research Board, 2004.

Road-ready reflectivity and durability.

Day or night, rain or shine, 3M™ Raised Pavement Markings can help enhance the visibility of center lines, edge lines and gore, ramp and specialty applications. These durable markers are designed to remain highly-visible even on rain covered roadways. They also create an audible rumble when struck by tires that alerts drivers when they veer out of their lane.

Up to
4.5X brighter

than initial R_L minimums and up to

7X brighter


than minimum post-abrasion R_L minimums as outlined in ASTM D4280 Standard Specification for RPMs at Odeg

Source: 3M Series 290 RPM Reflective Pavement Markers Test Report, Calcoast Industrial Testing Laboratory, Report No. 160412-01H, 2016.



Series 290 Non-Snowplow

These highly-reflective, durable markers feature 3M™ Diamond Grade™ microprismatic optics and a ceramic lens coating to provide extreme resistance to abrasion and cracking. Install them on concrete or asphalt with the supplied pressure-sensitive adhesive pad. Finger grips make handling easy and installation simple.



Series 190 Snowplowable

Ultra-tough polycarbonate design is built for the harshest environments. Available as replacement markers or pre-installed markers in snowplowable casings. Replacement markers feature a peel-away liner for direct application to existing castings or they can be installed with a commercially-available adhesive.



RPM Series 290		
Product No.	Body Color	Lens Color Options
One Way Markers		
RPM-290	White	White, Yellow, Red, Green
RPM-291	Yellow	
RPM-292*	Red	
RPM-297*	Green	
Two Way Markers		
RPM-290	White	White, Yellow, Red, Blue, Green
RPM-291	Yellow	
RPM-292*	Red	
RPM-295*	Blue	
RPM-297*	Green	

RPM Series 290-PSA		
Product No.	Body Color	Lens Color Options
One Way Markers		
RPM PSA-290	White	White, Yellow
RPM PSA-291	Yellow	
Two Way Markers		
RPM PSA-290	White	White, Yellow, Red, Blue, Green
RPM PSA-291	Yellow	
RPM PSA-292*	Red	
RPM PSA-295*	Blue	
RPM PSA-297*	Green	

RPM Series 190		
Product No.	Body Color	Lens Color Options**
One Way Markers		
RPM-190	Black	White, Yellow
Two Way Markers		
RPM-190	Black	Yellow, Red, White

*Specialty Markers: Make-to-Order and Longer Lead Times
**Some combinations not available, see price book for more information.



Transportation Safety Division
3M Center, Building 225-4N-14
St. Paul, MN 55144-1000
3M.com/RoadSafety

Raise your visibility at
3M.com/PavementMarkings.

Please recycle. Printed in USA.
3M and Diamond Grade are trademarks of 3M.
© 3M 2019. All rights reserved.