



**3M** Science.  
Applied to Life.™

# The ultimate choice in comfortable, durable protection.

## The 3M™ Ultimate FX Full Facepiece Respirator FF-400

For the work you do, comfort and durability are everything. With a soft feel to the face, comfortable head cradle, plus reduced heat and moisture buildup, 3M's Ultimate FX Full Facepiece Respirator delivers premium comfort that lasts as long as you do. And it's the only respirator with 3M's unique Scotchgard™ Paint and Stain Protector, which helps keep the lens dirt-, paint- and stain-resistant — not to mention so much easier to clean.

# Premium comfort, durable, easy-to-clean 3M™ Ultimate FX Full Facepiece Respirator FF-400

## Large lens with 3M™ Scotchgard™ Protection

- 3M's exclusive Scotchgard™ Paint and Stain Protector helps liquids bead up on the surface of the lens so they can easily be wiped away
- Large lens provides a superior field of view



## NEW Optional stacked lens cover accessory

- Minimizes prep time and lens cover replacement work stoppages
- 7 removable layers protect lens from debris, overspray and damage



## Advanced comfort & performance features

- Comfort cradle
- Soft silicone nose cup and face seal
- 3M™ Cool Flow™ Valve
- Low-profile bayonet design
- Bonded silicone gaskets



## Passive speaking diaphragm

- Optimally positioned for clearer and easier communications

## Facepieces

Part No.	Description	UPC#	Qty/ Case
FF-401	Facepiece, Small	50051135894182	4
FF-402	Facepiece, Medium	50051135894212	4
FF-403	Facepiece, Large	50051135894243	4

## Parts & accessories

Part No.	Description	Qty/ Case
FF-400-01	3M™ Buckle	30
FF-400-02	3M™ Button	30
FF-400-03	3M™ Lens Replacement	5
FF-400-04	3M™ Head Harness	5
FF-400-05	3M™ Lens Frame Assembly	5
FF-400-06	3M™ Comfort Cradle Head Harness Attachment	5

Part No.	Description	Qty/ Case
FF-400-07	3M™ Exhalation Valve Assembly	5
FF-400-08	3M™ Bayonet Assembly	10
FF-400-09	3M™ Exhalation Valve Cover	5
FF-400-10	3M™ Solid Exhalation Valve Cover	5
FF-400-11	3M™ Nose Cup Assembly	5
FF-400-13	3M™ Speaking Diaphragm Assembly	5
FF-400-15	3M™ Lens Cover	100
FF-400-17	3M™ Semi-Permanent Lens Protector	20
FF-400-18	3M™ Stacked Lens Cover (7 sheets) <b>NEW</b>	20
FF-400-20	3M™ Spectacle Kit	1
FF-400-25	3M™ Reusable Nylon Respirator Storage Bag	10
7582	3M™ Inhalation Valve	10
7583	3M™ Exhalation Valve	10



## WARNING

These respirators help protect against certain airborne contaminants. Before use, the wearer must read and understand the User Instructions provided as a part of the product packaging. A written respiratory protection program must be implemented meeting all the requirements of OSHA 1910.134, including training, fit testing and medical evaluation. In Canada, CSA standards Z94.4 requirements must be met and/or requirements of the applicable jurisdiction, as appropriate.

Misuse may result in sickness or death. For proper use, see packaging instructions, supervisor, or call 3M PSD Technical Service in U.S. at 1-800-243-4630 and in Canada at 1-800-267-4414.



**Personal Safety Division**  
3M Center, Building 235-2W-70  
St. Paul, MN 55144-1000

### For more information

In the U.S., contact:  
Technical Assistance: 1-800-243-4630  
Customer Service: 1-800-328-1667  
3M.com/PPESafety

In Canada, contact:  
Technical Assistance: 1-800-267-4414  
Customer Service: 1-800-364-3577  
3M.ca/PPESafety

© 3M 2015. All rights reserved. 3M, Scotchgard and Cool Flow are trademarks of 3M Company, used under license in Canada. Please recycle. Printed in U.S. 70-0714-8854-1