

**3M** Science.  
Applied to Life.™

# Made in the USA



**3M products listed in this brochure are manufactured in the USA as of September 1, 2015. 3M products offered on a government contract that require country of origin representation must be certified by 3M's Trade Compliance Department (contact your customer service support team and request a certification). If more than one year after the published date, please contact your customer service representative for an updated brochure at 800-245-3573.**

### 3M™ Insulators, Seals, Accessories

- Cold Shrink Insulator 8420, 8430, 8440 and 8450 Series
- Cold Shrink Connector Insulators QSLV-M and QI
- CPT – Corrosion Protection Kits
- PST Sheath Seal Kits
- Motor Lead Kits
- Electrostatic Animal Guards

### 3M™ Splices and Terminations

- Cold Shrink Splices QS-I, QS-II and QS-III
- Cold Shrink Terminations QT-II and QT-III
- Cold Shrink Splice Kits 5730, 5740 and 5550 Series
- Modular Splicing Kits
- Loadbreak Elbow Connectors
- Scotchlok™ Connectors (Lugs) – ALL Aluminum

### 3M™ and Scotch® Electrical Sealants, Mastics

- Moisture Sealant Strip 06147
- Moisture Sealant Pad 06149
- Vinyl Mastic Pads 2200
- Vinyl Mastic Roll 2210
- Rubber Mastic Tape 2228
- Scotch-Seal™ Mastic Compound 2229
- Mastic Strips 2230
- Scotchfil™ Electrical Insulation Putty Tape
- Electrical Moisture Block EMB
- Electrical Moisture Sealant EMS-II

### Scotch® Vinyl Electrical Tapes

- Premium Vinyl Electrical Tape 33
- Super 33+™ Premium Vinyl Electrical Tape
- Premium Vinyl Electrical Tape Super 88
- Vinyl Electrical Color Coding Tape 35 – ALL COLORS

### 3M™ Vinyl and Scotch® Specialty Tapes

- Heavy Duty Vinyl Tape 22
- Vinyl Tape 66R
- Temflex™ Vinyl Tape 1776
- Fire-Retardant and Electric Arc Proofing Tapes 77 and 77W
- Highland™ Vinyl Tape
- Scotchrap™ All-Weather Corrosion Protective Tape 50, 51
- Scotchrap™ Pipe Primer
- Heavy Duty Mining Tape 31
- Cable Jacket Repair Tape 2234
- Linerless Rubber Splicing Tape 130C
- Linerless Electrical Rubber 2242
- Barricade Tapes\* – Red, Yellow, Orange

### 3M™ Coatings, Insulating Sprays, Cleaners

- Scotchkote™ Electrical Coating and Electrical Coating FD
- Insulating Sprays 1601 (clear), 1602 (red)
- Cable Preparation Kits CC-2, CC-3, CC-Dry

### 3M™ and Scotch® Tapes for OEMs

- Epoxy Film Electrical Tape 1
- Epoxy Film Electrical Tape Super 10
- Epoxy Film Electrical Tape Super 20
- Glass Cloth Tape 27
- Anti-Static Utility Tape 40
- Composite Film Electrical Tape 44
- Acetate Cloth Tape 11, Black
- Polyester Film Electrical Tape 54
- Glass Cloth Tape 69
- Glass Cloth Electrical Tape 79, White
- Polyimide Film 92

### 3M™ Heat Shrinkable Tubing

- Bus Bar Tubing BBI
- Environmental Protection Sleeve, Adhesive-Lined, Polyolefin EPS 200, 300, 400
- Flexible Polyolefin FP-301
- Heavy-Duty Flame Retardant HDT
- Medium-Wall Cable Sleeve IMCSN
- Heavy-Wall Cable Sleeve ITCNSN
- Medium-Duty Flame-Retardant MDT
- Medium Wall MW
- Elastomeric Polyester Tubing PSTH, Black
- Automotive Tubing SMS
- Adhesive-Lined, Semi-Rigid Polyolefin TES
- Adhesive-Lined, Translucent, Semi-Rigid Polyolefin TMW
- Fluoroelastomer VTN-200

### 3M™ Connectors

- Performance Plus Connectors
  - O/B+, B/G+, R/Y+
  - Tan Connectors T/R+, T/Y+
- Electrical Spring Connectors
  - 312, 512, 512G
- Scotchlok™ IDC Connectors
  - 557, 558, 557T, 558T
  - 560, 560N, 560B, 562, 564, 567
  - 801, 804, 901, 902, 903, 905, 905N
- Direct Bury Splice Kits DBR/Y-6 and DBO/B-6
- Scotchlok™ Irrigation IDC Connectors
  - 314, 314U, 316IR
- Scotchlok™ Moisture Guard Connectors (MGC)

### 3M™ Flexible Insulation\*

- Does not include DM and DMD series products

### 3M™ Wire Lube

- Wire Pulling Cable Loosener WPCL
- Wire Pulling Lubricant Gel WL
- Wire Pulling Lubricant Communication WLC
- Wire Pulling Lubricant Wintergrade WLW
- Wire Pulling Lubricant Wax WLX

### 3M™ ScotchCode™ Wire Markers, Stackers

- Wire Marker Tape SDR – All variations
- Wire Marker Books SPB – All variations
- Wire Marker Tag STD 0-9 and Alpha
- Wire Marker Colors STD – All variations
- Write On Wire Marker Book SWB-1
- Write On Rolls SWD, SLW, SLS
- Furring Strip SIFS-1, Cable Stacker SI-1

### 3M™ Scotchcast™ Electrical Resins

- Liquid Resins 3, 4, 5, 8, 9, 10
- Liquid Resins 208, 210, 226, 235, 241, 243
- Liquid Resins 250, 251, 252, 253, 255
- Liquid Resins 280, 281, 282, 400
- Electrical Resin 2104, 2123, 2131, 2136
- Flame Retardant Compound 2131
- Connector Sealing Pack 3570G-N

### 3M™ Scotchcast™ Electrical Resin Splice Kits

- Resin Splice Kit 72-N Family
- Re-enterable Splice Kit 78-RX Family
- Inline Resin Splice Kit 82-A Family
- Wye Resin Splice Kit 82-B, 82-F Family
- Resin Splice Kits 5750, 5760 Series
- Multi-mold Resin Splice Kit 85 Series
- Wye Resin Splice Kit 90-B1
- Spacer Web 7820
- Wet Niche Potting Compound 2136
- Mold Kit M-20,-30,-40

### 3M™ Scotchlok™ Terminals and 3M™ Highland™ Terminals (bagged)

- Most terminals are made in the USA; contact EMD for information.

### 3M™ Fastening Products

- Cable Ties (except 48")
- Red Cable Ties
- Cable Tie Bases

### 3M™ Aluminum Conductor Composite Reinforced\*

- Conductor and Some Accessories

\*Note: Most made in U.S., some versions are made outside U.S.

3M, Scotch, Temflex, Scotchrap, Scotch-Seal, ScotchCode, Scotchfil, Scotchlok, Scotchcast, Scotchkote, Highland, and Super 33+ are trademarks of 3M Company.

#### Important Notice:

The country of origin determination for a 3M product is only valid with a current written certification from the 3M Trade Compliance Department. The information in this brochure is accurate, to 3M's knowledge and belief, which may be based on information provided by third party suppliers to 3M.



**Electrical Markets Division**  
6801 River Place Blvd.  
Austin, TX 78726-9000 USA

Phone 1-800-245-3573  
Fax 1-800-245-0329  
Web 3M.com/electrical

80-6016-0388-1F (09151)XX-1  
Please recycle. Printed in USA © 3M 2015.  
All rights reserved.