

**3M™ Pin Strip Header 1512 Series**

**Product Specification 78-5102-0139-1**

**Revised 7-25-12**



## Table of Contents

---

<b>Title Page</b>	1
<b>Contents</b>	2
<b>1.0 Scope</b>	3
<b>2.0 3M Customer Documents</b>	3
<b>3.0 Performance Testing</b>	3
<b>4.0 Performance and Characteristics Overview</b>	3
<b>5.0 Electrical</b>	4
<b>6.0 Mechanical</b>	4
<b>7.0 Physical</b>	5
<b>8.0 Environmental</b>	5
<b>9.0 Qualification Test Groups and Sequences</b>	6
<b>10.0 Figures</b>	6
<b>11.0 Agency Listings</b>	7
<b>Important Notice</b>	8
<b>Warranty Information</b>	8

Steven A. Neu: Approved 07-29-12  
Jim W. Wessman: Approved 07-29-12

## 1.0 Scope

This document summarizes test methods, test conditions, and product performance requirements for 3M™ Thru-Board Socket 1532 Series mated to 3M™ Pin Strip Header 1512 Series. In the event of performance data conflicts between this specification and any documents listed below, this specification supersedes those documents. Materials and finishes listed in the documents below apply and are included in this specification for reference only.

## 2.0 3M Customer Documents

78-5100-0521-4 Technical data sheet for Thru-Board Socket 1532 Series  
78-5100-0808-5 Technical data sheet for Pin Strip Header 1512 Series

## 3.0 Performance Testing

Unless otherwise specified, all tests shall be performed on 153244-2000-RB sockets mated to 151244-7422-RB headers at ambient environmental conditions per EIA-364. Unless otherwise specified, all values and limits are typical of those obtained by qualification testing of the subject product. All specifications are subject to revision and change without notice from 3M.

## 4.0 Performance and Characteristics Overview

### 4.1 Ratings

Dielectric Withstanding Voltage: 500 V<sub>DC</sub> at sea level

Current (AC or DC):

3.50 A 1 line energized

1.75 A 6 lines\* energized

1.00 A All lines energized

\*Lines are adjacent in 2x3 configuration

Current rating conditions: 30°C temperature rise, 20% derated

Temperature: -55°C to +105°C

Insulation resistance: >1 x10<sup>9</sup> Ω at 250 VDC

### 4.2 Materials

Socket:

Housing insulation: Glass filled LCP, black, 94V-0

Contact: Copper alloy

Header:

Insulation: Glass filled LCP, black, 94V-0

Contact: Copper alloy

### 4.3 Finishes

Plating:

Nickel: Underplating: 50 - 150 μ inches (1.27 - 3.81 μm), QQ-N-290, Class 2

Solder Tails: 200-300 μ inches (5.108-7.62μm), Matte or Tin Lead

Gold options: 30 μ inches (0.76 μm) Average, ASTM B488-01, Class C

**4.4 Regulatory Compliance**

See Regulatory Information Appendix (RIA) in the “RoHS compliance” section of [www.3Mconnector.com](http://www.3Mconnector.com) for compliance information. See customer drawings for regulatory specifics on each connector.

**5.0 Electrical**

Description or Parameter	Values & Limits	Units	Requirement or Conditions	Test Standard or Method
Dielectric withstanding voltage	500	Volts <sub>DC</sub>	Measured between adjacent and opposing contacts. No disruptive discharge during 1 minute duration. Sea level with 70% relative humidity.	EIA-364-20B Method B Condition I
Current rating per line	3.50	Amperes	1 line energized.	30° C temperature rise, 20% derated.
	1.75		6 lines energized.	
	1.00		All lines energized.	
Low level contact resistance	≤10	Milliohms	10 milliohm maximum ΔR contact resistance per mated interface throughout testing.	EIA-364-23A
Insulation resistance	>1000	Megohms	Measured between adjacent and opposing contacts with 500 VDC applied for 1 minute.	EIA-364-21C

**6.0 Mechanical**

Description or Parameter	Values & Limits	Units	Requirement or Conditions	Test Standard or Method
Vibration	≤10	ns	Mated connectors shall exhibit no discontinuities greater than specified. 10 milliohm maximum ΔR contact resistance per mated interface throughout testing.	EIA-364-28A Condition V Letter A, 1.5 hours each plane
Mechanical Shock	≤10	ns	Mated connectors shall exhibit no discontinuities greater than specified. 10 milliohm maximum ΔR contact resistance per mated interface throughout testing.	EIA-364-27B Condition A
Durability	50	Mating cycles	10 milliohm maximum ΔR contact resistance throughout testing.	EIA-364-09C

**7.0 Physical**

Description or Parameter	Values & Limits	Units	Requirement or Conditions	Test Standard or Method
Visual	N/A	N/A	No defects such as deformation, blisters, cracks or other damage.	EIA-364-18A
Tin Plating Thickness	5.08-7.62 (200-300)	Micro-meters (Micro-inches)	Average of random measurements from any 3 lots shall not be less than specified.	EIA-364-48
Nickel Plating Thickness	1.27 - 3.81 (50-150)	Micro-meters (Micro-inches)	Average of random measurements from any 3 lots shall not be less than specified.	EIA-364-48
Gold Thickness	0.63-0.89 (25-35)	Micro-meters (Micro-inches)	Average of random measurements from any 3 lots shall not be less than specified.	EIA-364-48

**8.0 Environmental**

Description or Parameter	Values & Limits	Units	Requirement or Conditions	Test Standard or Method
Temperature Life (Thermal Aging)	105	Degrees C	Measurements taken out for contact resistance measurements at 96,240,504,and 1000 Hrs. No physical abnormalities. 10 milliohm maximum $\Delta R$ contact resistance throughout testing.	EIA-364-17B Method A Condition 4
	1000	Hours		
Thermal Shock	-55 to 105	Degrees C	No physical abnormalities. 10 milliohm maximum $\Delta R$ contact resistance throughout testing.	EIA-364-32C Condition VII
	5	Cycles		
Humidity-Temperature Cycling	65 to -10	Degrees C	No physical abnormalities. 10 milliohm maximum $\Delta R$ contact resistance throughout testing.	EIA-364-31B Condition B Method III
	90 to 98	% Relative humidity		
	240	Hours		
Nitric Acid Vapor Test (Gold)	1	Hours	1 spot per sample lot. Porosity of gold contacts tested. No durability testing.	EIA-364-52 Category 3

**9.0 Qualification Test Groups and Sequences**

**9.1 Sequenced Tests**


Test or Examination	Test Group			
	A	B	C	D
	<b>Test Sequence</b>			
Low Level Contact Resistance	1, 3, 5	1, 3, 5, 7	1, 3, 5	1, 3, 5
Vibration			2	
Mechanical Shock			4	
Thermal Shock	2	4		
Humidity-Temperature Cycling	4	6		
Nitric Acid Vapor Test				4
Durability		2		2



**9.2 Independent Tests**

- 1 Dimensional
- 2 Dielectric Withstanding Voltage
- 3 Current Rating
- 4 Insulation Resistance
- 5 Plating Thickness
- 6 Contact Retention- EIA-364-29
- 7 Porosity Test- EIA-364-60
- 8 Temperature Life

**10. Figures**

**10.1 Current Rating**





**11.0 Agency Listings**

**11.1 Underwriters Laboratories (UL)**

Agency	File No.
UL	E68080
CUL	E68080

---

**3M is a trademark of 3M Company.**

**Important Notice**

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

**Warranty; Limited Remedy; Limited Liability**

This product will be free from defects in material and manufacture for a period of one (1) year from the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**

© 3M 2013. All rights reserved.