

The 3M™ Resilient Floor Protection System.

Tougher protection. Fewer chemicals.

Once your floors are protected with Scotchgard™ Resilient Floor Protector, you can maintain their beauty by cleaning daily with 3M™ Neutral Cleaner and occasional burnishing with the long-lasting 3M™ Tan Burnish Pad 3400.

Improve productivity and reduce operational costs when used as a complete system.

Order now or schedule a free demonstration by calling 1.866.649.1973.











See the science in action! Go to 3M.com/Resilient to see lab demonstrations of Scotchgard™ Resilient Floor Protector compared to traditional acrylic finishes.



The 3M™ Resilient Floor Protection System includes 3M™ Neutral Cleaner and the long-lasting 3M™ Tan Burnish Pad 3400.

Products and Ordering Information

| Product | Information & Applications | Size | Item # | Oty. |
|--|---|--------------------------------|----------------|-----------------------------|
|  Scotchgard™ Resilient Floor Protector | Proprietary high performance, water-based floor coating that protects and enhances the appearance of linoleum, vinyl tile and sheet vinyl. Estimated coverage 2,000 square feet per gallon when applied with the 3M™ Easy Shine Applicator. | 1 gallon bag 2.5 gallon jug | 85861 85880 | 2/cs 2/cs |
|  3M™ Tan Burnish Pad 3400 | Combines black mark removal and gloss generation. | Multiple sizes available | | 5/cs |
|  3M™ TopLine Autoscrubber Pad 5000 | For deeper scrubbing of floors prior to burnishing. Scrubs and cleans without dulling the finish. Open construction resists clogging. | Multiple sizes available | | 5/cs |
|  3M™ Red Buffer Pad 5100 | Designed for everyday cleaning and light scrubbing to remove light soil, scuff marks and black heel marks. | Multiple sizes available | | 5/cs |
|  3M™ Easy Shine Applicator Kit | Helps reduce worker exposure to floor finish and accelerates application compared to traditional mop and bucket methods. | Applicator w/ 16" pad | 55433 | 1/ea |
|  3M™ Easy Shine Applicator Pad | Washable and reusable 18" pads for the 3M™ Easy Shine Applicator. | 18" | 59646 | 10/cs |
|  3M™ Easy Trap Duster | Specially developed disposable sheets simplify removal of dust, dirt and sand from floor surfaces. | 8" x 6" x 125' | 55654 | 1 roll/box 250 sheets/cs |
| | | 8" x 6" x 30' | 59152 | 60 sheets/box 8 boxes/cs |
|  3M™ Neutral Cleaner Concentrate | Designed specifically for use with Scotchgard™ Resilient Floor Protector, the no-rinse, low-foaming formula has proven compatibility and will not leave residue that can cloud or dull the floor appearance. | 55 Gallon | 29644 | 1/cs |
| | | 2.5 Gallon | 59865 | 2/cs |
| | | 2 Liter | 3L, 3H | 6/cs |

Greener Solutions

The polyester fiber used to make a range of floor pads contains a minimum of 50% post-consumer recycled content. The recycled polyester fiber used is third-party certified for post-consumer recycled content.

3M™ Easy Trap Duster contains a minimum of 60% recycled content.

3M™ Brand Floor Pad families include: 3200, 3300, 3400, 3500, 5000 and 5100.

Product Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty, Limited Remedy and Disclaimer: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. User is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application. Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.



Commercial Solutions Division

3M Center, Building 220
St. Paul, MN 55144-1000
1-866-649-1973
3M.com/Resilient

3M, Scotchgard and the Plaid Design are trademarks of 3M. NFSI logo is a registered trademark of National Floor Safety Institute. ISSA is a registered trademark of ISSA. Used under license in Canada. Please recycle. Printed in U.S.A. © 3M 2015. All rights reserved. 78-8134-0558-2

Scotchgard™ Resilient Floor Protector

The next generation
of resilient floor protection
has arrived.

For a floor that can stand up to almost anything.



Tougher protection, fewer chemicals for a more durable, sustainable future.

**Presenting Scotchgard™ Resilient Floor Protector.
For a floor that can stand up to almost anything.**

**Performance.
Productivity.
Sustainability.**

It's all in the bag. (Or 2.5 gallon jug, if you prefer.)


- Superior gloss retention, black mark resistance and easier black mark removal*
- Superior soil resistance*
- Four times more durable than leading competing traditional acrylic floor finishes**
- Certified by the National Floor Safety Institute (NFSI) as providing "High Traction"
- May be used as a topcoat over traditional acrylic if additional gloss is desired
- Environmentally preferable, low odor & Zinc free***
- Superior hand sanitizer resistance*
- Builds initial hardness 40% faster than leading competing traditional acrylic floor finishes
- ISSA 2014 Innovation Award Winner

Less maintenance. Fewer chemicals.


Traditional floor finish can quickly become dull and dirty, requiring regular scrubbing or stripping to maintain its appearance. But once your floors are protected with Scotchgard™ Resilient Floor Protector, you can easily maintain their beauty by cleaning daily with 3M™ Neutral Cleaner Concentrate and occasional burnishing with the long-lasting 3M™ Tan Burnish Pad 3400.

- Improve productivity and reduce operational costs when used as a two-coat protector system
- Designed for use with Scotchgard™ Resilient Floor Protector, 3M™ Neutral Cleaner Concentrate leaves floors bright and clean without soapy residues that can dull the finish
- For best results, use the 3M Tan Burnish Pad 3400 or other 3M Burnishing pads to restore gloss quickly, remove scuffs and black marks
- May be applied with the 3M™ Easy Shine System or traditional mop and bucket
- Available in 2.5 gallon jug to refill one gallon pouch or for use with mop and bucket application

Increase productivity and cut chemical use



62% less installation time*



Unique and patented 3M Nano-Technology

*When compared to leading competing traditional acrylic floor finishes
**When compared to leading competing traditional acrylic floor finishes, based on 8-hour exposure
***Based on coating abrasion data (7-day cured) using Schieffer machine



Certified by the National Floor Safety Institute (NFSI) as providing "High Traction."

Scotchgard™ Resilient Floor Protector
Winner of the ISSA 2014 Innovation Award

