



# Paintable Undercoating Pouch, 5.5 Fl. Oz. 08747

Technical Data Sheet

June 2020

| 3M Part No.(s) | 3M Part Descriptor(s)                         |
|----------------|---|
| 08747          | 3M™ Paintable Undercoating Pouch, 5.5 Fl. Oz. |

**Product Description** 3M™ Paintable Undercoating Pouch 5.5 Fl. Oz. (PN 08747) is a rubberized undercoating designed to protect lower auto body panels and undercarriages from damage such as stone chipping, and prevent subsequent corrosion damage to bare metal. This coating is applied over clean bare metal, or primer coated surfaces and may be top coated with common automotive paint systems.

## Features

- Unique Pouch Package
- Corrosion Resistant Formula
- Automotive Paint Compatibility

## Typical Physical Properties

**Note:** The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

|                                   |                                      |
|-----------------------------------|--------------------------------------|
| <b>Container</b>                  | 5.5 fl. oz. (163 mL) Poly/Foil Pouch |
| <b>Base</b>                       | Rubber Copolymer                     |
| <b>Density lbs/Gallon (Appx.)</b> | 7.2                                  |
| <b>Color</b>                      | Black                                |
| <b>Consistency</b>                | Thick Liquid                         |
| <b>Viscosity</b>                  | 4,500 - 7,000 cps                    |
| <b>Solvent</b>                    | Toluene, VM&P Naphtha                |
| <b>Service Temperature</b>        | -20°F to 200°F (-29°C to 93°C)       |

# 3M™ Paintable Undercoating Pouch, 5.5 Fl. Oz.

## 08747

---

**Product Uses** Under body protection for wheel housing, frame rail, floor pan, lower rocker panel areas of auto bodies. This coating does not contain a UV screener and should not be used on top surfaces exposed to direct sunlight unless it is top coated with an appropriate paint. May be applied to clean, dry bare metal, contains corrosion inhibiting chemistry.

**For professional use only. Not intended for retail sale.**

---

**Performance Properties** **Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.**

**Paint Time:** 1 - 2 medium Coats @ 75°F (24°C) 30 - 60 minutes  
2 - 3 medium heavy Coats @ 75°F (24°C) 120 - 150 minutes

- Allow flash time between coats.
- May be applied over bare metal or prepared primer or paint.
- **DO NOT** solvent wipe this product prior to paint application.

If painting after 24 hours, scuff lightly before applying top-coats.

**Coverage:** 1 coat 50% overlap 15 sq. ft. (1.4 sq. meter)

- 
- Directions for Use**
1. **Preparation:** Clean all bare metal (welds, etc.) using an appropriate abrasive followed by cleaning with a VOC compliant surface cleaner. **(Do not apply acid etch primers in direct contact with 3M™ Paintable Undercoating – 5.5 fl oz PN 08747)**
  2. If applied over primer scuff the primer using 3M™ Scotch-Brite™ scuff pad (maroon), followed by cleaning with a VOC compliant surface cleaner.
  3. Remove 3M™ Paintable Undercoating Pouch from shipper and knead the pouch between your fingers to “break up” any solids that may have settled.
  4. Insert the PN 08747 5.5 fl oz Pouch into the 3M™ PPS™ H/O Pressure Cup (Mini) (PN 16121) and attach the Retaining Collar.
  5. Using a PPS shaker collar position the cup/pouch assembly into a paint shaker and shake for one to two minutes or shake well by hand for one to two minutes. Next puncture the liner inside the PPS lid using a sharp implement (a pencil works well for this).
  6. Attach the included red colored 3M™ Accuspray™ 2.0 mm Atomizing head to the 3M™ Accuspray™ Pressurized Spray Gun Model HGP20 (PN 16587), attach the cup assembly to the atomizing head and attach the pressure cup air feed tube to the gun body pressure side port (see directions for use contained with PN 16587 spray gun for details).
  7. Attach an air hose to the spray gun air control valve inlet and set full trigger pressure to 10 to 15 PSI (this spray gun is designed to function well at low pressure).

# 3M™ Paintable Undercoating Pouch, 5.5 Fl. Oz.

08747

---

**Directions for Use** 8. Spray a small test panel adjusting air inlet pressure and fluid needle adjustment to  
*(continued)* achieve desired texture and coverage.

9. Using the settings from the test apply the desired number of coats to achieve coverage and texture (when desired), allow to dry 30 minutes to 2 hours, dependent upon coating weight, ambient temperature and humidity

\*Immediately clean up over spray with a VOC compliant cleaner.

## IF PAINTING SEE INSTRUCTIONS BELOW

10. After coating dries it may be DA or hand sanded to remove excess texture or overspray prior to top coating using grade P400 to P800 abrasive. After 24 hours you must scuff or sand the coating using grade P400 to P800 abrasive, or 3M™ Scotch-Brite™ scuff pad (grey).

\***Note:** To smooth blend edges DA sand the blend using grade P1000 to P3000 3M™ Trizact™ abrasive damp.

11. Apply topcoats or sealer following your paint system guidelines.

\*To store any unused product cap the pouch outlet using a 3M™ PPS™ cap and store in an approved paint storage area.

---

## Applications

Applications include areas requiring undercoating protection to seal surfaces from environmental conditions and protect from stone chips. Panels such as wheel housing, frame rail, floor pan, and other body under side and internal panels are common auto body applications. This product is not designed to protect from UV exposure.

---

## Storage and Handling

Store at room temperature. Rotate stock on a “first-in, first-out” basis. When stored at the recommended conditions in original, unopened containers, this product has a shelf life of 12 months. Always use in a well-ventilated area.

# 3M™ Paintable Undercoating Pouch, 5.5 Fl. Oz.

08747

---

## Precautionary Information

Before using this product, please reference Product Label and/or Safety Data Sheet for Health and Safety Information. Note: Laws controlling the acceptable amounts of Volatile Organic Compounds (VOC's) vary by state, and in some cases by locality. For surface preparation and clean-up activities, consult federal, state and local regulations regarding use of products containing VOCs in your area.

---

## Technical Information

The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third-party intellectual property rights is granted or implied with this information.

---

## Product Selection and Use

Many factors 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product in accordance with all applicable instructions and with appropriate safety equipment, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

---

## Warranty, Limited Remedy, and Disclaimer

Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement or repair of the 3M product or refund of the purchase price. Warranty claims must be made within one (1) year from the date of 3M's shipment.

---

## Limitation of Liability

Except for the limited remedy stated above, and except to the extent prohibited by applicable law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

---

## Disclaimer

3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and other limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, death, or property damage. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit [www.3M.com](http://www.3M.com).<sup>[1]</sup>.



### Automotive Aftermarket Division

3M Center, Building 223-6S-  
0& St. Paul, MN 55144-1000  
1-877-666-2277 (1-877-MMM-CARS)  
[www.3MCollision.com](http://www.3MCollision.com)

3M, PPS, Accuspray, Scotch-Brite and Trizact are trademarks of 3M Company.  
Printed in U.S.A.

©3M 2020 P.N. 08747 (6/20)