

3M Science.
Applied to Life.™

3M™ Rugged Comfort
Half Facepiece
Reusable Respirator
6500 Series

Comfort and
convenience in
harsh environments

6500 Series. An easy choice for a tough world.

When shifts are long and conditions are challenging, your people will appreciate having the 3M™ Rugged Comfort Half Facepiece Reusable Respirator 6500 Series. With 3M's Quick Latch drop-down mechanism and Cool Flow™ valve, it's easy on, easy off and comfortable.



red dot award 2015
best of the best

▶ Convenient Quick Latch Drop-Down Mechanism

- Easy on and off as you move in and out of contaminated areas
- No need to remove hard hats or faceshields when lowering and raising the respirator



QUICK LATCH CLOSED

PULL UP ON LATCH

QUICK LATCH OPEN

PULL DOWN ON LATCH

To open Quick Latch: Grasp the latch at chin level and pull up. *To close Quick Latch:* Grasp the facepiece with your thumb on the bottom of the facepiece and your first two fingers on top of the latch. Place the facepiece over your nose and mouth while pushing down on the latch.

▶ Comfortable, Durable Silicone Face Seal

- 3M's lightest silicone facepiece, the 6500 Respirator Series provides comfort and stability with a soft, stable face seal
- Resilient silicone material keeps its shape in high-heat environments, which can help extend product life

▶ 3M™ Bayonet Connection


- Compatible with all 3M™ bayonet-style cartridges and filters (see back for listing of products)

▶ Adjustable Head Harness Assembly

- Optimum fit and comfort with three-size adjustable head cradle
- Long-lasting polyester/spandex straps

▶ Low-Profile Design for Compatibility

- Compatible with most welding/grinding shields
- Advanced half facepiece design for a wide field of view
- Simplified cleaning and maintenance with fewer parts and crevices



▶ Cool Flow™ Valve

- Enhanced comfort by reducing heat and moisture build-up
- Easier breathing with unique valve design
- Valve cover design directs exhaled breath and moisture downward



6500 QL Respirator, shown

6500 Series

3M™ Rugged Comfort Half Facepiece Reusable Respirator

Standard models

6501	Small
6502	Medium
6503	Large



Quick Latch models

6501QL	Small
6502QL	Medium
6503QL	Large



For more information

Technical Service: 1-800-243-4630
Customer Service: 1-800-328-1667
3M.com/workersafety



WARNING

This respirator helps reduce exposures to certain airborne contaminants. Before use, the wearer must read and understand the User Instructions provided as a part of the product packaging. Follow all local regulations.

In the U.S., a written respiratory protection program must be implemented meeting all the requirements of OSHA 1910.134, including training, fit testing and medical evaluation. In Canada, CSA standard Z94.4 requirements must be met and/or requirements of the applicable jurisdiction, as appropriate. Misuse may result in sickness or death. For proper use, see package instructions, supervisor, or call 3M PSD Technical Service in USA at 1-800-243-4630 and in Canada at 1-800-267-4414.



Personal Safety Division

3M Center, Building 235-2W-70
St. Paul, MN 55144-1000

Phone 1-800-328-3908
Fax 1-800-328-3909
Web 3M.com/workersafety

3M PSD products are for occupational use only

Inhaling particulates, gases and vapors is a serious hazard. Still, the job has to be done. That's why workforces rely on 3M™ Reusable Respirators and 3M™ Filters and Cartridges to help keep them working safely and comfortably.

Filters

3M™ Particulate Filter 2097, P100 with Nuisance Level Organic Vapor*

3M™ Particulate Filter 2091, P100

3M™ Advanced Particulate Filter 2291, P100

3M™ Advanced Particulate Filter 2297, P100 with Nuisance Level Organic Vapor*

3M™ Particulate Filter 5N11, N95



2097

2091

2291

2297

5N11

*Nuisance level refers to concentrations not exceeding the OSHA PEL or applicable government occupational exposure limits, whichever is lower.

Selected Cartridges

3M™ Organic Vapor Cartridge 6001

3M™ Organic Vapor Cartridge with Service Life Indicator 6001i**

3M™ Organic Vapor/Acid Gas Cartridge 6003

3M™ Organic Vapor Cartridge/P100 Particulate Filter 60921

3M™ Organic Vapor/P100 Particulate Service Life Indicator Cartridge 60921i**

3M™ Organic Vapor/Acid Gas Cartridge/P100 Particulate Filter 60923



6001 OV,
6001i OV

6003 OV/AG

60921 OV/P100,
60921i OV/P100

60923 OV/AG

Service Life Indicator,
available on 6001i and
60921i models**



Simple Indicator Bar



**Please see the 6001i and 60921i User Instructions or the 3M™ Select and Service Life Software (3M.com/ServiceLifeSoftware) to determine if the end of service life indicator (ESLI) is applicable for your work environment.

3M bayonet connection for compatibility with all bayonet-style 3M cartridges and filters 2000, 5000, 6000 and 7000 Series.

For a full listing of all 3M™ Cartridge and Filter options, contact your 3M representative or visit us at 3M.com/workersafety.

3M and Cool Flow are trademarks of 3M Company. Used under license in Canada. Please Recycle. Printed in the U.S.A.
© 2013, 2016, 3M. All rights reserved. 70-0716-2625-6