The power of peroxide

to keep your facilities clean.

3M[™] Peroxide Cleaner Concentrate is a versatile, no-rinse cleaner that brings the power of peroxide to most washable hard surfaces and carpets. Newly formulated to be "greener" and a more effective cleaner. Now Green Seal[™] GS-37 certified when sold in the 3M[™] Twist 'n Fill[™] Cleaning Chemical Management System, which is designed for accurate, easy, automatic dispensing in a two liter bottle. Also available separately in a bulk one gallon bottle of concentrate.



Approved by Facility Managers. Certified by Green Seal

A greener, better performing peroxide.

Put the "green" clean power of peroxide to work for you on all surfaces with 3M[™] Peroxide Cleaner Concentrate. It provides excellent removal of soil from most carpets and hard, nonporous surfaces.

Carpets

Features

- No rinsing necessary
- Leaves no messy residue behind
- Green Seal[™] GS-37 certified (3M[™] Peroxide **Cleaner Concentrate** 34L/H only)
- · Readily biodegradable per Green Seal[™] GS-37 standard
- Restrooms
- grout Removes hard-water build
- · For mirrors, sinks, glass, windows, bathroom

Hard Floors

- Does not dull or damage most floor surfaces
- For ceramic, terrazzo and vinyl composite tiles
- Use with 3M[™] Easy Scrub System and 3M[™] Easy Scrub Express System



The 3M[™] Twist 'n Fill[™] System makes dispensing easy.

The 3M[™] Twist 'n Fill[™] System is designed to accurately mix and dispense 3M[™] Peroxide Cleaner Concentrate to help ensure consistent, effective cleaning performance. It's great for filling portable containers, spray bottles and buckets.

- Unique bottle and cap design lets you interchange chemicals in seconds
- Very compact—fits in most closets
- · Easy to use-just insert bottle, twist and fill
- Integral air gap prevents chemical backflow
- Flexible—mount on wall or, for portability, on cart or cleaning equipment
- Automatic 3-gallon per minute dispense rate for bucket applications; 1-gallon per minute for trigger spray bottle applications



3M[™] Peroxide Cleaner Concentrate 34I /H is Green Seal™ GS-37 Certified



Ordering Information

Prod No.	Description	Size	UPC Number	Ready to Use Gallons per Bottle	ltems/ Case	Stock Number
34L*	3M [™] Peroxide Cleaner Concentrate 34L, Gray Cap	2 Liter	500-48011-59749-7	53	6/cs	70-0715-9554-3
34H*	3M [™] Peroxide Cleaner Concentrate 34H, Gray Cap	2 Liter	500-48011-59288-1	53	6/cs	70-0715-9565-9
34L*	3M [™] Peroxide Cleaner Concentrate 34L, Black Cap	2 Liter	500-48011-59779-4	53	6/cs	70-0715-9566-7
34H*	3M [™] Peroxide Cleaner Concentrate 34H, Black Cap	2 Liter	500-48011-59782-4	53	6/cs	70-0715-9567-5
59979	3M [™] Peroxide Cleaner Concentrate	Gallon	500-48011-59979-8	101	4/cs	70-0715-9580-8

*This product meets the Green Seal™ GS-37 standard based on effective performance. concentration of product, minimized/recycled packaging and protective limits on VOCs and human and environmental toxicity. Skin/eye damage met requirements at the as-used dilution, as specified for closed dilution systems. www.GreenSeal.org



Building and Commercial Services Division

3M Center St. Paul, MN 55144-1000 www.3M/facility

3M and Twist 'n Fill are trademarks of 3M Used under license in Canada Green Seal and the Green Seal certified mark are trademarks of Green Seal. Inc. Please recycle. Printed in U.S.A. © 3M 2013. All rights reserved. 78-8134-0573-1

Product Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty, Limited Remedy and Disclaimer: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. User is solely responsible for evaluating Control can anext the use and performance of a sim product in a particular application. User is solver responsible for evaluating the SM product and determining whether it is fit for a particular purpose and suitable for user's method of application. Unless an additional warranty is specifically stated on the applicable SM product packaging or product literature, 3M warrants that each SM product meets the applicable SM product specification at the time 3M ships the product. SM MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLED WARRANTY OR CONDITION OF MERCHANTIBLITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE, If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, whether direct, indirect, spe negligence or strict liability.

- Cleans and brightens Effective for spot cleaning
- up and soap scum
- fixtures and floors