



Technical Data

3M™ Glass Cleaner and Protector Concentrate 17A and 17L



Description

3M™ Glass Cleaner and Protector Concentrate 17A is a concentrated product to be diluted and dispensed using the 3M™ Flow Control System Wall Mount Dispenser or the 3M™ Flow Control System Portable Dispenser.

3M™ Glass Cleaner and Protector Concentrate 17L is a concentrated product to be diluted and dispensed using the 3M™ Twist 'n Fill™ Cleaning Chemical Management System.

3M™ Glass Cleaner and Protector Concentrate 17A and 17L are made with a streak-free, fast-drying formula. After repeated use*, 3M's Scotchgard™ Technology provides a protective barrier, making fingerprints, lipstick, makeup, lotion, hairspray, food grease, permanent marker, hard water and soap spots faster and easier to clean. Treated glass has an attractive streak-free shine. 3M™ Glass Cleaner and Protector also reduces fogging on windows and mirrors due to humid conditions.

Special Features

- Automatic dispensing eliminates measuring and mixing and helps ensure accurate dilutions
- Green Seal™ GS-37 Certification
- Streak-free cleaning
- Non-ammoniated formula

- Works like a heavy-duty glass cleaner without the high levels of solvent or ammonia
- Keeps glass looking clean longer
- Dries faster than other glass cleaners tested, saving time
- U.S. patent pending

Applications

- Interior windows
- Mirrors and other mirrored surfaces
- Glass
- Uncoated granite, ceramic and porcelain
- **NOT** for automotive, inside aquariums or eyewear use

*For best results, use exclusively on non-coated silica based substrates.

Packaging

3M™ Glass Cleaner and Protector Concentrate 17A

- 0.5-gallon bottle
- 4 bottles per case

Each 0.5-gallon bottle typically yields 40 ready to-use gallons (1:75 dilution ratio)

3M™ Glass Cleaner and Protector Concentrate 17L

- 0.528-gallon bottle
- 6 bottles per case

Each 0.528-gallon bottle typically yields 40 ready to-use gallons (1:82 dilution ratio)

General Use Directions

Dispense 3M™ Glass Cleaner and Protector Concentrate 17A using the 3M™ Flow Control System Wall Mount Dispenser or 3M™ Flow Control System Portable Dispenser into a properly labeled spray bottle.

Dispense 3M™ Glass Cleaner and Protector Concentrate 17L using the 3M™ Twist 'n Fill™ Cleaning Chemical Management System into a properly labeled spray bottle.

1. Spray the ready-to-use glass cleaner into a clean cloth or onto the surface.
2. Wipe the surface with a clean cloth or paper towel until clean and dry.
3. When using a squeegee, apply cleaner, scrub to loosen soil, then squeegee.

Improper use or dilution may result in altered product performance and may increase the risk of health effects.

*For best results, use exclusively on non-coated silica based substrates.

Personal Protective Equipment (PPE)

Recommendation: Refer to SDS for specific PPE guidance.

Ready-To-Use: When used as directed and diluted with a 3M chemical dispensing system: Eye or skin exposure not significant enough to require protection.



This product meets Green Seal™ Standard GS-37 based on effective performance, concentrated volume, minimized/recycled packaging, and protective limits on: VOCs and human & environmental toxicity. GreenSeal.org.



Waste Disposal Method: Dispose of contents/container in accordance with applicable local/regional/national/international

regulations. Rinse empty container with water and recycle (No.2 HDPE).

NOTE:

Refer to product Safety Data Sheet for specific physical properties, health hazard, first aid and precautionary information.

▪ 28-9276-8
(Concentrate)

▪ 28-9283-4
(RTU)

3M Branch Sales Offices

ANCHORAGE

11151 Calaska Circle
Anchorage, AK 99515

Telephone: 907/522-5200
Facsimile 907/522-1645

HONOLULU

4443 Malaai Street
Honolulu, HI 96818
Mail to: P.O. Box 30048
Honolulu, HI 96820

Telephone: 808/422-2721
Facsimile 808/422-9557

CONTINENTAL UNITED STATES

Customer Service Department
3M Center Building 223-5S-07
St. Paul, MN 55144-1000

Order Entry 1-800-852-9722
Facsimile 1-800-447-0408

CANADA

1840 Oxford Street East
London, Ontario, Canada
N5V 3G2

Mail to: P.O. Box 5757
London, Ontario, Canada
N6A 4T1

Telephone: 800/364-3577
Facsimile: 800/479-4453

Important Notice to User

Technical Information: The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

Product Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty and Limited Remedy: 3M warrants that each 3M product will be free from defects in material and manufacture for 90 days from the date of purchase from 3M's authorized distributor. 3M MAKES NO OTHER EXPRESS OR IMPLIED WARRANTIES, INCLUDING ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If a 3M product does not conform to this warranty, the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price. **Limitation of Liability:** Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal or equitable theory asserted.



Commercial Solutions Division

St. Paul, MN 55144-1000
1-800-852-9722
www.3M.com/facility

3M and Twist 'n Fill are trademarks of 3M Company.
Green Seal and the Green Seal Certified mark are trademarks of Green Seal, Inc.
Used under license in Canada.
© 3M 2015. All rights reserved.
Asset ID 741501