



Double Coated Tape 90775

Product Information

May 2013

Supersedes: New

Product Description

3M™ Double Coated Tape 90775 has a cellulose tissue carrier. The adhesive shows good resistance to high temperatures and chemicals.

Properties

The tissue carrier gives the tape improved handling characteristics during converting and application compared to transfer adhesives.

Construction

Product	Adhesive thickness frontside	Carrier	Adhesive thickness backside	Liner	Total thickness without liner
990775	0,075 mm	Translucent Tissue	0,075 mm	120 g/qm, 0,140 mm Paper polycoated White printed logo	0,150 mm

The frontside adhesive is exposed when the roll is unwound.
The backside adhesive is exposed when the liner is removed.
The calculation of the adhesive thickness is based on a density of 1,012 g/cm³.

Performance Characteristics

Adhesion after 15 Min at RT, FINAT FTM 1, 180° pullback with 300 mm/Min. 0,05 mm PET	Stainless Steel Polypropylene ABS Polycarbonate	17,0 N/25 mm 6,0 N/25 mm 17,0N/25 mm 17,9 N/25 mm
Adhesion after 72 h at RT, FINAT FTM 1, 180° pullback with 300 mm/Min. 0,05 mm PET	Stainless Steel Polypropylene ABS Polycarbonate	17,2 N/25 mm 6,3 N/25 mm 18,8 N/25 mm 19,6N/25 mm
Shear Strength at RT, FINAT FTM8, 25,4 mm * 25,4 mm area, with PET 0,05 mm, weight 1000 g. at RT.	Stainless Steel	10 000 Min

Temperature Resistance

Long term (days, weeks): 90°C
Short term (minutes, hours): 150°C

Storage

Store in cool and dry conditions at room temperature

Shelf Life

2 years from date of manufacture

Precautionary Information

Refer to product label and Material Safety Data Sheet for health and safety information before using the product.

For information please contact your local 3M Office.

www.3M.com

For Additional Information

To request additional product information or to arrange for sales assistance, please see below for contact details.

Important Notice

All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method or application. All questions of liability relating to this product are governed by the terms of the sale subject, where applicable, to the prevailing law

Values presented have been determined by standard test methods and are average values not to be used for specification purposes. Our recommendations on the use of our products are based on tests believed to be reliable but we would ask that you conduct your own tests to determine their suitability for your applications. This is because 3M cannot accept any responsibility or liability direct or consequential for loss or damage caused as a result of our recommendations

3M is a trademark of the 3M Company.

**3M Svenska AB
Industri**

Bollstanäsvägen 3
191 89 Sollentuna
Tel: 08-92 21 00
Fax: 08-92 22 88
E-post:
kundservice@mmm.com
www.3M.se/tejp

**3M a/s
Industri**

Hannemanns Allé 53
2300 København S
Tlf.: 43 48 01 00
Fax.: 43 20 15 65
E-mail:
dkindustri@mmm.com
www.3Mindustri.dk

**3M Norge AS
Avd. Industri**

Hvamveien 6
2013 Skjetten
Tel: 0 63 84
Fax: 63 84 17 88
E-post:
Kundeservice@mmm.com
www.3M.no/tape

**Suomen 3M Oy
Teollisuustuotteet**

PL 600
Keilaranta 6
02151 Espoo
Puh: 09-525 21
Fax: 09-525 2279
<http://www.3M.fi/teollisuus>