



Scotch[®] Filament Tape 898MSR

Product Data Sheet

August 2013
Supersedes: New

Product Description

Scotch Filament Tape 898MSR is a high-performance transparent filament tape reinforced along its length with continuous fibreglass-yarn filaments, which gives the tape a very high tensile strength. The clear polyester backing provides excellent abrasion, moisture and scuff resistance. The adhesive is a modified synthetic rubber resin adhesive specifically formulated to provide very good oily metal adhesion performance. The adhesive also provides a balanced performance having high adhesion and long term holding power for a variety of metal working applications.

Key Features

- Abrasion and moisture resistant.
- Good oily metal adhesion.
- High tensile strength.
- Allows printing and illustrations to be seen through the tape.
- High shear and good initial adhesion.
- Good aging.
- Good protection of filaments and adhesive to provide longer package life.
- Assures maximum package performance for limited outdoor use.
- Saves time through ease of dispensing and handling when used with a 3M dispenser.
- Provides advertising and warning capability when printed.
- Low unit costs by using less tape on applications where high tensile strength is one of the main requirements.
- Good holding, with minimum amount of tape, under a wide range of application conditions.
- Holds instantly with minimum rubdown.
- Boxes remain securely closed through normal warehouse time cycles.

Physical Properties

Adhesive Type	Rubber Resin (synthetic)
Backing	Polyester
Reinforcement	Glass yarn
Colour	clear

Performance Characteristics

	898MSR
Adhesion to Steel (Afera 5001)	8.3 N/cm
Tensile Strength (Afera 5004)	820 N/cm
Elongation (Afera 5004)	7%
Total Thickness (Afera 5006)	0.182mm

Storage	Store behind present stock. Store in a clean, dry place. Temperature of 4-26°C and 40-50% relative humidity are recommended. Rotate your stock.
Shelf Life	To obtain best performance, use this product within 18 months from date of dispatch.
For Additional Information	To request additional product information see address below.
Important Notice	<p>All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method or application.</p> <p>All questions of liability relating to this product are governed by the terms of the sale subject, where applicable, to the prevailing law</p>

Values presented have been determined by standard test methods and are average values not to be used for specification purposes. Our recommendations on the use of our products are based on tests believed to be reliable but we would ask that you conduct your own tests to determine their suitability for your applications. This is because 3M cannot accept any responsibility or liability direct or consequential for loss or damage caused as a result of our recommendations

3M is a trademark of the 3M Company.

3M United Kingdom PLC 3M House, 28 Great Jackson Street, Manchester, M15 4PA	Product Information : Tel 0870 60 800 50 Fax 0870 60 700 99	3M Ireland Limited The Iveagh Building The Park, Carrickmines Dublin 18, Ireland	Customer Service : Tel (01) 280 3555 Fax (01) 280 3509
--	---	--	--