


3M™ Fasara™ Glass Finishes Pixela (SH2FGPX)

Specification Sheet

Release A, Effective August 2013



Product Description


3M™ Fasara™ Glass Finishes – Pixela (the "Film" or "Product") is a decorative glass and window film that can be used to control both light and privacy through a building's interior glass.

Specifications

Product Code	SH2FGPX
Product Family	Border-Horizontal
Film Type	Polyester
Adhesive Type	Pressure-sensitive
Usage	Interior
Width	50 inch (1270mm)
Length	98.4 linear feet (30m)
Shading Coefficient (%)*	0.78
Visible Light Reflectance (%)*	18
Visible Light Transmittance (%)*	60

* As measured on 6mm clear glass.

Pattern Scale



Fasara - Pixela

Product Detail

Manufacturer Detail

3M™ Fasara™ Glass Finishes – Pixela is manufactured by the 3M Company.

UV Resistance

3M™ Fasara™ Glass Finishes – Pixela blocks at least 99% of UV light to reduce the discoloring (fading caused by sunlight) of furniture and other items that is mainly caused by UV light.

Fire Rating

The Product was tested according to ASTM E84 and is classified as Class A as defined in NFPA 101: Life Safety Code®.

Related Products

Pixela is the same color as Luce, which is a solid color film.

Installation and Warranty

Installation

To install the Product, refer to the 3M™ Fasara™ Glass Finishes Installation Guide.

Warranty SH2FGPX

For warranty information, refer to the 3M™ Fasara™ Glass Finishes Warranty Document.

Product Distribution and Contact Information

Distribution

3M™ Fasara™ Glass Finishes – Pixela is available through qualified dealers and distributors.

Samples provided upon request.

Contact Information

Contact 3M Architectural Markets at 1-888-650-3497, or www.3MArchitecturalMarkets.com.

3M Architectural Markets 3M U.S.

3M Center
Building 220-7W-07
St. Paul, MN 55144-1000
1-888-650-3497
3MArchitecturalMarkets.com

3M and Fasara are trademarks of 3M Company. © 3M 2013. All rights reserved. Please recycle.

