

3M™ Dyneon™ Fluoroelastomer FE 5620Q

Features and Benefits

- Composition: di-polymer of vinylidene fluoride and hexafluoropropylene
- Low viscosity version of FE 5640Q
- Process targets: injection and transfer molding, extrusion and calendaring
- Improved scorch resistance at high molding temperatures
- Proprietary incorporated cure technology
- Excellent mold release – can be used in automated injection molding equipment
- Improved cure technology resulting in more consistent part size from successive molding cycles
- Clean running
- Compounds prepared from FE 5620 can be formulated to meet Mil-R-83248

Note: Data in this document are not for specification purposes.

Typical Properties

Property	
Fluorine Content	65.9%
Specific Gravity	1.80
Color	Opaque Off-White
Solubility	Ketones and Esters
Mooney Viscosity ML 1 + 10 @ 121°C (250°F)	Approximately 23

Product Description

3M™ Dyneon™ Fluoroelastomer FE 5620Q can be compounded using standard water cooled internal mixers or two-roll mills with standard fillers and ingredients utilized in typical fluoroelastomer formulations. The “dry” ingredients should be blended before adding to the masticated gum. For best results, FE 5620Q should be banded on the mill several minutes prior to adding the blended dry ingredients. Once mixed, the compounded stocks display excellent processing characteristics and storage stability.

Product Form

FE 5620Q is packaged in slab form and is available in a returnable bulk shipping container system for 1,320 lbs (600 kg) of material. The bulk container system is comprised of 48 individual polyethylene bags containing 27.5 lbs (12.5 kg) of product. Smaller quantities are available in 55.1 lb (25.0 kg) boxes.

Safety/Toxicology

When recommended handling precautions are followed, 3M fluoroelastomers present no known health hazards. General handling precautions include: (1) Store and use all 3M fluoroelastomers only in well ventilated areas. (2) Do not smoke in areas contaminated with dust from 3M fluoroelastomers. (3) Avoid eye contact. (4) After handling 3M fluoroelastomers wash any contacted skin with soap and water.

Potential hazards, including evolution of toxic vapors, do exist during compounding or processing under high temperature conditions. Before processing 3M fluoroelastomers, consult the product MSDS (Material Safety Data Sheet) and follow all label directions and handling precautions. You should also read and follow all directions from other compound ingredient suppliers. Material Safety Data Sheets on 3M products are available from your 3M Sales Representative.

ISO 9001

All 3M fluoroelastomers are manufactured at ISO 9001 registered facilities. Our product realization process is also ISO 9001 registered.



Typical Properties of Vulcanizate

Compound	phr
FE 5620Q	100
N990 MT Black	30
MgO	3
Ca(OH) ₂	6

Note: Data in this document are not for specification purposes.

**Typical Rheological Properties (ASTM D5289)
Moving Die Rheometer (MDR)
100 cpm, 0.5° Arc, 6 Minutes**

Temperature	177°C (350°F)	200°C (392°F)
ML, Minimum Torque, Inch-lb (dN m)	0.8 (0.9)	0.5 (0.6)
t ₂ , Time to 2 Inch-lb Rise from Minimum – Minutes	2.2	0.8
t ₅₀ , Time to 50% Cure – Minutes	2.7	0.9
t ₉₀ , Time to 90% Cure – Minutes	3.7	1.1
MH, Maximum Torque, Inch-lb (dN m)	22.1 (25.0)	21.0 (23.7)

Typical Physical Properties

Press Cure 5 Minutes @ 177°C (350°F)
Post Cure 24 Hours @ 260°C (500°F)

Tensile, psi (Mpa)	2240	(15.4)
100% Modulus, psi (Mpa)	950	(6.5)
Elongation at Break, %	195	
Hardness, Shore A [ASTM D2240]	77	

Compression Set, (ASTM D395 Method B, O-rings -214)

70 Hours @ 200°C (392°F) – % Set	13
----------------------------------	----

Low Temperature Properties

TR10 [ASTM D1329]	-18°C (0°F)
-------------------	-------------

Warranty, Limited Remedy, and Disclaimer: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. User is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application. Unless a different warranty is specifically stated in the applicable product literature or packaging insert, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except where prohibited by law, 3M will not be liable for any loss or damages arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

Technical Information: Technical information, recommendations, and other statements contained in this document or provided by 3M personnel are based on tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed. Such information is intended for persons with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

