


Precision Polishing with Superior Performance Every Time.



3M™ Microfinishing Film Product Portfolio

Since the introduction of 3M™ Microfinishing Film decades ago, 3M has continued to provide consistent quality and the highest performance, while adding the features for our customers' benefit detailed below.

Increase productivity and reduce errors with:

- Colored film by grade
- Side of roll printing
- Shrink-wrapped rolls
- Roll-to-roll splicing tape
- Width by core size
- End of roll marking
- Long length rolls

3M™ Microfinishing Films

Product	Mineral	Backing Caliper (0.001")	Backside	Grades (Microns)												
				9	15	20	30	40	45	50	60	74	80	100	125	
372L	Aluminum Oxide	5	Type S	●	●	●	●	●			●	●		●	●	
372L Type 2* (colored)	Aluminum Oxide	5	Type S		●	●	●	●				●		●	●	
373L	Aluminum Oxide	5	Type Q	●	●	●	●	●			●	●		●	●	
373L Type 2* (colored)	Aluminum Oxide	5	Type Q		●	●	●	●				●		●	●	
382L Type 2 (colored)	Aluminum Oxide	6	Type S		●	●	●	●				●				
362L	Aluminum Oxide	3	Type S	●	●	●	●	●			●	●				
272L**	Aluminum Oxide	5	Type S	●	●	●	●	●			●	●		●	●	
472L	Silicon Carbide	5	Type S		●	●	●	●				●				
675L	Diamond	5	Type S	●		●	●			●						
	Diamond	6	Type S									●				●

*Suggest to specify the 372L or 373L Type 2 (colored) film whenever possible to assist with Error-proofing.

**European Lead Product. Plus wide rolls and belts globally.

3M Abrasives Systems Division
3M Center, Building 223-6S-03
St. Paul, MN 55144-1000
1-866-279-1235
www.3M.com/abrasives

Please recycle. Printed in U.S.A. © 3M 2013.
All rights reserved. 61-5002-8357-9

