



3M™ MCS™ Warranty

For EFI™ VUTEk® GS3250LXr, GS5250LXr*, and GS5500LXr* Printers including Pro and UltraDrop Series
Using EFI™ VUTEK® GSLXr 3M™ Superflex UV Ink (*Warranty includes white ink)

IMPORTANT! Only graphics manufacturers having a current Certificate of 3M™ MCS™ Warranty are eligible to extend this Warranty to their customers. Finished Graphics Warranty Period is stated in years for Vertical Graphics made with 3M Film, Inks and Graphic Protection using Approved Printers. Refer to the film's Product Bulletin for details and full trademark names, which can be viewed online by clicking the blue film number links. Also review the notes at the end of the matrix.

Film	Notes	Graphic Protection	VEH	OUT	W/R	IN
2 MIL						
IJ170Cv3	D	8518, 8519, 8520, 8915	7	3	2	5
		8528	7/2	3	2	5
		8548G, 8549L	7/2	3	2	5
		8900	3/1	—	—	—
		1920DR	—	—	—	—
		9740i none	5	2	2	5
IJ180	D	8518, 8519, 8520, 8915	7	3	2	5
IJ180C		8528	7/2	3	2	5
IJ180Cv3		8548G, 8549L	7/2	3	2	5
IJ180mC-10		8900	3/1	—	—	—
IJ180mC-114		1920DR	—	—	—	—
IJ180mC-120		9740i	5	2	2	5
IJ180C-10LSE		none	—	—	—	—
IJ180-10SLS						
IJ380Cv3	A, D	8548G, 8549L	5/2	—	2	—
LX480Cv3	D	8518, 8519, 8520, 8915	7	3	2	5
SV480Cv3		8528	7/2	3	2	5
LX480mC		8548G, 8549L	7/2	3	2	5
SV480mC		1920DR 9740i	— 5	— 2	— 2	— 5
IJ8150	D	8518, 8519, 8520, 8915, 8914	3	3	—	5
		8528	3/2	3	—	5
		1920DR	—	—	—	—
		9740i none	3 —	2 —	— —	5 —

Film	Notes	Graphic Protection	VEH	OUT	W/R	IN
IJ180mC-10UR	B	8518, 8519, 8520, 8915	2	2	—	2
IJ3552C		1920DR	—	—	—	—
		9740i none	2	2	—	2
IJ3690LF-10		8518, 8519, 8520, 8915	—	4	—	8
IJ3690LF-114		1920DR	—	—	—	—
		9740i none	—	2	—	5
IJ3650-10		3619, 3620, 3658G, 3660M	—	6	—	8
IJ3650-114		8518, 8519, 8520, 8915	—	4	—	8
		1920DR 9740i none	— — —	— 2 —	— — —	— 5 —
4 MIL						
IJ160-10		8518, 8519, 8520, 8915	2	2	—	4
IJ160C-10		8528	2	2	—	4
		1920DR	—	—	—	—
		9740i none	2 —	2 —	— —	4 —
IJ160-10		3645	—	—	—	1
IJ3555		8518, 8519, 8520, 8915	2	2	—	2
		1920DR	—	—	—	—
		9740i none	2 —	2 —	— —	2 —
8170-P40/P50		8914, 8518	1	2	—	5

Film	Notes	Graphic Protection	VEH	OUT	W/R	IN
ILLUMINATED						
IJ3630-20	C	3619, 3620, 3658G, 3660M	—	6	—	8
		8518, 8519, 8520, 8915	—	4	—	8
		1920DR	—	—	—	—
		9740i none	— —	2 —	— —	5 —
IJ3730-50	C	3619, 3620, 3658G, 3660M	—	6	—	8
IJ3730-60		8518, 8519, 8520, 8915	—	4	—	8
		1920DR 9740i none	— — —	— 2 —	— — —	— 5 —
Panagraphics III	H	3619, 3620, 3658G, 3660M	—	6	—	8
		8518, 8519, 8520, 8915	—	4	—	8
		none	—	—	—	—
FS-1	H	3619, 3620, 3658G, 3660M	—	6	—	8
		8518, 8519, 8520, 8915	—	4	—	8
		none	—	—	—	—
REFLECTIVE						
780mC-10R	D	8518, 8519	7	3	3	5
		8548G, 8549L	7/2	3	3	5
		1920DR	—	—	—	—
		9740i none	5 —	2 —	2 —	5 —
IJ680-10		8518, 8519	7	3	3	5
IJ680CR-10		1920DR	—	—	—	—
		9740i none	5 —	2 —	2 —	5 —
IJ5100-10		8518, 8519	3	2	—	3
IJ5100R-10		1920DR 9740i	— 3	— 2	— —	— 3

NOTES A Film IJ380Cv3 with overlamine 8548G or 8549L is for auto and watercraft wraps only.
 B Films IJ3552C/IJ180mC-10UR have 2 years durability when applied to flat and simple curved surfaces; 1 year durability when applied to compound curved surfaces, heated and stretched to conform.
 C Film IJ3630 or IJ3730 may be applied to 3M™ Panagraphics III Wide-Width Flexible Substrates or 3M™ Flexible Substrate FS-1.
 D For overlamine 8528 or 8548G or 8549L, or 8900, the first number represents the vertical durability and the second number the horizontal/non-vertical durability on vehicle graphics.
 H Be sure your printer is capable of supporting the width, weight and roll diameter of the flexible substrate to avoid damaging the printer.
IMPORTANT NOTE: Unless you are using 3M horizontal/non-vertical warranty overlaminates (8528, 8548G, 8549L, and 8900), you will only be eligible for a vertical warranty. See the 3M Graphics Warranty Bulletin for more detail.

VEH = Commercial Vehicle, Fleet Truck and Trailer, Bus, Personal Vehicles
 OUT = Outdoor Signs, OEM
 W/R = Watercraft or Railroad (Note: for most films, this refers to Watercraft. For Reflective films, it refers to Railroad).
 IN = Indoor signs

Warranty and Limited Liability. The following is made in lieu of all other express or implied warranties, including any implied warranty of merchantability or fitness for a particular purpose. All 3M products are warranted to be free of defects in materials and manufacture at the time of shipment and to meet the specifications stated in the film or media's Product Bulletin. Also see 3M Graphics Warranties Brochure, which gives the terms, additional limitations of the warranty, if any, and limitations of liability. Trademarks: 3M and MCS are trademarks of 3M Company. All other trademarks are the property of their rightful owners.

DISCLAIMER: With the exception of 3M branded products, 3M does not represent that any printer or printer accessory recommended in 3M literature will meet customer requirements, any federal, state or local regulations, or any applicable safety standards. Such determination is the responsibility of the printer owner.

Film	Notes	Graphic Protection	VEH	OUT	W/R	IN
FABRIC						
9100		9025UM	—	6	—	8

Film	Notes	Graphic Protection	VEH	OUT	W/R	IN
------	-------	--------------------	-----	-----	-----	----

Film	Notes	Graphic Protection	VEH	OUT	W/R	IN
------	-------	--------------------	-----	-----	-----	----

- NOTES
- A Film IJ380Cv3 with overlaminate 8548G or 8549L is for auto and watercraft wraps only.
 - B Films IJ3552C/IJ180mC-10UR have 2 years durability when applied to flat and simple curved surfaces; 1 year durability when applied to compound curved surfaces, heated and stretched to conform.
 - C Film IJ3630 or IJ3730 may be applied to 3M™ Panagraphics III Wide-Width Flexible Substrates or 3M™ Flexible Substrate FS-1.
 - D For overlaminate 8528 or 8548G or 8549L, or 8900, the first number represents the vertical durability and the second number the horizontal/non-vertical durability on vehicle graphics.
 - H Be sure your printer is capable of supporting the width, weight and roll diameter of the flexible substrate to avoid damaging the printer.
- IMPORTANT NOTE:** Unless you are using 3M horizontal/non-vertical warranty overlaminates (8528, 8548G, 8549L, and 8900), you will only be eligible for a vertical warranty. See the 3M Graphics Warranty Bulletin for more detail.

DISCLAIMER: With the exception of 3M branded products, 3M does not represent that any printer or printer accessory recommended in 3M literature will meet customer requirements, any federal, state or local regulations, or any applicable safety standards. Such determination is the responsibility of the printer owner.

- VEH = Commercial Vehicle, Fleet Truck and Trailer, Bus, Personal Vehicles
- OUT = Outdoor Signs, OEM
- W/R = Watercraft or Railroad (Note: for most films, this refers to Watercraft. For Reflective films, it refers to Railroad).
- IN = Indoor signs

Warranty and Limited Liability. The following is made in lieu of all other express or implied warranties, including any implied warranty of merchantability or fitness for a particular purpose. All 3M products are warranted to be free of defects in materials and manufacture at the time of shipment and to meet the specifications stated in the film or media's Product Bulletin. Also see 3M Graphics Warranties Brochure, which gives the terms, additional limitations of the warranty, if any, and limitations of liability. Trademarks: 3M and MCS are trademarks of 3M Company. All other trademarks are the property of their rightful owners.