

3M Occupational Health and Environmental Safety Division
Communication Solutions

PELTOR™

The Sound Solution



Peltor™ Blue-Line

Oil & Gas Communication Solutions





BP p.l.c.

The Power to Protect Your world

Take your safety personally

3M, the world's leader in safety and protective equipment, is proud to have the Peltor brand range as part of its product offering.

Peltor communication equipment as well as hearing, head & face protection products for noisy and hazardous environments are renowned world leaders. With more than 60 years of experience, the Peltor brand promises superior quality communication solutions that provide an optimal balance of comfort and protection.

It is our goal is to ensure that we satisfy your needs through the provision of exceptional leadership, expertise, quality and service excellence. With our global technology, manufacturing and knowledge network we do more than simply develop products that help your workforce to operate in safety and comfort. The advanced engineering and technology inherent with the Peltor brand fits with the high standard of quality and innovation of a continuously evolving range of product solutions that you, our customers, come to expect from 3M.

The last step we have taken is that we produce our product against IECEx standard also not only to ATEX . This will give our customer even more confidence in the safety do to IECEx have higher demand on the product it self as on the production site.



3M™ Peltor™ Blue-Line



Peltor™ Blue-Line range

Peltor Blue-Line is a series of intrinsically safe products designed for extreme environments. Developed in close collaboration with demanding users, these products have undergone rigorous testing in harsh environments.

The results prove that we can meet the demands and make communication easier and more reliable despite external factors.

The Peltor Blue-Line series is approved under the ATEX / IECEx directive and is also in compliance with the hearing standard EN352.

Peltor™ Blue-Line Headsets

- Headband with individually sprung stainless steel wires for an even distribution of pressure around the ears.
- Two-point fasteners for flexible, continuous height adjustment.
- Dynamic lip microphone that suppresses ambient noise.
- Microphone arm with fast and easy adjustment of distance, length, height and angle.
- Optimal acoustically designed high-attenuating shells that provide even more space for the ears.
- Broad ear cushions filled with fluid and foam provide a good seal and low pressure. The cushions are easy to replace.



Peltor™ Blue-Line Adapter Solutions

The adapter has a standard Peltor™ J11 chassi jack. This lets you use Peltor's wide standard range of headsets without any further adaptations. Just plug in and start talking. The outgoing wire has a contact for a communication radio or telephone. Contacts are available for most modern communication radio and Tetra systems on the market.

- The adapter is built into a functional, watertight, sturdy shell with no protruding parts and is designed to fit the size and shape of a hand.
- Special plastic for not generating sparks
- The cord reinforcement and chassis jack have been tested to withstand being plugged in, unplugged and bent at least 100,000 times.

3M™ Peltor™ Lite-Com Pro II

Programmable Wireless Communication Headset

Versatile

The new Peltor Lite-Com Pro II is a communication headset with high attenuation ear protection and a built-in short range communication radio for integration with industrial or other professional radio communication systems.

The boom mounted noise cancelling microphone is adjustable in all directions.

VOX function facilitates hands-free operation, while the PTT button makes it possible to communicate in extremely noisy areas, or whenever “push-to-talk” is wanted.

Programmable

Up to 30 radio channels are programmable in the 403-430–470 MHz frequency range with Peltor Radio Software. The selective squelch function with CTCSS tones or DCS digital codes, allows multiple users to work on the same channel without listening to each others communication.

Despite the high noise attenuating cups for your hearing protection, it is also possible to hear important sounds from the surroundings, for instance warning tones or a call of distress. Two external microphones pick up the surround sound for internal reproduction in stereo.

The sound level from the speakers is limited to 82 dB, for a full day's use of your headset without problems. You can also communicate with people standing close by in a noisy environment, without jeopardizing your hearing by lifting a cup.

To further increase the possibilities for wireless communication you can connect external electronic equipment to your Lite-Com Pro headset, for example a cell phone, a communication radio or almost any other audio source.

There is also an accessory cable with a PTT button, enabling remote PTT control of the Peltor Lite-Com Pro II built-in radio.

Low power

Operating time is up to 17 hours, using the Peltor™ ACK08. The working range with maximum output power is up to 3 km outdoors depending on actual conditions.

Easy to use

There are only four conveniently positioned function keys to handle all settings. Internal voice messages confirm all changes of modes and settings. The last setting is stored when the unit is switched off.



I M1 Ex ia I Ma

II 1G Ex ia IIC T4 -20°C ≤ Ta ≤ +50°C Ga

II 1D Ex ia IIIC T130°C Da



MT7H7F4010-EU-50



MT7H7F4010-EU-50



MT7H7B4010-EU-50

Models	Product code	Frequency	Ch. spacing	Weight
Headset headband	MT7H7F4010-50	403-470 MHz	12,5/20/25 kHz	540 g
Headset neckband	MT7H7B4010-50	403-470 MHz	12,5/20/25 kHz	500 g
Headset helmet	MT7H7P3E4010-50	403-470 MHz	12,5/20/25 kHz	540 g

Attenuation MT7H7F4010-EU-50

Frequency (Hz)	63	125	250	500	1000	2000	4000	8000	H	M	L	SNR
Mean attenuation (dB)	16.5	17.5	22.5	30.3	34.0	33.6	37.7	33.8	32 dB	28 dB	21 dB	31 dB
St. dev. (dB)	3.2	2.9	2.7	2.9	2.5	2.8	2.0	3.7				
APValue (84%)	13.3	14.6	19.8	27.4	31.5	30.8	35.7	30.2				

Attenuation MT7H7B4010-EU-50

Frequency (Hz)	63	125	250	500	1000	2000	4000	8000	H	M	L	SNR
Mean attenuation (dB)	17.7	17.9	23.3	30.5	34.5	33.5	38.1	34.7	32 dB	29 dB	21 dB	31 dB
St. dev. (dB)	3.7	3.7	3.1	2.2	2.2	3.1	3.1	2.3				
APValue (84%)	14.0	14.3	20.2	28.3	32.3	30.5	35.0	32.5				

Attenuation MT7H7P3E4010-EU-50

Frequency (Hz)	63	125	250	500	1000	2000	4000	8000	H	M	L	SNR
Mean attenuation (dB)	15.2	16.9	22.0	30.0	34.5	33.1	36.7	34.7	32 dB	28 dB	20 dB	30 dB
St. dev. (dB)	4.0	3.7	2.9	3.3	2.6	2.4	2.0	3.3				
APValue (84%)	11.1	13.2	19.2	26.7	31.9	30.7	34.6	31.3				

3M™ Peltor™ Lite-Com Pro II is sold through authorized Lite-Com Pro II dealers only.

3M™ Peltor™ Tactical™ XP Headset

– new options for volume settings



The Peltor Tactical XP protects you from harmful noise and impulse sounds, while allowing and even amplifying ambient sounds such as conversation, machine noises and warning signals. The built-in functions of the Tactical XP make it quite different from other active hearing protectors: the user can control and vary the volume function for the current situation. When necessary, ambient noise can be amplified more than any other Peltor hearing protector allows. Peltor Tactical XP lets you hear what you want to hear and blocks out all harmful noise. Each function and setting is indicated by a voice message. Peltor Tactical XP is also available without boom microphone.

- Fail safe functions which enable communication if batteries run out
- Equipped with the following functions: volume for the level dependent function, balance, adjustable release time, equalizer, volume for external input and external input mode
- Last setting is stored when switched off
- Automatic shut-off after two hours if no function is used
- Warning signal when power is low, before shut-off
- Battery life time approximately 1000 hours



Ex II 2G Ex ib IIC T4
Ex I M1 (-51 products)

MT1H7P3E-07-50

Models	Connector	Product code	Weight
Folding headband		MT1H7F2-50 ,51	390 g
Neckband		MT1H7B2-50 ,51	375 g
Helmet attachment		MT1H7P3E2-50 ,51	425 g
Headset headband	J11, TP-120	MT1H7F2-07-50 ,51	400 g
Headset neckband	J11, TP-120	MT1H7B2-07-50	385 g
Headset helmet	J11, TP-120	MT1H7P3E2-07-50 , 51	435 g

Headset with 0.4–1.0 m long spiral cord for connection to the Peltor Adapter

MT1H7F2* MT7H7B2*

Frequency (Hz)	125	250	500	1000	2000	4000	8000
Mean Attenuation (dB)	14,0	22,4	28,1	33,8	33,4	35,4	38,7
Standard Deviation (dB)	1,5	2,7	1,7	2,3	2,6	2,3	1,8
Assumed Protection (dB)	12,0	19,7	26,4	31,5	30,8	33,1	36,9

SNR=30 H=33 M=28 L=20

MT1H7P3E2*

Frequency (Hz)	125	250	500	1000	2000	4000	8000
Mean Attenuation (dB)	13,8	21,5	30,9	36,6	35,9	35,5	39,0
Standard Deviation (dB)	1,8	0,9	1,3	1,5	5,5	3,1	2,3
Assumed Protection (dB)	12,0	20,6	29,6	35,1	30,4	32,4	36,7

SNR=31 H=32 M=29 L=20

3M™ Peltor™ Adapter - the reliable link

The adapter with PTT function between the headset and the communication radio is crucial for communication. This means that you must always have the adapter within reach and yet out of the way. The adapter needs to tolerate rough treatment and harsh climates, day after day. The 3M™ Peltor™ Adapter has what it takes.

- The PTT button is logically positioned and easy to use, even with thick gloves on.
- A sturdy clamp on the back can be twisted 360 degrees for easy, flexible use in all situations.
- The whole adapter, and particularly the contact, is designed to keep moisture away from the electronics.



Ex II 2 G Ex ia IIC T4
Ex I M1

Product Code	Communication radios
FL5205	Ascot Tateco CTS900, Ericsson Freetset
FL5212	Motorola MX1000, MX2000, MX3000
FL5214	Motorola GP300 / Radius P110
FL5216	Ericsson P50/50
FL5218	Motorola HT1000, MT2000, GP900, GP1200
FL5230	Motorola GP320/340
FL5245	Atlantis TP8000
FL5237	Ascot 9D24 Ex
FL5244	Icom F51/61 Ex
FL52103	Funkwerk FT4 Ex
FL52107	Kenwood TK-2260/3260 Ex
FL52137	Ascot d81 Ex

EX Class:
Ex II 2 G Ex ib IIC T4

FL5259	Puma T3
FL5261	Sailor SP3530, 3540, 3560

Technical data

Conforms to the CE requirements in the EU's EMC directive 89/336/EEG.
Sealed to IP65 according to IEC 60529

3M™ Peltor™ Communication Solutions Blue-Line Headsets



Ex II 2 G Ex ib IIC T4



MT7H79P3E-50

3M™ Peltor™ Headset

Peltor's ATEX-approved headset and Listen Only headset are designed to ensure clear, reliable communication even in extremely noisy environments, while providing the perfect hearing protection for the situation.

- Microphone with effective noise compensation for clear and reliable communication
- Quick Positioning integrated microphone boom for easy handling

Models	Connector	Product code	Weight
Folding headband	J11, TP-120	MT7H79F-50	335 g
Neckband	J11, TP-120	MT7H79B-50	300 g
Helmet attachment	J11, TP-120	MT7H79P3E-50	345 g

Headset with 0.4–1.0 m long spiral cord for connection to the Peltor Adapter



Ex II 2 G Ex ib IIC T4



HTM79F-50

- Soft, wide, foam and fluid-filled ear cushions and individually sprung head band wires of stainless sprung steel provide an even and consistent distribution of pressure around the ears for the best possible comfort
- Beam-mounted earphones that provide the least possible resonance and distortion for excellent sound reproduction even in very high-noise environments

Models	Connector	Product code	Weight
Folding headband	3,5 mm Mono	HTM79F-50	310 g
Helmet attachment	3,5 mm Mono	HTM79P3E-50	320 g
Helmet attachment	2,5 mm Mono	HTM79P3E-53	320 g
Helmet attachment	3,5 mm Screw-in	HTM79P3E-54	320 g

Listen-Only headset, with 0.75–1.4 m spiral cord with moulded contact for connection to an EX-approved radio.

MT7H79B-50 MT7H79F-50 HTM79F-50

Frequency (Hz)	125	250	500	1000	2000	4000	8000
Mean Attenuation (dB)	17,2	26,4	33,9	37,2	35,4	33,2	37,0
Standard Deviation (dB)	3,1	2,5	2,7	2,3	2,6	2,4	2,0
Assumed Protection (dB)	14,1	23,9	31,2	34,9	32,8	30,8	35,0

SNR=33 H=33 M=31 L=23

MT7H79P3*-50 HTM7P3E-**

Frequency (Hz)	125	250	500	1000	2000	4000	8000
Mean Attenuation (dB)	17,7	27,1	33,8	38,1	36,2	33,6	37,1
Standard Deviation (dB)	2,9	2,1	2,4	2,6	2,3	2,5	2,2
Assumed Protection (dB)	14,8	25,0	31,4	35,5	33,9	31,1	34,9

SNR=32 H=33 M=32 L=24



Ex II 2 G Ex ib IIC T4



MT72H540F-50

3M™ Peltor™ Twin Cup Headset

- Extra high-attenuating twin shells with optimised acoustic design and excellent space for the ears for the best possible sound quality and comfort.
- Microphone with effective noise compensation for clear and reliable communication.
- Quick Positioning integrated microphone boom for easy handling

Models	Connector	Product code	Weight
Headset headband	J11, TP-120	MT72H540F-50	400 g
Headset helmet	J11, TP-120	MT72H540P3E-50	430 g

MT72H540P3E-50

Frequency (Hz)	125	250	500	1000	2000	4000	8000
Mean Attenuation (dB)	17,9	27,3	34,0	35,8	31,5	40,5	36,5
Standard Deviation (dB)	3,3	3,6	4,2	2,9	3,0	4,7	4,0
Assumed Protection (dB)	14,6	19,7	29,0	32,9	28,5	35,8	32,5

SNR=31 H=31 M=29 L=24

MT72H540F-50

Frequency (Hz)	125	250	500	1000	2000	4000	8000
Mean Attenuation (dB)	18,9	24,4	32,7	35,3	33,3	41,0	39,4
Standard Deviation (dB)	2,3	1,8	1,7	2,6	2,7	3,0	3,2
Assumed Protection (dB)	16,6	22,6	31,0	32,7	30,6	38,1	36,2

SNR=33 H=33 M=31 L=24

Peltor™ Wireless Solutions™

A more effective, flexible way to communicate

Peltor Wireless Solutions uses the latest Bluetooth technology to make communication in noisy environments easier and more effective. You can always be available – quickly, easily and wirelessly. No problems with snagging cords, and you can use your telephone or communication radio even when they're not in sight.

Peltor Wireless Solutions Headset

New wireless communication headset with a built-in Bluetooth* circuit that can quickly and easily connect to another Bluetooth unit up to 10 meters away. Operating time is up to 20 hours and standby time is 750 hours. Rechargeable Ex battery is included



Ex II 2G Ex ia IIC T4
Ex II 2D Ex iaD T130°
Ex I M1 Ex ia I

Models	Product code	Weight
Headset headband	MT53H7FWS2-50	370 g
Headset helmet	MT53H7P3EWS2-50	420 g
Battery Pack	ACK15-EC	
Charger	FR15-EC	



MT53H7FWS2-50

MT53H7FWS2-50

Frequency (Hz)	125	250	500	1000	2000	4000	8000
Mean Attenuation (dB)	13.8	21.5	30.9	36.6	35.9	35.5	39
Standard Deviation (dB)	1.8	0.9	1.3	1.5	5.5	3.1	2.3
Assumed Protection (dB)	12	20.6	29.6	35.1	30.4	32.4	36.7

SNR=31 H=32 M=29 L=20

MT53H7P3EWS2-50

Frequency (Hz)	125	250	500	1000	2000	4000	8000
Mean Attenuation (dB)	14	22.4	28.1	33.8	33.4	35.4	38.7
Standard Deviation (dB)	1.5	2.7	1.7	2.3	2.6	2.3	1.8
Assumed Protection (dB)	12.5	19.7	26.4	31.5	30.8	33.1	36.9

SNR=30 H=33 M=28 L=20

Accessories and spare parts

- HY79** **Hygiene kit.** Easy-to-replace hygiene kit consisting of attenuating cushions and ear cushions
- HYM1000** **Mike Protector.** Moisture and wind-tight. Hygienic, effective protector that increases the life span of the speech microphone. Packages of 5 metres, approx. 50 replacements
- M40/1** **Wind protector for microphone.** Effective against wind noise. For dynamic microphone. (MT7)
- M41/2** **Wind protector for surround microphone** for Tactical XP
- M60/2** **Wind protector for surround microphone** for Lite-Com Pro II
- MT91-50** **Throat microphone** ATEX-approved for Tactical XP and Peltor headset
- ACK08-50** **Rechargeable Li-Ion batterypack** 1350 mAh (only for Lite-Com Pro II)
- FL5602-50** **External PTT** for Lite-Com Pro



HY79



M41/2



HYM1000



MT91-50



FL5602-50



ACK08



M60/2

*Bluetooth is a registered trademark of Bluetooth SIG Inc



3M Personal Safety Division
3M Svenska AB, Box 2341
SE-331 02 Värnamo
Sweden
Phone: +46 (0) 370 65 65 65
Fax: +46 (0) 370 65 65 99
Email: peltorcommunications@mmm.com
Internet: www.3M.com/Peltorcomms

© 3M 2013. All rights reserved.
3M and Peltor are trademarks of 3M Corporation,
St. Paul, MN 55144-1000, USA

The **Bluetooth®** wordmark and logotype are the property of
Bluetooth SIG, Inc., and all use of them is subject to licensing
agreements.

Please recycle. Printed in Sweden.