

## 3M-Matic™ Side Belt Adjustable Case Sealer 8000a

The image features a 3M-Matic Side Belt Adjustable Case Sealer 8000a. It is a large industrial machine with a grey frame and red accents. A large yellow roll of tape is mounted on top. The machine has a conveyor belt system and a side belt mechanism. The background is a light grey with faint technical drawings of the machine's components, including rollers, belts, and structural frames, some of which are numbered (e.g., 1, 3, 5, 8, 17, 22, 23, 28, 36, 48, 53, 54).

**8000a**

Consistent.  
Reliable.  
Tough.

### And now, better than ever.

Today, companies need to be fast and flexible in every phase of their operations—and that includes end-of-line packaging. The 3M-Matic™ Side Belt Adjustable Case Sealer 8000a gives manufacturers and distributors from every industry the packaging flexibility and speed to stay one step ahead of the competition.

Narrow width cases have met their match in this state-of-the-art case sealer from 3M. Engineered for maximum throughput and stability for almost any case height and width, the 3M-Matic™ Side Belt Adjustable Case Sealer 8000a is the high volume solution for box sealing productivity.

*3M-Matic™ Case Sealers: Consistent. Reliable. Tough.*

**3M**

# Long lasting. Low maintenance. Trusted reliability.


## Innovative Features

- 3M™ AccuGlide™ 3 Taping Heads ensure reliable application of tape without box damage
- Interchangeable 2-inch or 3-inch taping heads maximize production flexibility
- Easily accessible side handle and reference ruler make height adjustments a snap for a wide variety of case heights from 3¾ inches to 36 inches
- Rugged, dual-extruded columns allow for smooth incremental adjustments to case heights

## Standard Features

- Spring-loaded side belt drive
- Top flap compression rollers
- Centrally located emergency stop
- Spring-loaded upper drive assembly
- Dual masts and dual lead screws

**Options:** Infeed and exit conveyors, locking casters, low tape indicator, light indicator, box hold-down attachment



Box Dimensions for 8000a and 8000a3 Machines: Inches (mm)

	Length	Width		Height <sup>1</sup>	
		8000a	8000a3	Standard Position	Standard Position
				Standard Tape Leg Length	Short Tape Leg Length
Minimum	6 (152)	4.5 (114)	5.5 (140)	4.25 (108)	3.75 (95)
Maximum <sup>2</sup>	N/L	21.5 (546)	21.5 (546)	28 (711)	27.5 (699)

<sup>1</sup> Requires a column adjustment for case heights lower than 4.25" or higher than 28".

<sup>2</sup> Maximum case height of 36" can be obtained by moving the columns and the upper assembly to the upper mast position. Minimum will be 12.25".

Learn more about 3M's full line of case sealing solutions at [3M.com/3M-Matic](http://3M.com/3M-Matic)

**Product Use:** User is responsible for determining whether the product is fit for a particular purpose and suitable for user's method of application.

**Warranty and Limited Remedy:** THE FOLLOWING WARRANTIES ARE MADE IN LIEU OF ALL OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO THE IMPLIED WARRANTY OF MERCHANTABILITY, THE IMPLIED WARRANTY OF FITNESS FOR A PARTICULAR PURPOSE AND ANY IMPLIED WARRANTY ARISING OUT OF A COURSE OF DEALING, A CUSTOM OR USAGE OF TRADE: 3M sells its 3M-Matic™ Side Belt Adjustable Case Sealer 8000a with the following warranties: 1) The Taping Head knife blades, springs and rollers will be free from all defects for ninety (90) days after delivery. 2) All other Taping Head parts will be free from all defects for three (3) years after delivery. 3) All other parts will be free from all defects for two (2) years after delivery. Please refer to individual data pages for additional details and exceptions. If any 3M-warranted part is proved to be defective within its warranty period, then the exclusive remedy and 3M's and seller's sole obligation shall be, at 3M's option, to repair or replace the part, provided the defective part is returned immediately to 3M's factory or an authorized service station designated by 3M. A part will be presumed to have become defective after its warranty period unless the part is received or 3M is notified of the problem no later than five (5) calendar days after the warranty period. If 3M is unable to repair or replace the part within a reasonable time, then 3M, at its option, will replace the equipment or refund the purchase price. 3M shall have no obligation to provide or pay for the labor required to install the repaired or replacement part. 3M shall have no obligation to repair or replace (1) those parts failing due to operator misuse, carelessness, or due to any accidental cause other than equipment failure, or (2) parts failing due to non-lubrication, inadequate cleaning, improper operating environment, improper utilities or operator error. **Limitation of Liability:** 3M and seller shall not be liable for direct, indirect, special, incidental or consequential damages based upon breach of warranty, breach of contract, negligence, strict liability or any other legal theory. The foregoing Warranty and Limited Remedy and Limitation of Liability may be changed only by a written agreement signed by authorized officers of 3M and seller.



## Industrial Adhesives and Tapes Division

Building 225-3S-06  
St. Paul, MN 55144-1000  
1-800-362-3550  
[3M.com/3M-Matic](http://3M.com/3M-Matic)

3M, 3M-Matic and AccuGlide are trademarks of 3M.  
Please recycle. Printed in USA.  
© 3M 2014. All rights reserved.  
70-0710-0431-4