

ScotchCode™ Write-on Dispensers

SLW SWD SMP

Data Sheet



Product Description

ScotchCode SLW / SWD

These self-laminating write-on marker dispensers are handy for identifying wire and cable as well as household, automotive, plumbing and sporting equipment. They are easy to use, refillable and come with an SMP permanent marking pen. The dispensers' design provides convenience and protects the die-cut adhesive markers.

ScotchCode SWL-R / SWD-R

A vinyl tape on paper support 0.10mm thick, with an acrylic pressure sensitive adhesive. It is conformable and resistant to dust, oil and temperatures up to 80°C.

- ❖ SLW-R : refill label roll for SLW dispenser.
- ❖ SWD-R : refill label roll for SWD dispenser.

ScotchCode SMP

The marker pen has an extra fine point and permanent, quick drying ink which is highly resistant to UV light and humidity.

A pen is supplied with each ScotchCode SLW and SWD dispenser.

Applications

- ❖ Wire and cable identification.
- ❖ Home Use: VCRs, TVs, cable, stereo components, phones, computers, luggage, satellite installation.
- ❖ Do-It-Yourself Home Improvements: home security, sprinkler systems, sound systems, exterior lighting design.
- ❖ Automotive: plugs, hoses, spark plugs, stereos, car alarms.
- ❖ Plumbing: pipes, hoses, tubes, parts, vents.
- ❖ Sporting Equipment: golf clubs, camping equipment, bags, bats, fishing rods, rackets, bicycles.
- ❖ Equipment Identification: hand and power tools.

Key Features and Benefits

Feature	Benefit
Ergonomically designed dispenser	Markers are easy to use
Pens and refill rolls sold separately	Reusable
Die-cut markers now in small, medium and large	Provides a variety of uses
Resists dirt, oil, heat and moisture	Markers stay clean and dry
Transparent overwrap with self-laminating pressure-sensitive adhesive	Protects printing

Presentation

Reference	Product	Labels per Roll	Write-on Area (WxL) (mm)	Marker Size (WxL) (mm)	Wire Diameter (mm)
SLW	Dispenser filled with labels and a pen	70	25 x 19	25 x 127	6 – 35
SLW-R	Refills	70	25 x 19	25 x 127	6 – 35
SWD	Dispenser filled with labels and a pen	250	19 x 8	19 x 35	2.3 – 7.8
SWD-R	Box of 10 refills	250	19 x 8	19 x 35	2.3 - 7.8
SMP	Box of 10 pens				

Important Notice

Technical information provided by 3M is based on experience and/or tests believed to be reliable, but their accuracy is not guaranteed and the results may not be relevant to every user's application. For this reason 3M does not accept responsibility or liability, direct or consequential, arising from reliance upon any information provided and the user should determine the suitability of the products for their intended use. Nothing in this statement will be deemed to exclude or restrict 3M's liability for death or personal injury arising from its negligence. All questions of liability relating to 3M products are governed by the seller's terms of sale subject where applicable to the prevailing law. If any goods supplied or processed by or on behalf of 3M prove on inspection to be defective in material or workmanship, 3M will (at its option) replace the same or refund to the Buyer the price paid for the goods or services. Except as set out above, all warranties and conditions, whether express or implied, statutory or otherwise are excluded to the fullest extent permissible at law.

3M and ScotchCode are trademarks of the 3M Company. Printed in the UK. © 3M United Kingdom PLC, 2003

Electrical Products Group

3M United Kingdom PLC
Sales Office
 PO Box 393
 Bedford MK41 0YE
 Telephone: 01234 229462
 Fax: 01234 229433

3M Ireland

Sales Office
 3M House, Adelphi Centre, Upper Georges Street
 Dun Laoghaire, Co Dublin, Ireland
 Telephone: 353 1 280 3555
 Fax: 353 1 280 3509

3M United Kingdom PLC

Head Office
 3M Centre, Cain Road
 Bracknell, Berkshire RG12 8HT
 Telephone: 01344 858000
 Fax: 01344 858758