

## Products designed for the way you like to work...

For every clinical situation, you'll find a 3M ESPE polyether or VPS impression material designed to suit your technique and procedure. Choose from a wide range of viscosities and set/working times – in both cartridge and Penta™ deliveries.

More proven solutions brought to you by 3M ESPE, the worldwide leader in impression materials.



### Ordering Information

#### Pentamix 3™ Auto Mixing Unit

77874	PENTAMIX 3 ANZ	NEW
77601	Penta Wall Mount for Pentamix 3	NEW
71512	50 Penta Mixing tips Red	

#### Imprint 3™ Penta™ HB & Penta™ Quickstep HB & Penta™ Putty

P310770	IMPRINT 3 PENTA HB INTRO KIT P3	NEW
P310790	IMPRINT 3 PENTA HB QUICK STEP INTRO KIT P3	NEW
P36959	IMPRINT 3 PENTA PUTTY INTRO KIT P3	NEW
10771PH	IMPRINT 3 PENTA HB REFILL PACK	
10971PH	IMPRINT 3 PENTA HB QUICKSTEP REFILL PACK	
10771PP	IMPRINT 3 PENTA PUTTY REFILL PACK	
P3808	IMPRINT 3 PENTA HB CARTRIDGE RF NA P3	NEW
P3807	IMPRINT 3 PENTA HB QUICK STEP CARTRIDGE P3	NEW
P3806	IMPRINT 3 PENTA PUTTY CARTRIDGE P3	NEW

#### Position Penta™ & Penta™ Quick

29062	POSITION PENTA QUICK REFILL PACK	
29012	POSITION PENTA REFILL PACK	
P3681	POSITION PENTA CARTRIDGE P3	NEW
P3691	POSITION PENTA QUICK CARTRIDGE P3	NEW

HB: heavy body MB: medium body LB: light body

#### Impregum™ Penta™ / Penta™ Soft MB

P31684	IMPREGUM PENTA INTRO KIT P3	NEW
31644	IMPREGUM PENTA REFILL PACK	
P3792	IMPREGUM PENTA CARTRIDGE P3	NEW
P31734	IMPREGUM PENTA SOFT INTRO KIT P3	NEW
31730	IMPREGUM PENTA SOFT REFILL PACK	
P3787	IMPREGUM PENTA SOFT CARTRIDGE P3	NEW

#### Impregum™ Penta™ DuoSoft HB/LB

P31738	IMPREGUM PENTA HB DUOSOFT INTRO KIT P3	NEW
31740	IMPREGUM PENTA HB DUOSOFT REFILL PACK	
31745	IMPREGUM PENTA LB DUOSOFT REFILL PACK	
P3793	IMPREGUM PENTA HB DUOSOFT CARTRIDGE P3	NEW
P3795	IMPREGUM PENTA LB DUOSOFT CARTRIDGE P3	NEW

#### Impregum™ Penta™ Soft Quick Step MB & HB/LB

P31771	IMPREGUM PENTA SOFT MB QUICK STEP INTRO P3	NEW
P31779	IMPREGUM PENTA SOFT HB/LB QUICK STEP INTRO P3	NEW
31765	IMPREGUM PENTA SOFT MB QUICKSTEP REFILL PACK	
31769	IMPREGUM PENTA SOFT HB QUICKSTEP REFILL PACK	
P3776	IMPREGUM PENTA SOFT MB QUICK STEP CARTRIDGE P3	NEW
P3774	IMPREGUM PENTA SOFT HB QUICK STEP CARTRIDGE P3	NEW

#### Ramitec Penta™

33112	RAMIETC PENTA REFILL PACK	
P3821	RAMITEC PENTA CARTRIDGE P3	NEW

# Pentamix™ 3

## Automatic Mixing Unit



The fastest automatic mixer in the universe

### Make Better Impressions

Even the most experienced practitioner, using the best materials, can encounter difficulties when making an impression. 3M ESPE has taken its long history in developing and testing impression materials, and assembled the **Making Better Impression Troubleshooting guide**. It identifies common impression problems and offers solutions. To get your **FREE copy**, download it now from our website – or call Customer Care at 1300 363 454.



Customer Service Centre: 1300 363 454  
For more information, please visit [www.3mespe.com.au](http://www.3mespe.com.au)

**3M ESPE**

**www.3MESPE.com.au**

**www.3MESPE.co.nz**

#### 3M Australia Pty Limited

3M ESPE Dental Division  
Building A, 1 Rivett Rd  
North Ryde, NSW 2113  
Toll Free: 1300 363 454  
ABN: 90 000 100 096

#### 3M New Zealand Limited

3M New Zealand Limited  
94 Apollo Drive  
Rosedale, Auckland 0632  
New Zealand  
Tel: 0800 80 81 82

Please recycle. Printed in Australia.  
© 3M 2011. All rights reserved.  
F38-141179

3M, ESPE and Filtek are trademarks of 3M or 3M ESPE AG. EsthetX, Flow-It, Revolution 2, Tetric EvoFlow, TPH3, Venus Flow and Vertise Flow are not trademarks of 3M or 3M ESPE AG.

**3M ESPE**

# Twice as Fast

# Saves Space


## Take the strain and uncertainty out of mixing impression materials.

Experience the speed, ease and accuracy of the Pentamix™ 3 Automatic Mixing Unit from 3M ESPE.

With the touch of a button, it mixes and dispenses a completely homogeneous mix – free of voids that interfere with the accuracy of impression detail and the fit of the restoration. And because it's fully automatic, it reduces strain on dental assistants, too.


## Gain more working time with the fastest mixer on the market.

The Pentamix 3 unit mixes and dispenses all your favorite 3M ESPE impression materials – even putty – twice as fast as the Pentamix™ 2 Mixing Unit and faster than any automatic mixing unit on the market. Cutting your mixing and tray-filling time in half gives you more usable working time to make an accurate impression – which means less stress for you and your assistants. It also means you can use comfortably quick-setting materials.



### Summary of advantages

- Dispenses Penta™ impression materials **in half the time of the Pentamix™ 2 Mixing Unit and faster than any other unit on the market**
- Saves counter space with the smallest footprint on the market
- Easy handling with push-button control on both sides
- Homogeneous mixing for void-free impressions
- Less waste – dispenses only amount of material needed
- Can be used with polyether, VPS and alginate replacement materials



Convenient gauge allows you to see when the material in the cartridge is getting low without opening the cover of the machine

Product name, working/setting times are visible, even when the device cover is closed

Easy cartridge exchange


Easy to attach mixing tip without opening device cover

Push-buttons on left and right side allow for easy operation

Appealing sleek design

## Save valuable counter space with the smallest footprint.

The Pentamix 3 unit helps you make the most of your valuable office space with the smallest footprint on the market.



Whether you're working with limited space or just want to completely free up your counter space, the wall-mount design option offers the ideal solution.



## Penta™ Tray Materials

Polyether	VPS
Impregum™ Penta™ Soft Quick Step Heavy Body	Imprint™ 3 Penta™ Putty
Impregum™ Penta™ Soft Quick Step Medium Body	Imprint™ 3 Penta™ Quick Step Heavy Body
Impregum™ Penta™ DuoSoft Heavy Body	Imprint™ 3 Penta™ Heavy Body
Impregum™ Penta™ Soft Medium Body	Position™ Penta™ Quick VPS Alginate Replacement
Impregum™ Penta™ Medium Body	
Ramitec™ Penta™	

For optimal performance, only 3M™ ESPE™ Penta™ impression materials are recommended for use in the Pentamix™ 3 Automatic Mixing Unit.