

Scotch-Brite™

Eraser Burnish Pad

For Ultra High Speed Burnishing

Technical Data

TD117. Date: Jan 1999
Supersedes: new issue
LC. Page 1 / 1

Description:

The Scotch-Brite™ Eraser Floor Pad is a premium quality floor maintenance pad, made of high quality synthetic fibre, in an open textured non-woven construction. Polishing particles are dispersed throughout and bonded with a durable adhesive. Each floor pad has a pre-cut centre hole.

Special Features:

- Specific fibre mix to ensure a faster polishing action and a high production of shine.
- Specially formulated for a more efficient erasing of marks (shoe soles, trolley wheels....)
- Highly soft to the floor : Non scratching/damaging protected floors
- Open textured construction for easier washing of pads after use
- Consistent performance
- Durable pad at work.

Where and When to Use:

RPM	800-1500	1200-3000
Strip		
Scrub		
Spray	X	
Buff	X	XX

XX Designed for X suitable

Dry buffing of protected floors under ultra high speed rotary floor machines that operate in the range of 1200-3000 rpm. Suitable for spray buffing/cleaning at 800-1500 RPM.

Directions for Use:

1. Install a clean floor pad under the machine pad holder
2. Dust mop the area.
3. Dry buff a section of floor in 2 passes
4. Move machine to next section
5. Dust mop entire floor area
6. Remove pad and wash after use.

Note: floors must be clean, free of soil and in dry condition prior to dry buff .

Maintenance of pad:

1. Remove from machine after each use and shake dust out of pads
2. Rinse wash under tap water or machine wash every 5 uses.
3. Hang up for drying . Do not use wet .

Note: machine washed floor pads will shrink about 20 mm after first washing cycle. Recommended washing-machine temperature is 40°C (higher temperature will decrease the life of the pad) .

Performance Advantages:

Produces up to 30% more shine on protected floors (Test 3M/DB)
Erases marks up to 4 times faster from protected floors (Test 3M/BMR)
Makes less scratches on the floor
Durability : 25 000 sqm at 1500 RPM in standard use with appropriate maintenance.

Product Specifications:

The Scotch-Brite Floor Pads consist of polyester fibre and synthetic adhesive. They are not significantly affected by water, detergents and cleaners normally used for floor maintenance.

Product Characteristics:

Colour: light pink
Marking: no
Thickness: 25.0mm
Centre hole: pre-cut at 85 mm
Weight: 1000 g/m₂
Fibre type: polyester, mixture of sizes.

Aggressiveness (Schiefer Value):

(Test method 3M/ST)
Expected value for polishing operation: 0g. 3M value : 0g

Packaging and labeling:

Packaging material made of at least 35% recycled material.
Multilingual coloured label on each case. Bar code on each label.

Standard Sizes:

Standard Outside Diameters:
432, 480, 505, 685 mm.
Other sizes available upon request (minimum quantities may apply).

Origin:

Made in U.S.A

Disposal Informations:

Discard into appropriate container, for incineration, if available.
Packaging material: recyclable.

Commercial Care Laboratory Europe

3M France - Eurotech
P.O. Box 28 – Avenue Boulé
F-95250 BEAUCHAMP