

3M Industrial Markets Center
Featured Products for Metal Fabrication



Bringing Workplace Solutions Into Focus



From skyscrapers and parking garages to the watch on your wrist, the buildings and machines that we have today would not exist without metal fabricators. 3M helps fabricated metal manufacturers cut, form, and assemble the metal infrastructure that is necessary to build our world.

Whether you're looking for reliable day-to-day items or the right product to address a specific problem, 3M Industrial Products for Fabricated Metal Manufacturing provide the performance you can rely on.



Workplace Solutions

Maintenance, Repair and Operation (MRO) work is the foundation of every business. Whether you're fixing something that has broken or performing routine maintenance on your facility, finding the right products is of the highest concern.

The 3M products found here reflect those commonly used by metal fabrication facilities to keep their business running smoothly. They are products that offer:

- Value** – through solutions that help improve efficiency and productivity
- Versatility** – with options to help keep your business running effectively and safely
- Vision** – via innovative solutions that help solve critical MRO challenges

The featured items are only a snapshot of 3M solutions for the metal fabrication industry. Contact us today to discuss the full line of products to renew your MRO operations.

Table of Contents

Abrasives	2–5
Adhesives	6
Facility Maintenance	7
Matting & Treads	8
Paint Finishing	9
Safety Products	9–11
Spray Equipment for Coatings . . .	12
Tapes	12–14

Abrasives



3M™ Cloth Belt 577F

Industry-leading performance from an Alumina Zirconia belt at an unbelievable price. Whether file belt or backstand grinding, get quality Alumina Zirconia on a YF-wt cloth backing, a durable film splice and grinding aid for cooler running—all for a competitive price.

UPC	Grade	MOQ	Size	Case Qty/Units
00-051141-30690-2	60	50	¼" x 18"	200
00-051141-30691-9	80	50	¼" x 18"	200
00-051141-30708-4	120	50	¼" x 18"	200
00-051141-30694-0	60	50	¼" x 24"	200
00-051119-05580-1	P80	50	¼" x 24"	200
00-051111-68668-3	60	50	½" x 12"	200
00-051111-68695-9	80	50	½" x 12"	200
00-051141-30709-1	120	50	½" x 12"	200
00-051141-30686-5	36	50	½" x 18"	200
00-051119-63081-7	60	50	½" x 18"	200
00-051119-82035-5	80	50	½" x 18"	200
00-051141-30689-6	120	50	½" x 18"	200
00-051141-30693-3	36	50	½" x 24"	200
00-051111-68669-0	60	50	½" x 24"	200
00-051111-68696-6	80	50	½" x 24"	200
00-051111-69436-7	120	50	½" x 24"	200
00-051141-30687-2	36	4	¾" x 18"	200
00-051115-19553-2	60	50	¾" x 18"	200
00-051141-30688-9	120	50	¾" x 18"	200
00-051125-19076-3	80	50	¾" x 18"	200
00-051125-16745-1	60	50	¾" x 20-½"	200
00-051111-68697-3	80	50	¾" x 20-½"	200
00-051125-22333-1	120	50	¾" x 20-½"	200



3M™ Fibre Disc 501C

A versatile, Alumina Zirconia fibre disc option that works well on mild steel but can also be used with good results on stainless steel.

UPC	Grade	MOQ	Max RPM	Size	Case Qty/Units
00-051111-50409-3	24	25	13,300	4-1/2" x 7/8"	100
00-051111-50413-0	36	25	13,300	4-1/2" x 7/8"	100
00-051111-50414-7	50	25	13,300	4-1/2" x 7/8"	100
00-051111-50415-4	60	25	13,300	4-1/2" x 7/8"	100
00-051111-50416-1	80	25	13,300	4-1/2" x 7/8"	100
00-051111-50417-8	100	25	13,300	4-1/2" x 7/8"	100
00-051111-50419-2	120	25	13,300	4-1/2" x 7/8"	100
00-051111-50412-3	36	25	12,000	5" x 7/8"	100
00-051111-50420-8	50	25	12,000	5" x 7/8"	100
00-051111-50421-5	60	25	12,000	5" x 7/8"	100
00-051111-50423-9	100	25	12,000	5" x 7/8"	100
00-051111-50424-6	120	25	12,000	5" x 7/8"	100
00-051111-50411-6	24	25	8,600	7" x 7/8"	100
00-051111-50426-0	36	25	8,600	7" x 7/8"	100
00-051111-50425-3	50	25	8,600	7" x 7/8"	100
00-051111-50428-4	80	25	8,600	7" x 7/8"	100
00-51125-63799-2†	100	25	8,600	7" x 7/8"	100
00-051111-50430-7†	120	25	8,600	7" x 7/8"	100



3M™ Flap Discs 566A

When you want it all, choose the versatile 566A flap disc for a great balance of cut and life on any metalworking application. Alumina Zirconia works on all metals.

UPC	Grade	MOQ	Max RPM	Size	Case Qty/Units
Type 27					
00-051141-55362-7	40	Case	13,300	4-1/2" x 5/8-11*	10
00-051141-55363-4	60	Case	13,300	4-1/2" x 5/8-11*	10
00-051141-55364-1	80	Case	13,300	4-1/2" x 5/8-11*	10
00-051141-55366-5	40	Case	13,300	4-1/2" x 7/8"	10
00-051141-55367-2	60	Case	13,300	4-1/2" x 7/8"	10
00-051141-55368-9	80	Case	13,300	4-1/2" x 7/8"	10
00-051141-55370-2	40	Case	8,600	7" x 5/8-11*	5
00-051141-55371-9	60	Case	8,600	7" x 5/8-11*	5
00-051141-55372-6	80	Case	8,600	7" x 5/8-11*	5
00-051141-55374-0	40	Case	8,600	7" x 7/8"	5
00-051141-55375-7	60	Case	8,600	7" x 7/8"	5
00-051141-55376-4	80	Case	8,600	7" x 7/8"	5
Type 29					
00-051141-55394-8†	40	Case	13,300	4" x 3/8-24*	10
00-051141-55395-5†	60	Case	13,300	4" x 3/8-24*	10
00-051141-55396-2†	80	Case	13,300	4" x 3/8-24*	10
00-051141-55398-6†	40	Case	13,300	4" x 5/8"	10
00-051141-55399-3†	60	Case	13,300	4" x 5/8"	10
00-051141-55400-6†	80	Case	13,300	4" x 5/8"	10
00-051141-55402-0	40	Case	13,300	4-1/2" x 5/8-11*	10
00-051141-55403-7	60	Case	13,300	4-1/2" x 5/8-11*	10
00-051141-55404-4	80	Case	13,300	4-1/2" x 5/8-11*	10
00-051141-55406-8	40	Case	13,300	4-1/2" x 7/8"	10
00-051141-55407-5	60	Case	13,300	4-1/2" x 7/8"	10
00-051141-55408-2	80	Case	13,300	4-1/2" x 7/8"	10
00-051141-55410-5	40	Case	8,600	7" x 5/8-11*	5
00-051141-55411-2	60	Case	8,600	7" x 5/8-11*	5
00-051141-55412-9	80	Case	8,600	7" x 5/8-11*	5
00-051141-55414-3	40	Case	8,600	7" x 7/8"	5
00-051141-55415-0	60	Case	8,600	7" x 7/8"	5
00-051141-55416-7	80	Case	8,600	7" x 7/8"	5

*Quick Change Hub Attachment

†Made-to-Order



3M™ Hookit™ Finishing Film Disc

Levels orange peel, dust nibs or paint runs in all types of paints. Appropriate for light sanding on refinish lacquer.

UPC	Grade	MOQ	Description	Size	Case Qty/Units
00-051131-00968-4	P1200	1 Box	100 Discs per box	6"	4 Boxes per case
00-051131-00907-3	P1500	1 Box	50 Discs per box	3"	4 Boxes per case
00-051131-00951-6	P1500	1 Box	100 Discs per box	5"	4 Boxes per case
00-051131-00950-9	P1500	1 Box	100 Discs per box	6"	4 Boxes per case



3M™ Trizact™ Hookit™ Foam Discs 443SA

High performance abrasive disc with Hookit™ attachment. P3000 for refining P1200-P1500 grade sand scratches during paint finishing process. 5000 grit for refining P3000 grade sand scratches.

UPC	Grade	MOQ	Description	Size	Case Qty/Units
00-051131-02085-6	P3000	1 Box	15 Discs per box	6"	4 Boxes per case
00-051131-30662-2	P5000	1 Box	15 Discs per box	6"	4 Boxes per case



Scotch-Brite™ Roloc™ Surface Conditioning Disc

Metalworking industry's top choice for cleaning, finishing, blending and deburring applications. Available in a full range of attachment systems.

UPC	Grade	MOQ	Color	Size	Case Qty/Units
00-048011-05523-7	A VFN	50	Blue	2" x NH	200
00-048011-05527-5	A MED	50	Maroon	2" x NH	200
00-048011-05528-2	A CRS	50	Brown	2" x NH	200
00-048011-05531-2	A MED	25	Maroon	3" x NH	100
00-048011-05532-9	A CRS	25	Brown	3" x NH	100



3M™ Roloc™ Disc 777F

A 3M™ ceramic grain Roloc™ disc constructed on a YF-wt, water resistant polyester cloth backing. Resin bonded for heat resistance. Can be run wet or dry.

UPC	Grade	MOQ	Max RPM	Size	Case Qty/Units
00-051144-76629-1	36	50	25,000	2"	200
00-051144-76630-7	50	50	25,000	2"	200
00-051144-76433-4	60	50	25,000	2"	200
00-051144-14661-1	80	50	25,000	2"	200
00-051144-80508-2	P100	50	25,000	2"	200
00-051144-80512-9	P120	50	25,000	2"	200
00-051144-76631-4	36	50	20,000	3"	200
00-051144-76632-1	50	50	20,000	3"	200
00-051144-76633-8	60	50	20,000	3"	200
00-051144-76634-5	80	50	20,000	3"	200
00-051144-80509-9	P100	50	20,000	3"	200
00-051144-80513-6	P120	50	20,000	3"	200



Scotch-Brite™ Hand Pads

Only 3M offers genuine Scotch-Brite™ Hand Pads. Universally used in a variety of applications, Scotch-Brite™ Hand Pads are excellent to clean, scuff, grain, denib, defuzz, blend or finish a variety of materials. Use by hand, with a hand pad block, or sanders.

UPC	ID	Grade	MOQ	Color	Size	Case Qty/Units
00-048011-04029-5	7447	A VFN	Case	Maroon	6" x 9"	60 (3 Boxes of 20)
00-048011-04229-9	7447B	A VFN	Case	Maroon	6" x 9"	60 (1 Box of 60)
00-048011-04051-6	7446	S MED	Case	Gray	6" x 9"	40 (4 Boxes of 10)
00-048011-04028-8	7448	S ULF	Case	Lt. Gray	6" x 9"	60 (3 Boxes of 20)
00-048011-04050-9	7440	A MED	Case	Tan	6" x 9"	40 (4 Boxes of 10)



Scotch-Brite™ Multi-Flex Abrasive Sheet Roll

More “scrunchable” than hand pads and conveniently dispensed from its self-contained packaging, these 8" x 4" sheets can get to hard to reach corners and crevices. Excellent sharpness makes it a suitable substitute for steel wool. Used wet or dry, Scotch-Brite™ multi-flex abrasives won't rust. Use for sealer sanding, denibbing, defuzzing, highlighting and top coat finishing applications.

UPC	Grade	MOQ	Color	Size	Case Qty/Units
00-051131-07521-4	A VFN	1 Roll (60 Sheets)	Maroon	8" x 20'	240 (4 Rolls of 60 sheets)
00-051131-07522-1	S ULF	1 Roll (60 Sheets)	Gray	8" x 20'	240 (4 Rolls of 60 sheets)



Scotch-Brite™ EXL Deburring Wheel

The top choice for high performance and durability in deburring and finishing applications. Use to clean, finish, deburr or polish all types of metals, composites and glass. Abrasive mineral: S = silicon carbide; A = aluminum oxide.

UPC	Grade	MOQ	Max RPM	Size	Case Qty/Units
00-048011-13616-5	8A MED	Case	6,000	6" x 1/2" x 1"	4
00-048011-09548-6	8S FIN	Case	6,000	6" x 1/2" x 1"	4
00-048011-05790-3	9S FIN	Case	6,000	6" x 1/2" x 1"	4
00-048011-13617-2	8A MED	Case	6,000	6" x 1" x 1"	3
00-048011-09549-3	8S FIN	Case	6,000	6" x 1" x 1"	3
00-048011-05132-1	9S FIN	Case	6,000	6" x 1" x 1"	3
00-048011-17459-4	8A MED	Case	4,500	8" x 1/2" x 3"	4
00-048011-14629-4	8S FIN	Case	4,500	8" x 1/2" x 3"	4
00-048011-05791-0	9S FIN	Case	4,500	8" x 1/2" x 3"	4
00-048011-13619-6	8A MED	Case	4,500	8" x 1" x 3"	3
00-048011-09551-6	8S FIN	Case	4,500	8" x 1" x 3"	3
00-048011-05135-2	9S FIN	Case	4,500	8" x 1" x 3"	3
00-048011-13620-2	8A MED	Case	4,500	8" x 2" x 3"	2
00-048011-09552-3	8S FIN	Case	4,500	8" x 2" x 3"	2
00-048011-05136-9	9S FIN	Case	4,500	8" x 2" x 3"	2



3M™ High Performance Depressed Center Grinding Wheels

3M ceramic abrasive grain for fast cut and long life. Innovative technology provides excellent product life and cut rates to increase productivity and throughput while lowering total abrasive costs. Specially formulated to be used on stainless and mild steel.

UPC	MOQ	Max RPM	Size	Case Qty/Units
Type 27				
00-051115-66555-4	10	15,300	4" x 1/4" x 3/8"	20
00-051115-66554-7	10	15,300	4" x 1/4" x 5/8"	20
00-051115-66544-8	10	13,300	4-1/2" x 1/4" x 7/8"	20
00-051115-66545-5	10	12,250	5" x 1/4" x 7/8"	20
00-051115-66546-2	10	10,200	6" x 1/4" x 7/8"	20
00-051115-66547-9	10	8,500	7" x 1/4" x 7/8"	20
00-051115-66548-6	10	6,650	9" x 1/4" x 7/8"	20
Type 27 (Quick Change)				
00-051115-66553-0	10	13,300	4-1/2" x 1/4" x 5/8"-11	20
00-051115-66549-3	10	12,250	5" x 1/4" x 5/8"-11	20
00-051115-66550-9	10	10,200	6" x 1/4" x 5/8"-11	20
00-051115-66551-6	10	8,500	7" x 1/4" x 5/8"-11	20
00-051115-66552-3	10	6,650	9" x 1/4" x 5/8"-11	20

Adhesives



3M™ Scotch-Weld™ Epoxy Adhesive DP190 Duo-Pak

Bonds to a variety of materials such as metals, ceramics, wood and many plastics. 3M™ Scotch-Weld™ EPX™ Applicator and mix nozzles are required for dispensing (not included).

UPC	Color	Size	Packaging
00-021200-22647-2	Gray	50 mL	12/Case
00-021200-87840-4	Gray	200 mL	12/Case
00-021200-87841-1	Gray	400 mL	6/Case



3M™ Scotch-Weld™ Epoxy Adhesive DP420 Duo-Pak

Toughened, two-part epoxy adhesive. 2:1 mix ratio, 20 minute work life and handling strength in approximately 2 hours. 3M™ Scotch-Weld™ EPX™ Plus II applicator and mix nozzles are required for dispensing (not included). Exhibits good shear and peel strengths along with good impact and durability. It bonds extremely well to many surfaces, such as metals, ceramics, wood and some plastics.

UPC	Color	Size	Packaging
00-021200-41528-9	Black	37 mL	12/Case
00-021200-41530-2	Black	200 mL	12/Case
00-021200-41529-6	Black	400 mL	6/Case
00-021200-82236-0	Off-white	37 mL	12/Case
00-021200-87832-9	Off-white	200 mL	12/Case
00-021200-87833-6	Off-white	400 mL	6/Case



3M™ Scotch-Weld™ Epoxy Adhesive DP460NS Duo-Pak

Toughened, non-sag, two-part epoxy adhesive. 2:1 mix ratio, 60 minute work life and handling strength in approximately 4 hours. 3M™ Scotch-Weld™ EPX™ Plus II applicator and mix nozzles are required for dispensing (not included).

UPC	Color	Size	Packaging
00-021200-43670-3	Off-white	37 mL	12/Case
00-021200-43671-0	Off-white	200 mL	12/Case
00-021200-43672-7	Off-white	400 mL	6/Case



3M™ Stainless Steel Cleaner and Polish

Ideal for stainless steel, chrome, laminated plastics and aluminum surfaces. With a high-gloss formula, it wipes clean with no streaks or buildup, resists fingerprints and masks surface blemishes. Pleasant lime fragrance.

UPC	Description	Size	Packaging
50-048011-14002-0	Aerosol	21 oz.	12/Case



Scotch-Brite™ General Purpose Scouring Pad 96

Use for everyday cleaning of most cooking utensils and equipment. Scours 2 to 3 times faster and lasts 2 to 3 times longer than comparable pads. Non-rusting and resilient, this synthetic pad is an ideal replacement for steel wool or stainless steel scrubbers.

UPC	Color	Description	Size	Packaging
50-048011-08293-1	Green	20 Pads per box	6" x 9"	3 Boxes/Case



Scotch-Brite™ Heavy Duty Scouring Pad 86

Open construction pad with tough fibers and abrasives make fast work of heavy duty cleaning jobs. Use in the kitchen to replace scrapers, steel wool and metal sponges. Typical applications include heavily baked-on food and food processing equipment.


UPC	Color	Description	Size	Packaging
50-048011-05509-6	Green	12 Pads per box	6" x 9"	3 Boxes/Case



Scotch-Brite™ Medium Duty Scrub Sponge 74

Dual-action cleaning tool. On one side, it's a No. 96 scouring pad for scrubbing and cleaning. On the other side, the cellulose sponge quickly wipes up spills and messes and can carry cleaning solutions to the work surface.

UPC	Color	Size	Packaging
50-048011-20688-7	Yellow/Green	6.1" x 3.6" x 0.7"	20/Case



Scotch-Brite™ Purple Scour Pad 2020

Cleans your dirtiest pots and pans twice as fast as conventional heavy-duty scouring—with less scratching. Food debris rinses out of the pad easily. Unique web construction stands up to your toughest jobs. Scratches less than other heavy duty pads.

UPC	Color	Size	Packaging
50-048011-59033-7	Purple	2.8" x 4.5"	24/Case



Scotch-Brite™ Power Sponge 3000

Two cleaning tools in one – a Scotch-Brite™ Power Pad combined with a sponge. Up to eight times less abrasive than other medium duty/heavy duty commercial scouring products to reduce scratching. Features 3M's unique anti-microbial technology integrated into every fiber. Sponge resists growth of odor-causing bacteria through hundreds of uses.

UPC	Color	Size	Packaging
50-048011-23163-6	Purple/Green	2.8" x 4.5" x 0.6"	20/Case

Matting & Treads



3M™ Safety-Walk™ Cushion Matting 3270E

Spring-coiled vinyl foam compresses uniformly and continually, providing greater comfort and less fatigue. Suitable for medium-duty foot traffic. With edging. 0.55" thick.

UPC	Color	Size	Packaging
00-048011-34826-1	Black	3' x 5'	1/Case
00-048011-34827-8	Black	4' x 6'	1/Case



3M™ Safety-Walk™ Cushion Mat 5270E

Fatigue-resistant matting with integral edging. Suitable for heavy-duty foot traffic. With edging. 0.63" thick.

UPC	Color	Size	Packaging
00-048011-54577-6	Black	3' x 5'	1/Case
00-048011-55946-9	Black	4' x 6'	1/Case



3M™ Safety-Walk™ Slip-Resistant General Purpose Tapes and Treads 600 Series

This mineral-coated, slip-resistant material features a highly durable surface. Low-profile design helps reduce trip hazards.

UPC	ID	Color	Size	Packaging
50-048011-19221-0	610	Black	2" x 60'	2 Rolls/Case
50-048011-19223-4	610	Black	4" x 60'	1 Roll/Case
50-048011-19218-0	610	Black	6" x 24"	50 Treads/Case
50-048011-19224-1	610	Black	6" x 60'	1 Roll/Case
50-048011-26421-4	630	Safety Yellow	2" x 60'	2 Rolls/Case
50-048011-26420-7	630	Safety Yellow	4" x 60'	1 Roll/Case



3M™ Safety-Walk™ Slip-Resistant Medium Resilient Tapes and Treads 310 Series

Features a resilient, non-mineral, slip-resistant material. Soft surface is suitable for bare feet. For locker rooms and recreational/athletic equipment, boats and docks, interior stairwells, entryways and lobbies.

UPC	ID	Color	Size	Packaging
50-048011-19294-4	310	Black	2" x 60'	2 Rolls/Case
50-048011-19296-8	310	Black	4" x 60'	1 Roll/Case
50-048011-19292-0	310	Black	6" x 24"	50 Treads/Case
50-048011-19297-5	310	Black	6" x 60'	1 Roll/Case



3M™ Perfect-It™ Foam Compounding Pad

High performance foam compounding pad. Refines P1200 or finer sand scratches. For use with 3M™ Compounds. The Perfect-It brand means this is 3M's highest performing foam compounding pad.

UPC	Color	Description	Use With	Size	Case Qty/Units
00-051131-05706-7	White	Double sided	3M™ Quick Connect Adaptor 05752	9"	6/Case
00-051131-33284-3	White	Double sided	3M™ Quick Connect Adaptor 05752	6"	6/Case
00-051131-05737-1	White	Single sided	3M™ Hookit™ backup pads (PN 05717 or PN 05718)	8"	6/Case



3M™ Perfect-It™ EX Rubbing Compound

3M's best rubbing compound when looking for EXtra performance: EXtra Cutting. EXtra Smooth Handling. EXtremely Easy to Use and Clean Up. Unique formula quickly removes P1200 grade and finer sand scratches and other surface defects.

UPC	Size	Case Qty/Units
00-051131-36058-7	8 oz.	12/Case
00-051131-36060-0	1 qt.	6/Case
00-051131-36061-7	1 gal.	4/Case

Safety Products



3M™ Maintenance Sorbent Rug, High Capacity

This maintenance sorbent rug is designed for use in industrial maintenance applications. It is designed to sorb liquids while enduring the punishment of being tread upon. Sorbent rugs are both durable and versatile. The M-RGC36100E coating acts as a fluid barrier, protecting the surface below the rug.

UPC	ID	Color	Description	Size	Packaging
00-051138-29002-3	M-RGC36300E	Gray	Rug	36" x 300'	1/Case
00-051138-29003-0	M-RGC36100E	Gray	Rug with coating	36" x 100'	1/Case



3M™ Maintenance Sorbent Pillow M-PL715

Maintenance sorbent pillows are designed with a scrim that encases particulate sorbent material. Used in areas where greater capacity than a sorbent pad is desired. Small and lightweight, pillows are tear-resistant.

UPC	ID	Description	Size	Packaging
50-051138-21531-1	M-PL715	Sorbs approx. 8 gal./Case	7" x 15"	16/Case



3M™ Maintenance Sorbent Folded M-FL550DD, High Capacity

This high capacity maintenance sorbent has a scrim on one side to increase strength and help eliminate linting. Dispenses from a carrying/dispenser box in the form of a continuous roll, perforated every 16" so you can select the length required. Utilizing 3M's folded sorbent technology, it can be used as a pillow, pad, roll or boom.

UPC	ID	Size	Packaging
50-051131-07172-3	M-FL550DD	5" x 50'	3/Case



3M™ Maintenance Sorbent Pad M-PD1520DD, High Capacity

This high capacity sorbent has a scrim on one side to increase strength and help eliminate linting. This conveniently sized pad allows the user to quickly spread sorbent on and in the path of a spill.

UPC	ID	Description	Size	Packaging
50-051131-07164-8	M-PD1520DD	Sorbs approx. 37.5 gal./Case	15.5" x 20.5"	100/Case



3M™ Maintenance Sorbent Roll M-RL15150DD, High Capacity

This maintenance sorbent pad has a scrim on one side to increase the strength and help eliminate linting. Available in a convenient width of 15", perfect for lining drawers, covering workbenches or masking larger areas from mist and overspray.

UPC	ID	Description	Size	Packaging
50-051131-07166-2	M-RL15150DD	Sorbs approx. 31 gal./Case	15.5" x 150'	1/Case



3M™ Petroleum Sorbent Pads, High Capacity

High capacity petroleum sorbent pads have a scrim on one side to increase strength and help eliminate linting. Conveniently sized pads allow the user to quickly spread sorbent over and in the path of a spill.

UPC	ID	Description	Size	Packaging
50-051138-28991-6	HP-156	Sorbs approx. 37.5 gal.	17" x 19"	100/Case
00-051138-29116-7	HP-157	Sorbs approx. 75 gal.	34" x 38"	50/Case



3M™ Petroleum Sorbent Folded P-FL550DD

Four folded petroleum sorbents in one. It can be used as a boom, pillow, pad, or roll, which means fewer products need to be stocked to meet your sorbent needs. Perforations every 16" allow you to select the length desired. Each perforated sheet unfolds to approximately 18" by 16".

UPC	ID	Description	Size	Packaging
50-051131-07173-0	P-FL550DD	Sorbs approx. 31.5 gal.	5" x 50'	3 Boxes/Case



3M™ Particulate Respirator 8210, N95

Designed to help provide comfortable, reliable worker protection against certain non-oil based particles. Its lightweight construction helps promote greater worker acceptance, comfort and increased wear time.

UPC	Description	Packaging
50-051138-46457-3	20/Inr	160/Case



3M™ Particulate Respirator 8511, N95

Uniquely designed to help provide protection against certain non-oil based particles. It is ideally suited for work settings that involve heat, humidity, or long periods of wear.

UPC	Description	Packaging
50-051138-54343-8	10/Inr	80/Case



3M™ Half Facepiece 6300

For use with 3M™ Cartridges 6000 Series; 3M™ Filters 2000, 2200, 7000 or 5000 Series; or 3M™ Dual Airline Systems for protection against a variety of gases, vapors and particulate hazards according to NIOSH approvals.

UPC	ID	Size	Packaging
50-051131-07026-9	6300	Large	24/Case



3M™ Full Facepiece 6000 Series

For use with 3M™ Cartridges 6000 Series; 3M™ Filters 2000, 2200, 7000 or 5000 Series; or 3M™ Dual Airline Systems for protection against a variety of gases, vapors and particulate hazards according to NIOSH approvals.

UPC	ID	Size	Packaging
50-051138-54159-5	6900	Large	4/Case





3M™ Particulate Filter with Nuisance Level Organic Vapor Relief 2097, P100

NIOSH approved for environments containing certain oil and non-oil based particles. Use with 3M™ Respirators 5000 Series or 3M™ Cartridge 6000 Series with 3M™ Adapter 502, or 3M™ Half and Full Facepieces 6000, 7000 and FF-400 Series with bayonet filter holders.

- Not NIOSH certified for use against ozone.

UPC	Packaging
50-051131-07184-6	100/Case



3M™ Organic Vapor Cartridge 6001

NIOSH approved against certain organic vapors. Use with 3M™ Half and Full Facepieces 6000, 7000 and FF-400 Series with bayonet filter holders.


UPC	Packaging
50-051138-21674-5	60/Case



3M™ SecureFit™ Protective Eyewear

Stylish, lightweight design weighs less than one oz. Features proprietary 3M™ Pressure Diffusion Temple Technology that helps diffuse pressure over the ear to enhance frame comfort while not compromising the security of fit across a diverse workforce. Meets ANSI Z87.1-2010 and CSA Z94.3 standards.


UPC	ID	Packaging
10-078371-65717-5	SF201AF	20/Case



3M™ E-A-R™ Classic™ Foam Earplugs

3M™ E-A-R™ Classic™ earplugs set the standard in hearing protection as the world's first foam earplugs. Constructed from slow-recovery foam that is flame-resistant and moisture-resistant. NRR 29 db.* Test compatible with 3M™ E-A-Rfit™ Validation System. Packaged 200 pair/Box, 10 boxes/Case.

UPC	ID	Description	Packaging
10-080529-10000-6	310-1001	Uncorded, Pillow Pack	2000/Case
10-080529-11001-2	311-1101	Corded, Poly Bag	2000/Case
10-080529-12002-8	312-1201	Uncorded, Poly Bag	2000/Case



3M™ E-A-R™ UltraFit™ Earplugs 340-4004

Feature a proprietary, premolded, triple-flange design that fits comfortably in most earcanals. Soft polymer is washable and reusable. NRR 25 dB.* Test compatible with 3M™ E-A-Rfit™ Validation System. Packaged 100 pair/Box, 4 boxes/Case.

UPC	ID	Description	Packaging
10-080529-40003-8	340-4004	Corded, Poly Bag	400/Case



3M™ Speedglas™ Welding Helmet 9100 FX

Features a flip-up 9100XX dark shade 5, 8-13 auto-darkening filter assembly, shade 5 Side Windows and a clear 8" x 4.25" (200 mm x 110 mm) faceshield. For Stick, MIG and TIG processes, grinding and torch cutting.

UPC	ID	Packaging
00-051131-49675-0	06-0600-30SW	1/Case

*The NRR may overestimate the protection provided during typical use.

3M recommends reducing the NRR by 50% for estimating the amount of noise reduction provided.

Spray Equipment for Coatings



3M™ Dirt Trap Protection Material

White non-woven surface protection material with adhesive backing. Designed to protect surfaces while trapping dust, dirt, and paint overspray. Great for capturing and containing foreign object debris.

UPC	ID	Color	Size	Case Qty/Units
00-051131-36849-1	36849	White	4" x 300'	6 Rolls per case
00-051131-36850-7	36850	White	6" x 300'	4 Rolls per case
00-051131-36851-4	36851	White	14" x 300'	1 Roll per case
00-051131-36852-1	36852	White	28" x 300'	1 Roll per case
00-051131-36853-8	36853	White	56" x 300'	1 Roll per case



3M™ Accuspray™ Spray Gun Model HG14

Accuspray™ technology for applications requiring the use of a 1.4 mm atomizing head. Like all Accuspray System guns, the HG14 kit delivers the equivalent of a new spray gun—whenever you want one—for a fraction of the cost. Kit contains one spray gun, three atomizing heads and an airflow control valve. Orange color on handle.

UPC	Size	Case Qty/Units
00-051131-16577-9	1.4 mm	1/Case



3M™ Accuspray™ Spray Gun Model HG18

This revolutionary product provides the equivalent of a brand new spray gun on demand for a fraction of the cost. Kit contains one spray gun, three atomizing heads and an airflow control valve. Silver colored handle.

UPC	Size	Case Qty/Units
00-051131-16570-0	1.8 mm	1/Case



3M™ Accuspray™ Atomizing Head

Replaceable atomizing heads for use with any 3M™ Accuspray™ Spray Gun with replaceable atomizing head technology. Refill kits contain four atomizing heads.

UPC	Color	Size	Case Qty/Units
00-051131-16609-7	Red Opaque	2.0 mm	4 Heads per kit/6 Kits per case
00-051131-16611-0	Clear	1.8 mm	4 Heads per kit/6 Kits per case
00-051131-16612-7	Orange	1.4 mm	4 Heads per kit/6 Kits per case

Tapes



3M™ Utility Duct Tape 2929

General use grade, conformable cloth duct tape made with polyethylene film over cloth scrim and rubber adhesive. A good choice for temporary repairs, sealing, holding and marking.

UPC	Color	Description	Size	Case Qty/Units
00-051115-24883-2	Silver	Individually labeled	1.88" x 50 yd.	24 Rolls per case



3M™ Heavy Duty Duct Tape 3939

Waterproof polyethylene film over cloth scrim backing, with a rubber adhesive used for demanding duct tape applications. High-tack adhesive for good, quick stick to many surfaces. Offers easy tear and conformability. Good moisture resistance. Good tensile strength. 9.0 mil.

UPC	Color	Description	Size	Case Qty/Units
00-051131-06975-6	Silver	Individually labeled	48 mm x 54.8 m	24 Rolls per case
00-021200-85562-7	Silver	Bulk	72 mm x 54.8 m	12 Rolls per case



3M™ High Performance Green Masking Tape 401+

High performance masking tape used for critical paint masking applications. 3M proprietary solvent-free adhesive sticks with confidence to most surfaces including metal, rubber, glass, and plastic, while removing cleanly in one piece. Temperature range up to 250°F (121°C) for 30 minutes.

UPC	Color	Description	Size	Case Qty/Units
00-051115-64759-8	Green	Bulk	12 mm x 55 m	48 Rolls per case
00-051115-64760-4	Green	Bulk	18 mm x 55 m	48 Rolls per case
00-051115-64761-1	Green	Bulk	24 mm x 55 m	24 Rolls per case
00-051115-64767-3	Green	Individually labeled	24 mm x 55 m	24 Rolls per case
00-051115-64762-8	Green	Bulk	36 mm x 55 m	16 Rolls per case
00-051115-64768-0	Green	Individually labeled	36 mm x 55 m	16 Rolls per case
00-051115-64763-5	Green	Bulk	48 mm x 55 m	12 Rolls per case
00-051115-64769-7	Green	Individually labeled	48 mm x 55 m	12 Rolls per case
00-051115-69109-6	Green	Bulk	6 mm x 55 m	96 Rolls per case
00-051115-64764-2	Green	Bulk	72 mm x 55 m	8 Rolls per case
00-070006-74575-9	Green	Log Roll, Bulk	1490 mm x 55 m	1 Roll per case



Scotch® Filament Tape 890MSR

Polyester backed tape with a modified synthetic rubber adhesive and is reinforced with fiberglass filaments. Offered in clear or black. Tensile strength: 600 lb./in.

UPC	Color	Description	Size	Case Qty/Units
00-051125-74062-3	Black	Bulk	12 mm x 55 m	72 Rolls per Case
00-051125-74063-0	Black	Bulk	18 mm x 55 m	48 Rolls per Case
00-051125-74064-7	Black	Bulk	24 mm x 55 m	36 Rolls per Case
00-051125-74057-9	Clear	Bulk	12 mm x 55 m	72 Rolls per Case
00-051125-74058-6	Clear	Bulk	18 mm x 55 m	48 Rolls per Case
00-051125-74943-5	Clear	Individually labeled	24 mm x 55 m	36 Rolls per Case
00-051125-74059-3	Clear	Bulk	24 mm x 55 m	36 Rolls per Case
00-051125-74060-9	Clear	Bulk	36 mm x 55 m	24 Rolls per Case
00-051125-74942-8	Clear	Individually labeled	48 mm x 55 m	24 Rolls per Case
00-051125-74061-6	Clear	Bulk	48 mm x 55 m	24 Rolls per Case



Scotch® Filament Tape 8919MSR

Clear polyester backed tape with a modified synthetic rubber adhesive, reinforced with fiberglass filaments. Tensile strength: 380 lb./in.

UPC	Description	Size	Case Qty/Units
00-051125-74051-7	Bulk	18 mm x 55 m	48 Rolls per case
00-051125-74939-8	Individually labeled	24 mm x 55 m	2 Rolls per pack, 18 Packs per case
00-051125-74052-4	Bulk	24 mm x 55 m	36 Rolls per case
00-051125-74053-1	Bulk	36 mm x 55 m	24 Rolls per case
00-051125-74940-4	Individually labeled	48 mm x 55 m	24 Rolls per case
00-051125-74054-8	Bulk	48 mm x 55 m	24 Rolls per case
00-051125-74941-1	Individually labeled	72 mm x 55 m	12 Rolls per case
00-051125-74055-5	Bulk	72 mm x 55 m	12 Rolls per case
00-051125-74056-2	Bulk	96 mm x 55 m	8 Rolls per case



Scotch® Filament Tape 898

Clear polypropylene backing with a synthetic rubber resin adhesive resists abrasions, moisture, scuffing and tearing. Fiberglass reinforced. Ideal for L-clip box closures. High strength bundling and reinforcing, strapping and non-regular slotted container closing.


UPC	Description	Size	Case Qty/Units
00-051125-74913-8	Individually labeled	12 mm x 55 m	2 Rolls per pack, 36 Packs per case
00-051125-74914-5	Individually labeled	18 mm x 55 m	2 Rolls per pack, 24 Packs per case
00-051125-74915-2	Individually labeled	24 mm x 55 m	36 Rolls per case
00-051131-06898-8	Bulk	24 mm x 55 m	36 Rolls per case
00-051111-91756-5	Bulk	36 mm x 110 m	24 Rolls per case
00-021200-39868-1	Bulk	36 mm x 55 m	24 Rolls per case
00-021200-39871-1	Individually labeled	48 mm x 55 m	12 Rolls per inner, 24 Rolls per case
00-051125-74916-9	Individually labeled	48 mm x 55 m	24 Rolls per case
00-021200-39869-8	Bulk	48 mm x 55 m	24 Rolls per case



3M™ VHB™ Heavy Duty Outdoor/Indoor Mounting Tape 5952

A very conformable foam that bonds and seals simultaneously to withstand vibration, impact and weathering. 45.0 mil.

UPC	Color	Description	Size	Case Qty/Units
00-021200-74122-7	Black	Small Pack	1/2" x 36 yd.	4 Rolls per case
00-021200-59967-5	Black	—	1/2" x 36 yd.	18 Rolls per case
00-051115-25522-9	Black	—	3/4" x 15 yd.	12 Rolls per case
00-021200-97056-6	Black	Bulk	3/4" x 36 yd.	12 Rolls per case
00-021200-74123-4	Black	Small Pack	3/4" x 36 yd.	3 Rolls per case
00-021200-74121-0	Black	Small Pack	1" x 36 yd.	2 Rolls per case
00-021200-56229-7	Black	—	1" x 36 yd.	9 Rolls per case



3M™ VHB™ Tape 5925

Very conformable foam, modified acrylic adhesive, thickness 0.025" (0.64 mm), red PE film liner. UL 746C -File MH17478. 25.0 mil.

UPC	Color	Size	Case Qty/Units
00-021200-56297-6	Black	1/4" x 36 yd.	36 Rolls per case
00-021200-56230-3	Black	1/2" x 72 yd.	18 Rolls per case
00-021200-56228-0	Black	1" x 72 yd.	9 Rolls per case



3M™ VHB™ Tape 5925WF

Very conformable foam, modified acrylic adhesive, thickness 0.025" (0.64 mm), red PE film liner. UL 746C -File MH17478. 25.0 mil.

UPC	Color	Size	Case Qty/Units
00-051115-63866-4	White	1" x 72 yd.	9 Rolls per case



3M™ VHB™ Tape 5962

Very conformable foam, modified acrylic adhesive, 62.0 mil, red PE film liner. UL 746C -File MH17478.

UPC	Color	Size	Case Qty/Units
00-021200-74165-4	Black	1" x 36 yd.	9 Rolls per case



SORBENT PRODUCTS WARNING

Failure to properly handle and dispose of sorbents contaminated by hazardous materials could result in serious physical injury or death. For proper handling, consult the Material Safety Data Sheet for the material absorbed, applicable safety and health standards, contact your supervisor, or call 3M CSD Technical Service in the USA at 1-800-626-8578.



RESPIRATORY PRODUCTS WARNING

These respirators help protect against certain airborne contaminants. Before use, the wearer must read and understand the USER Instructions provided as a part of the product packaging. A written respiratory protection program must be implemented meeting all the requirements of OSHA 1910.134 including training, fit testing and medical evaluation. In Canada, CSA standards Z94.4 requirements must be met and/or requirements of the applicable jurisdiction, as appropriate. **Misuse may result in sickness or death.** For proper use, see packaging instructions, supervisor, or call 3M OH&ESD Technical Service in USA at 1-800-243-4630 and in Canada at 1-800-267-4414.



EYE & FACE PRODUCT WARNING

These eye and face protection products help provide limited eye and face protection. **Misuse or failure to follow warnings and instructions may result in serious potential injury, including blindness or death.** For proper use, selection, and applications against flying particles, optical radiation and / or splash see supervisor, read User Instructions and warnings on the package or call 3M OH&ESD Technical Service in the USA at 1-800-243-4630. In Canada, call 1-800-267-4414.



HEARING PROTECTION PRODUCTS WARNING

These hearing protectors help reduce exposure to hazardous noise and other loud sounds. **Misuse or failure to wear hearing protectors at all times that you are exposed to noise may result in hearing loss or injury.** For proper use, see supervisor, User Instructions, or call 3M in USA at 1-800-243-4630. In Canada, call Technical Service at 1-800-267-4414. If there is any drainage from your ear or you have an ear infection, consult with your physician before wearing ear plugs. Failure to do so may result in hearing loss or injury.



WELDING HELMET WARNING

This product is designed to help protect the wearer's eyes and face from harmful radiation including visible light, ultra-violet radiation (UV), infra-red radiation (IR), sparks and spatter resulting from welding processes. These products must be used only by qualified persons who are properly trained in their use and maintenance. **Misuse may result in permanent eye injury and vision loss.** Always wear ANSI Z87.1 compliant safety spectacles in addition to any welding helmet. For proper use, see supervisor, or User Instructions or call 3M in USA 1-800-243-4630. In Canada, call Technical Service at 1-800-267-4414.



IMPORTANT NOTICE TO PURCHASER

Warranty, Limited Remedy, and Disclaimer: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. User is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application. Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

3M, Accuspray, Classic, E-A-R, E-A-Rfit, EPX, Hookit, Perfect-It, Roloc, Safety-Walk, Scotch-Brite, Scotch-Weld, SecureFit, Speedglas, Trizact, UltraFit, and VHB are trademarks of 3M. Scotch is a registered trademark of 3M.



Industrial Markets Center

3M Center, Building 225-4S-25
St. Paul, MN 55144-1000
www.3M.com

Please recycle. Printed in USA.
© 3M 2014. All rights reserved.