3M

Diamond Grade[™] Conspicuity Marking Series 997/997S

Description

Advantages

- Durable, flexible, microprismatic, retroreflective sheeting
- For applications on soft sided vehicles
- Excellent angularity in both horizontal and vertical
- Easy to apply
- Up to 3 years exterior durability
- Sheeting resists fuel vapors or occasional spills
- 997S is the segmented version



Application and Uses

3M[™] Diamond Grade[™] Conspicuity Marking for Curtain Sided Vehicles Series 997 is designed to mark the side and rear perimeter of trucks and trailers for enhanced visibility and detection.

ECE Norms

Diamond Grade Series 997 is approved as Retroreflective Markings for heavy and long vehicles and their trailers according to ECE regulation 104.

Limitations of End Uses

We do not normally warrant other applications, but please contact 3M to discuss your needs further.

Specifically, we do not warrant this sheeting for the application on digitally printed canvas protected by a water based clear coat.

Product line

Property	Desc	Description		
Number and color	997	-10	White	
		-71	Yellow	
		-72	Red	

Characteristics

Property	Description
Adhesive color and type	Clear, Pressure Sensitive
Liner	Opaque paper
Application substrates	3M approved canvas, not
	older than 6 months
Application temperature	10°C to 30°C
range for air and	
substrate	
Thickness without	0,36 - 0,4mm
premask tape	
Performance range	-35°C to +65°C

General Performance Characteristics

The durability of Marking Series 997 depends on the following:

- Selection, preparation and temperature of the substrate
- Application methods
- Cleaning and maintenance methods
- Exposure conditions

Warranted Durability

The sheeting is warranted for 36 months when used as vehicle marking and the exposure of the face is vertical at 90° \pm 10°.

Further information about warranty can be obtained from 3M.

You have statutory rights. Our goods come with guarantees that cannot be excluded under the Australian Consumer Law. You are entitled to a replacement or refund for a major failure and compensation for any other reasonably foreseeable loss or damage. You are also entitled to have the goods repaired or replaced if the goods fail to be of acceptable quality and the failure does not amount to a major failure.

Application

- Check the proper temperature using an Infrared-Thermometer like 3M[™] Scotchtrak[™] IR-500.
- Do not overlap sheeting
- Application underneath belts or buckles is not recommended.
- Remove premask tape after application using a 180° pull off angle.
- Allow the canvas to remain undisturbed for a minimum of 2 hrs after application
- Contact your 3M representative for detailed processing and application procedures

Maintenance and Cleaning

Hand wash with sponge, cloth, or soft brush using warm water and detergent. The cleaner must be wet, non-abrasive, without strong solvents and have a pH value between 3 and 11 (neither strongly acidic nor strongly alkaline). Rinse thoroughly.

To remove grease, oil. or tar, use cloth moistened with heptane, VM&P naptha or mineral spirits. Wash with detergent and water and rinse thoroughly. Using the high pressure hot steam cleaning the following conditions should be applied/ set up:

- maximum pressure 80 bar
- maximum temperature 60°C
- minimum of 30 cm distance of cleaning jet from sheeting surface
- cleaning wand to be held at no greater angle than 45 degree from perpendicular to the sheeting surface

Storage and Shelf Life

- Marking series 997 must be used within 1 year after date of receipt from 3M.
- Partially used rolls should be returned to the shipping carton or suspended horizontally from a rod or pipe through the core.
- Store the sheeting in a clean, dry area and away from direct sunlight.

Chemical Resistance

- Resists mild acids, mild alkalis and salts
- Excellent water resistance
- Resists occasional fuel spills

Important Notice to Purchaser/ User

All statements, technical information and recommendations herein are based on tests we believe to be reliable, but the accuracy or completeness thereof is not guaranteed. We shall not be liable and no warranty shall apply for products not applied according to our published information folder.

Before using, a user must determine the suitability of the product for its intended use, and the user assumes all risk and liability whatsoever in connection therewith. All questions of warranty and liability relating to this product are governed by the terms of the sale subject, where applicable, to the prevailing law.

For Further Assistance

For help on specific questions relating to 3M Scotchlite products, please contact your local 3M Technical service person or contact:

Traffic Safety Systems Division 3M Australia Pty 3M Centre, Bldg A, 1 Rivett Road North Ryde NSW 2113 Tel: 136 136

www.3MReflective.com.au

Traffic Safety Systems Division 3M New Zealand Ltd, 94 Apollo Drive, Rosedale Auckland Tel: 0800252627